

HP DesignJet T2600dr 36-in PostScript Multifunction Printer (3EK15B)



ENGINEERED FOR COLLABORATION—Turn your workgroups into highly efficient teams

Create highly efficient teams with the most compact, quiet MFP[3] that supports collaboration with a smart interface and access to shared folders.[2] Meet deadlines with the fastest print speed and the only automatic print stacking.[3]



SEAMLESS EXPERIENCE—Designed for all

Radically simple experience with a smart 15.6-inch interface and the easiest PDF printing with HP Click.[1]

UNLEASH PERFORMANCE—To turn design into delivery

Showcase design versatility from precise line drafts to boldly colored 3D renders, with HP Bright Office Inks.

SECURE—World's most secure large-format printer[5]

Rely on the best network protection with features like HP Secure Boot and whitelisting.[5]

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print, copy, scan
Connectivity, standard	Gigabit Ethernet (1000Base-T), Wi-Fi (with optional Jetdirect accessory), supporting the following standards: TCP/IP, BootP/DHCP (IPv4 only), DHCPv6, TFTP (IPv4 only), SNMP (v1, v2c, v3), Apple Bonjour Compatible, WS Discovery, Embedded Web Server (HTTP, HTTPS), IPsec, SMTP (email), Raw IP printing (9100), LPD, IPP, WS print, NTLM v2, SMBv3, SSL/TLS, 802.1X authentication (LEAP, PEAP, EAP-TLS), DFS
Mobile printing capability	Direct print from mobile apps on iOS, Android, and Chrome OS; email printing with HP ePrint and HP Smart app for iOS and Android
Software included	HP Click, HP mobile, ePrint and iOS/Android support plus the HP Smart app for mobile, HP Web Jetadmin, HP JetAdvantage Security Manager, HP SmartTracker (optional)
Energy star certified	Yes
Scan file format	JPEG, TIFF and multipage TIFF, PDF and multipage PDF
Scan input modes	USB, shared network folder, printer HDD, email
Scanner type	Sheetfed, CIS (Contact Image Sensor)
Minimum dimensions (W x D x H)	1390 x 760 x 1240 mm
Minimum dimensions (W x D x H)	55 x 30 x 49 in
Weight	109 kg
Weight	240 lb
Power consumption	120 W (printing); <36 W (ready); <10 W (sleep); 0.3 W (off)
Environmental certification	ENERGY STAR, ErP, WEEE, RoHS (EU, China, Korea, India), REACH, EPEAT
What's in the box	HP DesignJet T2600 Multifunction Printer, printer stand and media bin, 15.6" touchscreen, spindles (x2), printheads, introductory ink cartridges, user guide, power cords
Manufacturer Warranty	One-year limited hardware warranty

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Compared to Canon Direct Print & Share and based on "One Click Print." Once image is selected, one-click printing when printing the entire file without any modifications to the print settings. Applicable to PDF, JPEG, TIFF, DWF, HP-GL/2 files.

[2] Using Lightweight Directory Access Protocol (LDAP).

[3] Based on comparable large-format inkjet printers under \$12,000 (USD) as of December, 2018. IDC figures show that Canon, Epson, and HP combine for 98% share of this printing category worldwide as of Q3, 2018. Most compact footprint calculated using all devices in "Operation mode" with an Open Basket and the arm of the Screen (front panel) spread out to enable user interaction and the scanner lifted on the Canon TX 3000 T36 MFP and the Epson SC-T5200 MFP to enable top media loading. Most quiet according to internal HP testing of sound pressure level during operating mode (plain paper, line drawing, Normal mode) compared to published specification of competitive printers. Percentage calculations of noise based on lineal units vs. Canon TX-3000 published spec of 51dB(A). Fastest print speed based on sustained printing speeds. Only automatic print stacking based on unicity of the integrated stacker versus competitive printers only offering basket or bin with stacking position.

[5] Advanced embedded security features are based on HP review of 2019 published embedded security features of competitive printers, as of February 2019.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

