



GUS4C2

Access Pro USB-C 2-Port Keyboard Mouse & Peripheral Switch (TAA Compliant)

The IOGEAR TAA Compliant Access Pro 2-Port Keyboard, Mouse & Peripheral Switch lets you share a keyboard and mouse as well as other USB peripherals and instantly switch between two USB-C-equipped laptops or desktops with the push of a button.



Features

- Quickly switch & share devices on 2 USB-C computers
- Transfer files¹ between connected Mac & PC with Beyond OS™ software
- Charge devices with up to 85W PD3.02 on Port 1
- Switch method via remote push-button, mouse swipe¹ or hotkey combination³
- LED indicator shows active host computer
- File transfer function supports both Windows and Mac OS X
- 3x USB-A and 1x USB-C ports
- Supports up to 10Gbps data transfer rate
- Plug-n-play, no driver installation required
- Overcurrent protection safeguards USB devices from power damage
- TAA Compliant

Note

1 Beyond OSTM software installation is required on both USB-C computers

2 Actual Power wattage depends on the capacity of USB-C power adapter used

3 Keyboard must be connected to USB-A port 1

Requirements

- USB-C (Thunderbolt 3 compatible) host computer
- 1x standard 104 key wired USB keyboard (for hotkey switching)*
- Windows 10
- Mac OS X 10.12 and higher

Package Contents

- 1 x GUS4C2
- 1 x 6ft Remote Push-button
- 2 x USB-C 3.1 G2 Cable (1m)
- 1 x Quick Start Guide
- 1 x Warranty Card

*In order for hot key operation of the keyboard when switching computers, our switch emulates a standard wired 104 key

www.iogear.com



keyboard. We can not guarantee the use of wireless (including Bluetooth), multifunction, gaming, integrated card readers, or programmable keyboards.



Specifications

FUNCTION	GUS4C2
Upstream Port	
USB-C	2x USB-C Gen 2 (Thunderbolt 3 compatible)
Downstream Port	
USB-A	3x USB-A 3.1 Gen 2 (blue), support up to 10W total for 3 x USB-A + 1 x USB-C
USB-C	1x USB-C 3.1 Gen 2 (black), support up to 10W total for 3 x USB-A + 1 x USB-C
Data Rate	Up to 10Gbps
Power	
Power Pass-Thru	100W, designated to port 1 host computer only (A total of up to 85W can be charged to the laptop after deduction of max 15W used by the dock)
LEDs	
Host Status	White when target host computer is activated
Overcurrent	LED will flash when total power of downstream USB-A and USB-C port over 10W
Operating System Requirements	
Mac	Mac OS X 10.x
Windows	Windows 10
DIMENSIONS	GUS4C2
Unit Dimensions	
Height	0.9" (2.3 cm)
Length	5.6" (14.2 cm)
Depth	3.54" (9 cm)
Unit Package Dimensions	
Length	7.28"
Width	6.1"
Depth	2.16"
Master Carton	
Height	7"
Width	15.16"
Depth	8.12"
Master Carton Qty.	6 pc
Weight	
Master Carton Wt.	8.25 lbs
Unit Pack Wt.	1.25 lbs



DIMENSIONS	GUS4C2
Unit Wt.	0.65 lb