



GTD737

Quantum Dual Mode Thunderbolt 3 Dock Pro Station

Simplify personal and professional dual 4K workspaces with the ultra-fast connectivity of the IOGEAR Quantum Dual Mode Thunderbolt™ 3 Dock Pro™ Station. Expand to a full workstation with nine (9) additional ports and a variety of high-speed connectors through the single included Thunderbolt 3 (USB-C) cable.



Features

- Dual 4K @60Hz displays with a Thunderbolt 3 Laptop
- Single 4K @30Hz display or dual HD displays with a USB-C with DP Alt Mode Laptop*
- Charging Power up to 60W via external 135W power supply
- Integrated Ethernet Gigabit network speeds (10/100/1000Mbps)
- File transfers at up to 40Gbps speeds via Thunderbolt 3

*Laptops using USB-C DP Alt-mode ports will run dual monitors up to 1080p on Windows and dual 4096 x 2160 @ 30hz (Mirrored) on Mac OS

*New M1 Chip Macbooks with USB4 ports are limited to one external display.

Requirements

- Mac OSX Sierra 10.12 or later
- Windows 10 or later
- Thunderbolt 3 (USB-C) enabled computers or computers with USB-C DP alt mode support*

*USB-C DP alt mode enabled computers will run at lower resolutions. See Features for more information.

Package Contents

- 1x GTD737
- 1x Thunderbolt 3 0.7m cable
- 1x AC Power adapter
- 1x Quick Start Guide
- 1x Warranty Card



Specifications

FUNCTION	GTD737	DIMENSIONS	GTD737
Upstream Port		Unit Dimensions	
Thunderbolt	Thunderbolt 3	Height	1.06" (2.7 cm)
Cable Length	2.3ft (0.7m)	Length	6.6" (16.9 cm)
Connectors		Depth	3.14" (8 cm)
Audio Input	1x 3.5mm Combo headphone jack	Unit Package Dimensions	
USB-A	1x USB-A(3.1 Gen 2, BC 1.2) 2x USB-A(3.1 Gen 1)	Height	5.9"
USB-C	2x USB-C(3.1 Gen 2)	Width	9.17"
LAN	Gigabit (10/100/1000Mbps)	Depth	3.3"
Display Output		Master Carton	
DisplayPort	2x Displayport 1.2	Height	9.44"
Cable Type	Thunderbolt 3 40Gbps	Width	10.7"
		Depth	6.7"
Resolution	Thunderbolt Mode: Dual Display up to 4096x2160@60Hz, Single Display up to 4096x2160@60Hz / USB-C Mode: Dual Display up to 1920x1080@60Hz(extended mode)Windows, Dual Display 4096x2160@30Hz(Mirror mode)- Mac , Single View up to 4096x2160@30Hz- both Mac & Wi	Master Carton Qty.	3 pc
		Weight	
		Master Carton Wt.	9.2 lbs
		Unit Pack Wt.	2.75 lbs
		Unit Wt.	0.7 lbs