



GUD3C04

# Access Pro™ 2-Port USB-C KVM Switch (TAA Compliant)

Easily switch between two USB-C devices and control them with one keyboard, one mouse and view content on one 4K monitor. IOGEAR's Access Pro™ 2-Port USB-C KVM Switch requires no software and comes complete with the Power Delivery function, USB-C cables, and a 6-foot push-button remote switch.



HDMI®  
HIGH DEFINITION MULTIMEDIA INTERFACE



## Features

- 2-Port USB-C KVM Switch with Power Passthrough
- Control and share 2 USB-C devices with DP Alt Mode from one keyboard, mouse, and an HDMI monitor
- Power Passthrough<sup>1</sup> with up to 75W charging for laptop<sup>2</sup> and up to 10W for smartphone<sup>3</sup>
- Supports USB-C/Thunderbolt™ 3 MacBook Air®, MacBook Pro®, iPad Pro®, Windows® & Android 8+ devices
- Resolution up to 4K UHD 3840 x 2160 @30Hz for USB-C laptops
- Resolution up to 1080p @60 for USB-C tablets and smartphones
- Thunderbolt 3 laptop compatible
- USB 3.1 Gen1 supports data transfer rates up to 5 Gbps
- Compatible with Apple M1 chip devices; provides power for laptop charging up to 85W (USB-C Power Adapter is needed)
- Convenient switching between devices via a push-button remote
- Supports DeX® Mode<sup>4</sup> on Samsung USB-C smartphones
- Plug-n-Play; no software or driver needed
- HDCP 1.4 Compliant

Note:

<sup>1</sup>Connect Limited Power Source (LPS) certified USB-C power adapter

<sup>2</sup>Must be plugged into Primary USB-C port 1

<sup>3</sup>When plugged into Secondary USB-C port 2

<sup>4</sup>Samsung DeX Mode is only supported on Samsung Galaxy S8, S8+, S9, S9+, S10, S10+, and Note 8, Note 9, and Tab S4; other Android devices support mirror screen

## Requirements

### Sources:

- USB-C enabled devices with DP-Alt Mode over USB-C
- USB-C external power source (recommend a Limited Power Source (LPS) certified USB-C power adapter)

## Package Contents

- 2-Port USB-C KVM Switch with Power Delivery
- 2 x 3ft USB-C to USB-C cables
- 1 x 6ft Remote pushbutton
- Quick Start Guide
- Warranty Card

[www.iogear.com](http://www.iogear.com)



**Console:**

- HDMI monitor
- Standard wired 104 keys USB keyboard
- Standard wired 2 or 3-button USB mouse

**Operations:**

- Windows® 10 (32/64 bit)+
- MacOS® X 10.12+
- iPadOS® 12.1+; iPad Pro® 3rd generation (2018)1
- Android 8+2
- Chrome OS®

\*For complete HID keyboard and mouse support, iPadOS 13+ is recommended \*\*2DeX Mode is only supported on Samsung Galaxy S8, S8+, S9, S9+, and Note 8, Note 9, and Tab S4 for extended screen; other Android devices support mirror screen



## Specifications

<b>FUNCTION</b>	<b>GUD3C04</b>
Upstream Port	
USB-C	1x USB-C for laptop, 1x USB-C for smartphone; data rate up to 5Gbps
Downstream Port	
HDMI	1x HDMI 1.4b compliant, up to 4K UHD 3840 x 2160 @30Hz resolution (4K laptops); up to 1080p (smartphones and tablet sources)
USB-A	2x USB-A 3.1 Gen 1, data rate up to 5Gbps
USB-C	1x USB-C for Power Pass-Thru
Power	
Power Pass-Thru	Port 1 supports up to 75W at 5V/9V/15V/20V. Port 2 supports up to 10W (5V/2A)
Power Consumption	5V/3A (15W)
Operating System Requirements	
Mac	MacOS X 10.12+
Windows	Windows 10 (32/64 bit)+
Android	Android 8+
iOS	iPadOS 12.1+; iPad Pro 3rd generation (2018) for full HID keyboard and mouse support
Chrome OS	Chrome OS
Environment	
Humidity	0-80% RH, Non-condensing
Operation Temperature	32 - 104°F (0-40°C)
Storage Temperature	-4 - 140°F (-20-60°C)
<b>DIMENSIONS</b>	<b>GUD3C04</b>
POP Information	
10" Peg Hook	3
6" Peg Hook	2
Unit Dimensions	
Height	0.9" (2.29cm)
Length	5.75" (14.6cm)
Depth	4.75" (12.07cm)
Unit Package Dimensions	
Height	7.28" (18.5cm) + 1.5" (3.8cm) hanging tab
Width	6.1" (15.5cm)
Depth	2.16" (5.5cm)



<b>DIMENSIONS</b>	<b>GUD3C04</b>
Master Carton	
Height	7.87" (20cm)
Width	15.16" (38.5cm)
Depth	6.69" (17cm)
Master Carton Qty.	6
Weight	
Master Carton Wt.	8.9lb (4.05kg)
Unit Pack Wt.	1.4lb (0.64kg)
Unit Wt.	0.8lb (0.36kg)