

HP DesignJet T830 24-in Multifunction Printer (F9A28D)



**Communicate more effectively—no learning curve needed—
with print plus scan and copy capabilities**

Immediately update all your partners on project review results with the most compact large-format MFP.[2] Intuitive, convenient print/scan/copy and HP DesignJet print quality help you communicate effectively and move the project forward.



CONVENIENT—Fast, agile, intuitive print/scan/copy

Print documents fast—up to 26 seconds for A1/D-size prints.[1]

TRUSTED—HP DesignJet quality and reliability

Get HP DesignJet quality also in small-format sizes—print half-size documents with 50-sheet A4/A3 input tray.

COMMUNICATION—Immediately share meeting results

Use built-in scanner to copy and distribute sketches and hand-annotated drawings to peers/partners right away.

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print, copy, scan
Connectivity, standard	Gigabit Ethernet (1000Base-T), Wi-Fi 802.11b/g/n
Connectivity, optional	HP USB 3.0 to Gigabit LAN Adapter
Mobile printing capability	Wi-Fi Direct and local Wi-Fi connectivity to enable mobile printing via HP ePrint, Apple AirPrint™ and HP Smart App. Supports printing from most smartphones and tablets using these operating systems: Android, iOS
Software included	HP Click, HP Smart app, HP Support Assistant, HP Print Preview for Windows, HP DesignJet Utility for macOS and Windows
Sustainable impact specifications	Free, convenient HP ink cartridge and printhead recycling with HP Planet Partners; FSC®-certified papers and a range of recyclable HP media with a take-back program; ENERGY STAR® certified; EPEAT® registered
Energy star certified	Yes
Scan file format	JPEG, PDF, TIFF
Scan input modes	Scan to email, scan to cloud (through HP Smart app), network, USB, computer, mobile
Scanner type	Sheetfed, CIS (Contact Image Sensor), media jam detection sensor, front feed scanning method
Minimum dimensions (W x D x H)	1098 x 605 x 1155 mm
Minimum dimensions (W x D x H)	43.2 x 23.4 x 45.5 in
Weight	46.7 kg
Weight	103 lb
Power consumption	35 watts (printing), 3.5 watts (sleep), 0.2 watts (standby)
Environmental certification	ENERGY STAR, EPEAT, CE marking (including RoHS, WEEE, REACH). In compliance with WW RoHS materials restriction requirements in China, Korea, India, Vietnam, Turkey, Serbia, and Ukraine.
What's in the box	HP DesignJet T830 24-in MFP, printhead, ink cartridges, printer stand, spindle, quick reference guide, setup poster, startup software, power cord, refeed preventers
Manufacturer Warranty	One-year limited warranty. Warranty and support options vary by product, country and local legal requirements.

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Mechanical printing time, printed in Fast mode with Economode on, using HP Bright White Inkjet Paper (bond) and Original HP Bright Office Inks.

[2] The HP DesignJet T830 24-inch and 36-inch Multifunction Printers are the most compact large-format devices performing print/scan/copy functions based on H x W x L specifications published as of May, 2017.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

