

HP Pro mt440 G3 Mobile Thin Client (72L66AA)



Secure, stylish, and affordable cloud productivity.

Drive productivity and performance on-the-go with the 12th Gen Intel® Celeron® processor[2], long battery life with HP Fast Charge[8], WLAN[3], and essential ports in the HP Pro mt440 Mobile Thin Client. Confidently move through your day with a device built with aluminum materials for durability.



Business-class cloud productivity

Power through your day with the latest Intel® Celeron® processor[2] and a mix of modern and legacy ports.

Protect your data and device

Rest easy with a mobile thin client that helps keep your cloud computing experience safe with a self-healing BIOS.

Built to be seen, built to last

Get an eye-catching device that features a durable chassis built with aluminum materials that can withstand daily wear and tear.

Specifications

Operating System Software	Windows 10 IoT Enterprise
Processor Family	Intel® Celeron® processor
Processor Name	Intel® Celeron® 7305 (1.1 GHz base frequency, 8 MB L3 cache, 5 cores, 5 threads)
Chipset	SoC
Standard Memory Description 01	8 GB DDR4-3200 MT/s (2 x 4 GB)
Memory Slots	2 SODIMM
Hard Drive Description (01)	256 GB PCIe® NVMe™ M.2 SSD
Hard Drive Description (02)	256 GB PCIe® NVMe™ SSD
Graphics Card Segment 01	Integrated
GScardseg 01 Available Card 01	Intel® UHD Graphics
Display Description (metric)	35.6 cm (14") diagonal, FHD (1920 x 1080), IPS, narrow bezel, anti-glare, 250 nits, 45% NTSC
Display Description	14" diagonal, FHD (1920 x 1080), IPS, narrow bezel, anti-glare, 250 nits, 45% NTSC ^[17,20,21,22]
Audio Features	Dual stereo speakers, dual array microphones
Product Dimensions (metric)	32.19 x 21.39 x 1.99 cm
Product Dimensions (imperial)	12.67 x 8.42 x 0.78 in
Weight (metric)	Starting at 1.48 kg (Weight will vary by configuration.)
Weight (imperial)	Starting at 3.26 lb (Weight will vary by configuration.)
Keyboard	HP Premium Keyboard – spill-resistant, backlit keyboard with drain
Pointing Device	Clickpad with multi-touch gesture support, taps enabled as default
Integrated Camera	720p HD camera
External I/O Ports	1 AC power; 1 headphone/microphone combo; 1 RJ-45; 1 SuperSpeed USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1); 1 HDMI 2.1b; 3 SuperSpeed USB Type-A 5Gbps signaling rate (1 charging, 1 USB Power Delivery) (HDMI cable sold separately.)
Network Interface	Realtek RTL8111HSH-CG GbE
Wireless Technologies	Realtek Wi-Fi 6 RTL8852BE (2x2) and Bluetooth® 5.3 wireless card
Protocols supported (long)	Citrix® ICA/HDX; Microsoft RFX/RDP; VMware Horizon® View™ through RDP/PCoIP, and Blast Extreme (Protocols are dependent on operating system installed.); Azure Virtual Desktop add-on; Microsoft 365
Power Supply Required	HP Smart 65 W EM External AC power adapter ^[27]
Battery Type	HP Long Life 3-cell, 42 Wh Li-ion
Manageability Features	HP ThinUpdate; HP Cloud Endpoint Manager; HP Write Filter; Windows Defender; HP BIOS Configuration Utility; HP Device Manager ^[19]
Sustainable Impact Specifications	Low Halogen
Security Management	USB enable/disable (via BIOS); Power-on password (via BIOS); Setup password (via BIOS); Support for chassis padlocks and cable lock devices; HP Secure Erase; BIOS Update via Network; HP BIOSphere Gen6; HP Sure Start Gen7; HP Tamper Lock; HP DriveLock and Automatic DriveLock ^[23,24,34]
Software Included	HP Connection Optimizer; HP Hotkey Support
Browser Supported Description	Mozilla Firefox; Microsoft Edge ^[35,36]
UPC Number	(A2M) 197029032935; (A2N) 197029033055; (AB0) 197029033208; (AB1) 197029033178; (AB2) 197029033130; (AB4) 197029033185; (AB5) 197029033147; (AB6) 197029032973; (AB7) 197029032966; (AB8) 197029033086; (AB9) 197029033017; (ABA) 197029032775; (ABB) 197029032911; (ABD) 197029032928; (ABE) 197029033062; (ABF) 197029032904; (ABG) 197029033116; (ABH) 197029032997; (ABJ) 4573595824222; (ABL) 197029032799; (ABM) 197029032805; (ABT) 197029032959; (ABU) 197029033093; (ABV) 197029032867; (ABZ) 197029032980; (AC8) 197029032782; (ACB) 197029033031; (ACF) 4573595824215; (ACH) 197029032812; (ACJ) 197029033161; (ACQ) 197029033048; (AKC) 197029032942; (AKD) 197029033000; (AKL) 197029033192; (AKQ) 197029033024; (AKS) 197029032874; (AR6) 197029033154; (B10) 197029032850; (B1L) 197029033109; (BCM) 197029032898; (BED) 197029032836; (BH4) 197029032843; (BH5) 197029032829; (UUF) 197029033123; (UUG) 197029032881; (UUZ) 197029033079

Top Recommended Displays, Accessories and Services

Wired Headset

Poly EncorePro 525 USB-A Stereo Headset	783R3AA
Poly EncorePro 320 Stereo USB-A Headset TAA	767G0AA

Messaging Footnotes

[2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited.

[8] Recharges your battery up to 50% within 30 minutes when the system is off or in standby mode. Power adapter with a minimum capacity of 65 watts is required. After charging has reached 50% capacity, charging will return to normal. Charging time may vary +/-10% due to System tolerance.

Technical Specifications Footnotes

[17] FHD/HD content required to view FHD/HD images.

[19] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[21] Actual brightness will be lower with touchscreen or Sure View.

[22] Touchscreen not available with ThinPro.

[23] HP BIOSphere Gen6 features may vary depending on the platform and configuration.

[24] HP Sure Start Gen7 is available on select HP PCs and requires Windows 10 and higher.

[27] Availability may vary by country.

[34] HP Tamper Lock is an optional feature that must be configured at the factory and requires a supervisor password be established prior to use.

[35] Microsoft Edge available for Windows only.

[36] Firefox available for ThinPro only.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Celeron, and XMM are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

