

## HP SD Pro 2 44-in Scanner (5EK01A)



**Boost production with accurate color scanning—crisp lines and fine detail—delivered in high speed**

Empower production workflows with the high-speed, high-quality HP SD Pro 2 44-in Scanner. Produce scans with crisp lines and fine detail with CIS technology. Enhanced features enable workflow efficiencies that speed up collaboration and outcomes.



**ACCELERATE—Speed up production and drive results**

Accomplish more with incredible speeds—scan 9 inches/sec (22.8 cm/sec) in color, 18 inches/sec (45.7 cm/sec) in grayscale.[1]

**EXPAND—Do more with advanced scanning technology**

Reproduce AEC/CAD drawings, blueprints, maps with crisp lines and fine detail using CIS scanning technology.

**OPTIMIZE—Integrate and secure your workflow**

Enjoy seamless integration with HP PageWide XL and HP DesignJet printers—rely on HP to support the solution.

Specifications

Functions	Copy, scan
Connectivity, standard	Gigabit Ethernet (1000Base-T), USB 3.1 gen 1 (3+1) and USB 2.0 (1) rear
Compatibility	HP DesignJet T600 Printer Series; HP DesignJet T790 Printer series; HP DesignJet T795 Printer; HP DesignJet T920 Printer series; HP DesignJet T930 Printer series; HP DesignJet T940 Printer; HP DesignJet T1300 PostScript® Printer; HP DesignJet T1500 Printer series; HP DesignJet T1530 Printer series; HP DesignJet T1600 Printer; HP DesignJet T1700 Printer series; HP DesignJet T2500 Multifunction Printer series; HP DesignJet T2530 Multifunction Printer series; HP DesignJet T2600 Multifunction Printer series; HP DesignJet T3500 Production Multifunction Printer; HP DesignJet XL 3600 Multifunction Printer; HP PageWide XL 39x0, 4x00, 5x00, 6x00, 8x00 Printers; HP DesignJet Z6/Z9+ PostScript® Printer series; HP DesignJet Z6/Z9+ Pro Printer series; HP DesignJet Z5200 Photo Printer; HP DesignJet Z5400 PostScript® Printer; HP DesignJet Z5600 PostScript® Printer; HP DesignJet Z6610 Production Printer; HP DesignJet Z6810 Production Printer series
Energy star certified	Yes
Scan file format	PDF, PDF/A, TIFF, JPEG, JPEG2000, DWF, multi-page PDF generation
Scan input modes	File, email, USB, HDD, network folder, FTP, print
Scanner type	CIS scanning technology
Minimum dimensions (W x D x H)	1530 x 930 x 1660 mm
Minimum dimensions (W x D x H)	60 x 37 x 65 in
Weight	60 kg
Weight	132 lb
Power consumption	47 W (scanning), 32 W (ready), 1.8 W (sleep)
Environmental certification	ENERGY STAR, WEEE, RoHS (EU, China, Korea, India), REACH, EPEAT
What's in the box	HP SD Pro 2 44-in Scanner, stand, touchscreen (panel PC), quick reference guide, media guides, setup poster, maintenance sheet, copy/scan software, documentation software, Ethernet cable, USB cable, power cords
Manufacturer Warranty	One-year limited hardware warranty

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Grayscale scanning: A1/D image with black text graphics at 200 dpi; color scanning: A1/D fully-inked color image at 200 dpi, 24-bit RGB.

## Technical Specifications Footnotes

No Technical Specifications Footnotes

---

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

