

# HP Color LaserJet Pro 4201dw Printer (4RA86F)



## Fast color printing and easy set up.

Get a blazing fast color printer and easy set up with LaserJet Pro.



### Maximum productivity in full color

Support your business workteam with this compact, high-performing, color printer, ideal for up to 10 users.

### Simple set up.

Quickly set up your printers so you can focus more on your business.

### Advance your security with HP Wolf Pro

Get printer fleet security out of the box. Preconfigured settings mean it's ready when you are.

## Featuring

Business team solution

Blazing fast speed

Self-healing Wi-Fi® [7] [7]

True-to-life colors [14] [14]

HP Web Jetadmin. [3] [3]

## Specifications

<b>Print Resolution Technologies</b>	HP ImageREt 2400, PANTONE® calibrated
<b>Print quality black (best)</b>	Up to 600 x 600 dpi; Up to 38,400 x 600 enhanced dpi
<b>Print quality color (best)</b>	Up to 600 x 600 dpi
<b>Print speed black (ISO, A4)</b>	Up to 33 ppm
<b>Print speed black (ISO, letter)</b>	Up to 35 ppm
<b>Print Speed Color (ISO)</b>	Up to 33 ppm
<b>Print speed color (ISO)</b>	Up to 35 ppm
<b>Print speed</b>	Print speed up to 35/33 ppm black & color (Letter/A4)
<b>Functions</b>	Print
<b>Duplex printing</b>	Automatic
<b>Duty cycle (monthly, A4)</b>	Up to 50,000 pages
<b>Duty cycle (monthly, letter)</b>	Up to 50,000 pages
<b>Printer smart software features</b>	Automatic duplex, collation, watermarks, printable forms, quiet mode, HP premium print quality mode, accepts a variety of paper sizes and types
<b>Energy savings feature technology</b>	HP Auto-On/Auto-Off Technology; Instant-on Technology
<b>Replacement cartridges</b>	HP 210A Black Original LaserJet Toner Cartridge (~2,000 pages) W2100A; HP 210A Cyan Original LaserJet Toner Cartridge (~1,800 pages) W2101A; HP 210A Yellow Original LaserJet Toner Cartridge (~1,800 pages) W2102A; HP 210A Magenta Original LaserJet Toner Cartridge (~1,800 pages) W2103A; HP 210X Black Original LaserJet Toner Cartridge (~7,500 pages) W2100X; HP 210X Cyan Original LaserJet Toner Cartridge (~5,500 pages) W2101X; HP 210X Yellow Original LaserJet Toner Cartridge (~5,500 pages) W2102X; HP 210X Magenta Original LaserJet Toner Cartridge (~5,500 pages) W2103X <sup>[2]</sup>
<b>Supplies feature</b>	TerraJet Cartridge
<b>Connectivity, standard</b>	1 Gigabit Ethernet 10/100/1000 Base-TX network; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11n; 1 Wi-Fi 802.3az; 1 Wi-Fi Direct; Walk-up USB; Auto-crossover Ethernet
<b>Network capabilities</b>	Yes, via built-in 10/100/1000Base-Tx Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1x; 802.11ac (Wi-Fi 5)
<b>Wireless capability</b>	Yes, built-in dual-band Wi-Fi (Wi-Fi 5); Authentication via WEP, WPA/WPA2/WPA3, WPA Enterprise; Encryption via AES or TKIP; WPS; Wi-Fi Direct
<b>Mobile printing capability</b>	HP Smart App; Apple AirPrint™; Mobile Apps; Mopria™ Certified; Wireless Direct Printing
<b>Network protocols, supported</b>	TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, Apple AirPrint™, Mopria, IPP Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Stateful via DHCPv6), SSL Security and Certificate management; Management: SNMPv1, SNMPv2, SNMPv3, HTTP/HTTPS, Syslog
<b>Software included</b>	No software solutions are included in the Box only on <a href="http://hp.com">http://hp.com</a> or <a href="http://123.hp.com">http://123.hp.com</a>
<b>Compatible Operating Systems</b>	Windows 11; Windows 10; Windows Client OS; Android; iOS; Mobile OS; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; Linux; Citrix; Chrome OS (Citrix Ready Kit Certification - Up to Citrix Server 7.18 for more information see <a href="http://citrixready.citrix.com">http://citrixready.citrix.com</a> ; Citrix Server 6.5; Citrix XenApp & XenDesktop 7.6; Linux- For more information see <a href="http://developers.hp.com/hp-linux imaging-and-printing">http://developers.hp.com/hp-linux imaging-and-printing</a> ; Novell iPrint server; Unix- For more information see <a href="http://hp.com/go/unixmodelscripts">http://hp.com/go/unixmodelscripts</a> ; Windows Server 2008 R2 64-bit ; Windows Server 2012 64-bit; Windows Server 2012 R2 64-bit; Windows Server 2016 64-bit; Windows Server 2019 64-bit; Windows Server 2022 64-bit; (All operating systems with the latest updates); Android; iOS; macOS Big Sur v11.0; macOS Catalina v10.15; macOS Monterey v12.0; macOS's-; Mobile OS's-; Win10; Win11; Windows Client OS (32/64 bit)-; (All operating systems with the latest updates))
<b>Technical features</b>	Automatic 2-sided printing; Cloud-based fleet management; Compact size; Made with recycled plastic; ENERGY STAR®; Network printing; HP Auto-on/Auto-off; TerraJet Toner; Private Print via PIN; Professional print quality; Walk-up USB; WiFi Direct
<b>Sustainable impact specifications</b>	ENERGY STAR® certified; EPEAT® registered; Contains post-consumer recycled plastic
<b>Energy star certified</b>	Yes
<b>Ecolabels</b>	IT ECO Declaration; EPEAT® Silver Australia; EPEAT® Silver Canada; EPEAT® Silver US; ENERGY STAR® certified
<b>Blue Angel compliant</b>	No, please refer to the ECI (Ecolabel Comparison Information) document
<b>Faxing</b>	No
<b>Display area (imperial)</b>	2.0 x 1.3 inch
<b>Display area (metric)</b>	51.6(W) X 30.1(H) mm

<b>Display</b>	4-line back lit LCD
<b>Minimum dimensions (W x D x H)</b>	421 x 427 x 288 mm
<b>Minimum dimensions (W x D x H)</b>	16.6 x 16.8 x 11.3 in
<b>Weight</b>	~16.33 kg
<b>Weight</b>	~36 lb
<b>Power consumption</b>	580 watts (active printing), 17 watts (ready), 0.7 watts (sleep), 0.7watts (HP auto-off/auto-on), 0.07 watts (auto-off/manual-on), 0.07 watts (off) <sup>[5]</sup> <i>([5] Values based on 115V test results based on Energy Star test method.)</i>
<b>Power supply type</b>	Internal (built-in) Power Supply
<b>What's in the box</b>	HP Color LaserJet Pro 4201dw; 4 preinstalled introductory HP LaserJet Toner Cartridges (Black: ~1,200 pages; Cyan, Magenta, Yellow: ~1,000 pages); In-box documentation (Reference guide; Setup Card; Regulatory flyer); HP printer software is available at <a href="http://www.hp.com/support">www.hp.com/support</a> ; Power cord; USB cable. <sup>[1]</sup>
<b>Manufacturer Warranty</b>	One-year Bench/Depot Repair warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to <a href="http://hp.com/support">hp.com/support</a> to learn about HP award winning service and support options in your region. (wty code 4E; wty ID A033)

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[3] HP Web Jetadmin is available for download at no additional charge at [hp.com/go/webjetadmin](http://hp.com/go/webjetadmin).

[14] Standard print mode for HP Color LaserJet Pro series with HP TerraJet technology compared to predecessors. See [hp.com/TerraJet/colors](http://hp.com/TerraJet/colors).

## Technical Specifications Footnotes

[1] For yield information on the cartridge(s) included with your printer, see <http://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[2] Declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/toneryield>

[5] Values based on 115V test results based on Energy Star test method.

---

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

