

HP Color LaserJet Enterprise Flow MFP 6800zf Printer (6QN36A)



Powerfully productive. Extraordinarily efficient.

Transform your workflows with advanced capabilities in a compact footprint. Customizable configurations from print speeds to color panels[10] help to meet the needs of busy workgroups. All while protecting your business against evolving security threats. Please note: floor-standing finisher (632P1A) must be ordered together with the printer.



Customizable and scalable solutions [8]

Get the functionality you need with unprecedented, flexible configurations built to order. Optimize your device to meet your business needs and your budget.

Fast and seamless digitization

Customize your print experience with cloud-connected HP Workpath apps. Access personalized content and integrate paper and digital workflows.[1]

Everything you expect from an office printer

Experience ultra-fast scanning speeds and ultimate productivity with HP Flow technology and up to 200 ipm[3] duplex scan technology

Specifications

Print Resolution Technologies	HP ImageREt 3600, Enhanced (600x600 dpi), Fine Lines (1200x1200 dpi), Quickview (300x300 dpi)
Print quality black (best)	Up to 1200 x 1200 dpi
Print quality color (best)	Up to 1200 x 1200 dpi
Print speed black (ISO, A4)	Up to 52 ppm
Print speed black (ISO, letter)	Up to 55 ppm
Print Speed Color (ISO)	Up to 52 ppm
Print speed color (ISO)	Up to 55 ppm
Print speed	Print speed up to 55 ppm (black) and 55 ppm (color)
Functions	Print, copy, scan, fax
Duplex printing	Automatic
Duty cycle (monthly, A4)	Up to 100,000 pages
Duty cycle (monthly, letter)	Up to 100,000 pages
Printer smart software features	Apple AirPrint™, Mopria-certified, Open Extensibility Platform, FutureSmart Firmware, Instant-on Technology, HP Auto-On/Auto-Off technology, Easy Access USB, Two-Sided Printing, Hardware Integration Pocket, Intuitive 10.1 in (25.6 cm) touchscreen control panel, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, print preview
Copier smart software features	Auto scale; Reduce/enlarge from scanner glass (25 to 400 percent); Collate; Auto color detection; Two-sided copying; Image adjustments (darkness, background cleanup, sharpness); Job build
Scanner advanced features	Optimize text/picture; Image adjustments; Job build; Output quality setting; Selectable scan resolution 75 to 600 dpi; Auto detect color; Edge Erase; Job notification; Blank page suppression; HP Quick Sets; HP EveryPage; Auto orientation; Embedded Optical Character Recognition (OCR), Auto crop to page; Auto-tone; Onscreen editing with highlighting, redaction and signature capabilities
Fax smart software features	Stored faxes; Fax archiving; Fax forwarding; Scale to fit; Fax address book; LAN/Internet fax; Fax number confirmation; Holiday fax schedule
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology; Instant-on Copy
Replacement cartridges	HP 213A Black Original LaserJet Toner Cartridge (~3,500 pages) W2130A; HP 213A Cyan Original LaserJet Toner Cartridge (~3,000 pages) W2131A; HP 213A Yellow Original LaserJet Toner Cartridge (~3,000 pages) W2132A; HP 213A Magenta Original LaserJet Toner Cartridge (~3,000 pages) W2133A; HP 213X High Yield Black Original LaserJet Toner Cartridge (~9,000 pages) W2130X; HP 213X High Yield Cyan Original LaserJet Toner Cartridge (~6,000 pages) W2131X; HP 213X High Yield Yellow Original LaserJet Toner Cartridge (~6,000 pages) W2132X; HP 213X High Yield Magenta Original LaserJet Toner Cartridge (~6,000 pages) W2133X; HP 213Y Extra High Yield Black Original LaserJet Toner Cartridge (~18,000 pages) W2130Y; HP 213Y Extra High Yield Cyan Original LaserJet Toner Cartridge (~12,000 pages) W2131Y; HP 213Y Extra High Yield Yellow Original LaserJet Toner Cartridge (~12,000 pages) W2132Y; HP 213Y Extra High Yield Magenta Original LaserJet Toner Cartridge (~12,000 pages) W2133Y; HP 217Z Ultra Yield Black Original LaserJet Toner Cartridge (~32,000 pages) W2170Z; HP 217Z Ultra Yield Cyan Original LaserJet Toner Cartridge (~24,000 pages) W2171Z; HP 217Z Ultra Yield Yellow Original LaserJet Toner Cartridge (~24,000 pages) W2172Z; HP 217Z Ultra Yield Magenta Original LaserJet Toner Cartridge (~24,000 pages) W2173Z ^[2]
Supplies feature	TerraJet Cartridge
Connectivity, standard	1 Fax; 1 Gigabit Ethernet 10/100/1000T network; 1 Hardware Integration Pocket 2nd generation (HIP2); 1 Hi-Speed USB 2.0 (host); 1 SuperSpeed USB 3.0 (device); 1 SuperSpeed USB 3.0 (host)
Connectivity, optional	HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A
Modem	33.6 kbps
Network capabilities	Yes, via HP Jetdirect Ethernet embedded print server which supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec; 802.11a/b/g/n wireless networking (optional).
Mobile printing capability	Apple AirPrint™; Mopria™ Certified; NFC Touch-to-print (optional)
Network protocols, supported	Via built-in networking solution: TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, IPP 2.0, Apple AirPrint™, Google Cloud Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual, TFTP Config, ARP-Ping), IPv6 (Stateless Link-Local and via Router, Statefull via DHCPv6); Management: SNMPv2/v3, HTTP/HTTPS, Telnet, TFTP Config, FTP FW Download, Syslog; Security: SNMPv3, SSL Cert Management, Firewall, ACL, 802.1x
Software included	No software solutions are included in the Box only on http://hp.com http://123.hp.com ;
Compatible Operating Systems	Windows 11; Windows 10; Windows Client OS; Android; iOS; Mobile OS; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; Linux; Citrix; Chrome OS (Citrix Ready Kit Certification - Up to Citrix Server 7.18 for more information see)

Technical features	Fax; Automatic document feeder; Automatic 2-sided printing; Bluetooth printing; Cloud-based fleet management; Color touchscreen with apps; ENERGY STAR®; Network printing; Fast first page out; Full ream of paper input; Google Cloud Print; HP Auto-on/Auto-off; TerraJet Toner; Private Print via PIN; Scan-to-cloud; Scan-to-email; Scan-to-folder; Touchscreen; Walk-up USB
Sustainable impact specifications	5% post-consumer recycled plastic; ENERGY STAR® certified; EPEAT® registered
Energy star certified	Yes
Ecolabels	CECP; IT ECO Declaration; Blue Angel; EPEAT® Gold registered; SEPA; KOECO; ENERGY STAR® certified
Blue Angel compliant	Yes, Blue Angel DE-UZ 219—only ensured when using Original HP supplies
Copy speed (black, normal quality, A4)	Up to 52 cpm
Copy speed (color, normal quality, A4)	Up to 52 cpm
Copy speed black (normal, letter)	Up to 55 cpm
Copy speed color (normal, letter)	Up to 55 cpm
Copy speed black duplex (A4)	Up to 52 ipm
Copy speed black duplex (Letter)	Up to 55 ipm
Digital sending standard features	Scan to Email; scan to network folder; scan to USB drive; scan to SharePoint; scan to FTP; scan to SFTP; scan to LAN fax; scan to Internet Fax; local address book; SMTP over SSL; automatically detect color/monochrome; high compression PDF; image adjustments (darkness, contrast, background cleanup, sharpness); optimize text/picture (text, mixed, printed picture, photograph); content orientation; scan mode (book, 2-sided ID); erase edges; auto page crop; job build; image preview; blank page suppression; automatically straighten; embedded OCR; optimize text/picture (auto); scan to multi-destination; automatic tone; auto orientation; multi-feed detection; reverse and retry; document editing; auto paper color removal; job separation (blank page, barcode); watermark; stamps
Fax Resolution Black (best)	Up to 300 x 300 dpi
Faxing	Yes
Scan speed (normal, A4)	Up to 95 ppm/190 ipm (b&w), up to 95 ppm/190 ipm (color)
Scan speed (normal, letter)	Up to 100 ppm/200 ipm (b&w), up to 100 ppm/200 ipm (color)
Scan file format	PDF; Hi-Compression PDF; PDF/A; JPEG; TIFF; MTIFF; XPS ^[1]
Scan input modes	Front panel applications: Copy; Fax; Scan to Email; Scan to Network Folder; Scan to USB; Scan to Job Storage; Open Extensibility Platform (OXP), HP Workpath applications
Scan technology	Charge Coupled Device (CCD) Flatbed; Contact Image Sensor (CIS) ADF
Scanner type	Flatbed ; ADF
Display area (imperial)	8.53 x 5.34 in
Display area (metric)	21.7 x 13.6 cm
Display	10.1 in (25.6 cm) Color Graphics Display (CGD) with touchscreen; rotating (adjustable angle) display
Minimum dimensions (W x D x H)	500 x 460 x 651 mm
Minimum dimensions (W x D x H)	19.7 x 18.1 x 25.6 in
Weight	~42.2 kg
Weight	~92.84 lb
Power consumption	717 watts (Printing/Copying), 63.4 watts (Ready), 1.1 watts (Sleep), 0.1 watts (Auto Off/Manual On), 0.1 watts (Manual Off) (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.)
Power supply type	Built in 110V or 220 V Power Supply (not dual voltage, power supply varies by part number with option code identifier)
What's in the box	HP Color LaserJet Multifunction Printer; HP Black Original LaserJet Toner Cartridge (~9,000 yield), HP Cyan, Magenta and Yellow Original LaserJet Toner Cartridges (~6,000 yield each) (toner cartridges installed); Documentation (Hardware Install Guide); Power cord; For 6800zfw+ and 6801zfw+, floor-standing finisher (632P1A) must be ordered together with the printer ^[1]
Manufacturer Warranty	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements. Go to http://hp.com/support to learn about HP award winning service and support options in your region.

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Not all MFPs may be compatible with Workpath apps. To enable HP Workpath, some devices may require optional accessory or firmware to be upgraded. Not all apps may be available in all locations. Subscription may be required. Personalized content and integration functions are applicable to supported HP Workpath apps only.

[3] Scan speeds measured from ADF. Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software. Measured using standards found at: http://standards.iso.org/ittf/PubliclyAvailableStandards/SC28_Test_Pages/

[8] To learn more about configure to order options, contact your HP or Partner Representative.

[10] This product comes with Atmosphere Blue (standard) panels. Panels in other colors (Constellation Yellow, Comet Red, Aurora Purple, Lunar Grey, Cosmic Green) are only available transactionally via HP Configure to Order, or contractually via Managed Print Services. Models offered in China have Lunar Grey (standard) instead of Atmosphere Blue. Please contact your HP or partner representative to learn more about customizable color panels.

Technical Specifications Footnotes

[1] For yield information on the cartridge(s) included with your printer, see <https://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[2] Declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <https://www.hp.com/go/toneryield>

[11] For Scan software, we support: Windows (JPG, RAW(BMP), PDF, TIFF, PNG, RTF) and Mac (JPG, JPG-2000, TIFF, PNG, PDF, Searchable PDF, RTF, TXT)

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

