


KOP55XHB2(-S)
KOP55XHB2(-S)A



All Weather Rated Display: IP66



Display's Operating
Temperature Range:
-31°F to 140°F
(-35°C to 60°C)

- Includes two Peerless-AV® 55" Xtreme™ High Bright Outdoor Displays to offer maximum flexibility
- All stainless steel and aluminum body combined with an outdoor rated paint finish to provide the ultimate in corrosion resistance
- Wind tested up to 135 mph
- Sleek yet rugged design protects the display, while also providing ample space for component storage
- Available in black or silver and with or without speakers to ensure your product needs are met
- KOP55XHB2(-S)A includes four 4 inch, 100 watt, waterproof speakers to ensure high-quality, undistorted audio output for outdoor usage

Dual-Sided Smart City Kiosk

INCLUDES (2) 55" XTREME™ HIGH BRIGHT OUTDOOR DISPLAYS

Upgrade your current signage with a brand new Peerless-AV® Dual-Sided Smart City Kiosk. This next generation Smart City Kiosk will allow you to replace dynamic, digital content quickly, easily, and remotely, drawing in more engagement than your previous static signage. By combining a sleek, modern aesthetic with an approachable and easy-to-use design, the Smart City Kiosk puts functionality at the forefront. A 10-point IR touch overlay can also be added, on one or both sides of the kiosk, for an interactive customer experience. Outdoor elements are no match for this kiosk because it is all-weather rated, highly durable, and built to last. Maintenance and installation are also simplified with no cranes or forklifts needed and secure rear doors that allow quick access to the display for maintenance purposes. The Smart City Kiosk comes packed with ample component storage and two 55" Xtreme™ High Bright Outdoor Displays with full HD1080p resolution. Even when placed in direct sunlight, you are guaranteed a bright and crisp picture when sharing digital signage content - Whether that is focused on travel, wayfinding, advertising, weather, entertainment, and more.



IP66 RATED DISPLAY

Fully sealed design prevents the ingress of foreign materials, such as water, dust, moisture and insects, from entering the display

OPTIONAL IR TOUCH OVERLAY

Create an interactive kiosk by adding the KIRP-XHB4-(HT)*, which can detect up to 10 touch points, whether finger, gloved hand or stylus, all in a convenient plug-and-play design

**This product uses TSI technology.*

IP55 RATED MEDIA CABINET

Provides a dedicated, spacious area for storing AV components, and the integrated fans provide active cooling



LOUVERED SIDE VENTS

Allow for display and component ventilation while keeping cords and other internals hidden from view for a clean install



KOP55XHB2(-S)A Includes (4) Speakers

Model Shown: KOP55XHB2

EXTENDED BASE COVER

Allows power and data to be run up through bottom center, while keeping conduit concealed, for a clean installation

RoHS



TAA
COMPLIANT

Please visit peerless-av.com/en-us/patents for patent information.

info@peerless-av.com

peerless-av.com

peerless-AV®
Driving Technology Through Innovation

Model Numbers

Smart City Kiosk Enclosure Warranty: 5 Years
Xtreme™ High Bright Outdoor Display Warranty: 2 Years

KOP55XHB2	Black Dual-Sided Smart City Kiosk, Includes (2) 55" Xtreme™ High Bright Outdoor Displays
KOP55XHB2-S	Silver Dual-Sided Smart City Kiosk, Includes (2) 55" Xtreme™ High Bright Outdoor Displays
KOP55XHB2-A	Black Dual-Sided Smart City Kiosk, Includes (2) 55" Xtreme™ High Bright Outdoor Displays and Speakers
KOP55XHB2-SA	Silver Dual-Sided Smart City Kiosk, Includes (2) 55" Xtreme™ High Bright Outdoor Displays and Speakers

Product Specifications

	DIMENSIONS (W x H x D)	PRODUCT WEIGHT	FINISH	AVAILABLE COLORS
KOP55XHB2(-S) KOP55XHB2(-S)A	35.38" x 84.13" x 14.75" (899 x 2137 x 375mm)	270lb (122kg) 314lb (142kg)	Smooth Powder Coat	KOP55XHB2, KOP55XHB2-A: Black KOP55XHB2-S, KOP55XHB2-SA: Silver


Package Specifications

	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
KOP55XHB2(-S) KOP55XHB2(-S)A	Skid 1 (Kiosk): 48.00" x 90.00" x 40.00" (1219 x 2286 x 1016mm) Skid 2 (Displays): 60.00" x 39.00" x 40.00" (1524 x 991 x 1016mm)	Skid 1 (Kiosk): KOP55XHB2(-S): 300lb (136kg) KOP55XHB2(-S)A: 350lb (159kg) Skid 2 (Displays): 271lb (123kg)	KOP55XHB2: 735029349259 KOP55XHB2-S: 735029349266 KOP55XHB2-A: 735029349273 KOP55XHB2-SA: 735029349280	KOP55XHB2(-S): Kiosk, Mounting Hardware, (2) Xtreme™ High Bright Outdoor Displays, and Instructions KOP55XHB2(-S)A: Kiosk, Mounting Hardware, (2) Xtreme™ High Bright Outdoor Displays, (4) Speakers, (2) Amps, and Instructions	1

Accessories

KIRP-XHB4:	IR Touch Overlay
KIRP-XHB4-HT:	IR Touch Overlay with Heater*
ACCK-KOPBASE-B2B:	Base Bolt Template for Dual-Sided SC Kiosk

* Heater option available for kiosks located in extended subzero climate where snow or ice accumulation on the screen could be a concern.



MODEL NO.	DIMENSION "A"	DIMENSION "B"	DIMENSION "C"	DIMENSION "D"	DIMENSION "E"	DIMENSION "F"
KOP55XHB2(-S)	35.38" (899mm)	84.13" (2137mm)	12.75" (324mm)	14.75" (375mm)	50.05" (1271mm)	29.38" (746mm)
KOP55XHB2(-S)A	35.38" (899mm)	84.13" (2137mm)	12.75" (324mm)	14.75" (375mm)	50.05" (1271mm)	29.38" (746mm)

Architect Specifications

The Dual-Sided Smart City Kiosk shall be a Peerless-AV® model KOP55XHB2(-S) and KOP55XHB2(-S)A and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor displays, kiosks, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV
2300 White Oak Circle
Aurora, IL 60502
USA

(800) 865-2112
(630) 375-5100

Peerless-AV EMEA
Unit 2 Curo Park
Frogmore, St. Albans
Hertfordshire, AL2 2DD
United Kingdom

+44 (0) 1923 200 100

Peerless-AV B.V.
Papendorpseweg 75
3528 BJ Utrecht
The Netherlands

+31 (0) 70 770 8037

Peerless-AV Latin America
Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo, N.L.,
México, 66062

+52 (81) 8384-8300

