



GCS1602CC

Access Pro+ 2-Port 4K USB-C Desktop KVM with DisplayPort output and USB peripheral (TAA)

Easily switch between two USB-C devices and control them with up to 4 USB-A peripherals and view content on one 4k monitor. IOGEAR's GCS1602CC USB-C KVM Switch requires no software and comes complete with a charging Power function, USB-C cables, and a 6-foot push-button remote switch.



Features

- Control and share 2 USB-C devices with DP Alt Mode from one keyboard, mouse, and a DisplayPort monitor.
- Resolution up to 4K UHD 3840 x 2160 @60Hz
- Two additional USB peripheral ports built in for more USB connectivity
- USB 3.2 Gen 1 compliant and up to 5 Gbps data transfer rates
- Support Power Pass through up to 100W charging on Port 1 with additional USB-C Power Supply (Sold separately)
- Plug-n-Play; no software or driver needed.
- Supports USB-C/Thunderbolt 4 host device with DP Alt Mode
- Supports DP 1.4 Alt Mode

Requirements

Console:

- DisplayPort monitor
- Standard 104-key wired USB keyboard
- Standard 3 button wired USB mouse

Computers:

- USB-C enabled computer with DP Alt Mode*

Operating Systems:

- Windows® 10, 11
- Mac OS X 10.12+
- iPadOS 13.1 or later
- Android 8+

Package Contents

- 1 x 2-Port USB-C KVM Switch
- 2 x USB-C to USB-C Cables
- 1 x Remote Port Selector
- 1 x Power Adapter
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GCS1602CC
Upstream Port	
USB-C	2x USB-C for Laptops; data rate up to 5Gbps
Downstream Port	
DisplayPort	1x DP 1.4 compliant, up to 4k60Hz
USB-A	4x USB-A 3.2 Gen 1, data rate up to 5Gbps
USB-C	1x USB-C for Power Pass-Thru
Power	
Power Pass-Thru	Port 1: Supports 100W USB-C laptop charging at 5V, 9V, 15V, and 20V output Port 2: Supports max. 5V, 3A output
Input Rating	DC12V, 3.3A
Operating System Requirements	
Mac	Mac OS® X 9.0+
Windows	Windows® 10, 11 (32-bit / 64-bit) with 7th-Gen Intel Core Processor or above
Android	Android 8+
iOS	iPadOS 13.1 or later
Environment	
Humidity	0-80% RH, Non-condensing
Operation Temperature	32 - 104°F (0-40°C)
Storage Temperature	-4 - 140°F (-20-60°C)
DIMENSIONS	GCS1602CC
Unit Package Dimensions	
Height	6.8 in. (17.3 cm)
Length	11.2 in (28.3 cm)
Width	2.5 in. (6.2 cm)
Master Carton	
Height	7.6 in. (19.4 cm)
Length	15.8 in. (40.2 cm)
Width	11.8 in. (30 cm)
Master Carton Qty.	6
Weight	
Master Carton Wt.	15.3 lb. (6.9 kg)
Unit Pack Wt.	2.3 lb. (1.02 kg)