

HP DesignJet T950 36-in Printer (2Y9H1G)



The world's most efficient A3-A1 printing experience to boost productivity[1]

Boost productivity with the world's most efficient A3-A1 experience.[1] Do it all—print multi-size CAD and renders with the integrated input/output tray. Save time with HP Click. And go beyond with this robust and compact plotter.



MOST EFFICIENT[1]—Save time, get through more jobs

Pick up your jobs quickly and simply—stacker holds up to 40 pages flat for easy collection.[2]

CONNECTED—Work securely from virtually anywhere

Save time with HP Click—print in fewer steps and avoid reprinting with print preview.

GO BEYOND—Meet office and environmental needs

Advance environmental goals—printer is made with at least 35% recycled plastics[4] and recyclable supplies[5].

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print
Connectivity, standard	Gigabit Ethernet (1000Base-T), no Wi-Fi module or capability
Software included	HP Click for Windows and macOS, HP app for Windows, macOS, Android, and iOS
Technical features	A3 input tray;Stacker;A3 sheet organizer;Auto-power on/off scheduler;Max. resolution 2400 x 2400 dpi;HP Wolf Pro Security;130/300 ml cartridges;HP Flex Tech Inks
Energy star certified	Yes
Minimum dimensions (W x D x H)	1407 x 720 x 967 mm
Minimum dimensions (W x D x H)	55.4 x 28.3 x 38.1 in
Weight	56 kg
Weight	123.5 lb
Power consumption	35 W (printing), <5.5 W (ready), <2.5 W (sleep), <0.2 W (standby). Auto-scheduled printer on/off usage.
Environmental certification	ENERGY STAR, EPEAT, UL ECOLOGO® certified inks, CE marking (including WEEE, RoHS, REACH, ErP). In compliance with applicable WW RoHS materials restriction requirements.
What's in the box	HP DesignJet T950 Printer, printhead, introductory ink cartridges, printer stand, spindle, guide, warranty flyer, power cord

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] The HP DesignJet T950 is faster than its main competitors: 44% faster than competitor A and 43% faster than competitor B in end-to-end performance, including job preparation with printing software, processing, printing, and collection. Testing performed by Sogeti, April 2023. Detailed test report is available upon request.

[2] Based on test results using A1 size, plain paper, and standard configuration. Stacking capacity is subject to paper type, printed file and ambient conditions.

[4] Declared %RCP content is based on the quantity and weight of parts made with RCP resin over the total plastic parts.

[5] Program availability varies. See <https://www.hp.com/go/recycle>

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

