

# Product data sheet

Specifications



APC Smart-UPS Modular Ultra On-Line, 10kW scalable to 15kW, Lithium-ion, Tower 24U, 208/240V, Network Management, W/ External battery chassis

SRYL10K15XLT24

## Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

## Main

|                                  |                                                          |
|----------------------------------|----------------------------------------------------------|
| Main Input Voltage               | 208 V AC 1 phase<br>120 V AC 1 phase<br>240 V AC 1 phase |
| Other Input Voltages             | 240 V                                                    |
| Maximum Input Current per Phase  | 51 A                                                     |
| Load power factor                | 0.5 leading to 0.5 lagging                               |
| Number of input connectors       | 1 Hard Wire 4-wire (2PH+N+G)                             |
| Input Frequency                  | 40 - 70 Hz                                               |
| Output voltage                   | 120 V AC 1 phase<br>208 V AC 1 phase<br>240 V AC 1 phase |
| Other Output Voltages            | 240 V                                                    |
| Rated power in W                 | 10000 W                                                  |
| rated power in VA                | 10000 VA                                                 |
| Bypass type                      | Built-in Bypass                                          |
| Maximum configurable power in VA | 10000 VA                                                 |
| Max Configurable Power (Watts)   | 10000 W                                                  |
| Overload Operation               | 60 seconds @ 125% and 30 seconds @ 150%                  |
| Topology                         | On-Line                                                  |
| Waveform Type                    | Sine wave                                                |

## Complementary

|                                      |                                                                                           |
|--------------------------------------|-------------------------------------------------------------------------------------------|
| Battery Size                         | Li-Ion (Lithium Ion) internal included                                                    |
| Control panel                        | Touch Screen LCD User Interface                                                           |
| Emergency Power Off (EPO)            | Yes                                                                                       |
| Pre-Installed SmartSlot&trade; Cards | Network management card                                                                   |
| UPS connectivity                     | Serial port<br>USB port<br>Available expansion slot<br>Embedded network management card 3 |
| Number of rack unit                  | 24U                                                                                       |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                  |                                    |
|----------------------------------|------------------------------------|
| color                            | Black and silver                   |
| Height                           | 47.2 in (1198 mm)                  |
| Width                            | 23.6 in (600 mm)                   |
| Depth                            | 35.4 in (900 mm)                   |
| Net Weight                       | 427.7 lb(US) (194 kg)              |
| Mounting Location                | Front                              |
| Mounting mode                    | Tower                              |
| Number of power module           | 2                                  |
| Number preinstalled power module | 2                                  |
| Additional specification         | Network management card            |
| Range of Product                 | Smart-UPS Modular Ultra            |
| Product or Component Type        | Uninterruptible power supply (UPS) |

## Environment

|                                       |                              |
|---------------------------------------|------------------------------|
| Product Certifications                | ENERGY STAR V2.0 (USA)       |
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C)      |
| Ambient Air Temperature for Storage   | 5...113 °F (-15...45 °C)     |
| Storage altitude                      | 0...49212.6 ft (0...15000 m) |
| Storage Relative Humidity             | 0...95 %                     |
| Acoustic level                        | 68 dB                        |
| Operating altitude                    | 0...9842.52 ft (0...3000 m)  |

## Batteries & Runtime

|                          |                                                                                                                           |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Run Time                 | <a href="#">View Runtime Graph</a>     |
| Efficiency               | <a href="#">View Efficiency Graph</a>  |
| Battery Type             | Li-Ion (Lithium Ion)                                                                                                      |
| Extendable Run Time      | 0                                                                                                                         |
| Included Battery Modules | 2                                                                                                                         |
| RBC Quantity             | 2                                                                                                                         |
| Battery design life      | 8...10 year(s)                                                                                                            |

## Ordering and shipping details

|      |              |
|------|--------------|
| GTIN | 731304622116 |
|------|--------------|

## Packing Units

|                        |                           |
|------------------------|---------------------------|
| Unit Type of Package 1 | PCE                       |
| Nbr. of units in pkg.  | 1                         |
| Package 1 Height       | 52.05 in (132.2 cm)       |
| Package 1 Width        | 29.4 in (74.6 cm)         |
| Package 1 Length       | 39.2 in (99.5 cm)         |
| Package weight(Lbs)    | 476.99 lb(US) (216.36 kg) |

# Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 60 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

|                                                        |                                               |
|--------------------------------------------------------|-----------------------------------------------|
| Total lifecycle Carbon footprint                       | 35 464 kg CO2 eq.                             |
| Carbon footprint of the manufacturing phase [A1 to A3] | 8 684 kg CO2 eq.                              |
| Carbon footprint of the distribution phase [A4]        | 114 kg CO2 eq.                                |
| Carbon footprint of the installation phase [A5]        | 81 kg CO2 eq.                                 |
| Carbon footprint of the use phase [B2, B3, B4, B6]     | 26 135 kg CO2 eq.                             |
| Carbon footprint of the end-of-life phase [C1 to C4]   | 451 kg CO2 eq.                                |
| Environmental Disclosure                               | <a href="#">Product Environmental Profile</a> |

## Use Better



### Materials and Substances

|                                        |                                                                                        |
|----------------------------------------|----------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                    |
| Packaging without single use plastic   | No                                                                                     |
| SCIP Number                            | 31346aed-552c-4a16-81d9-e683a383b6da                                                   |
| EU RoHS Directive                      | <a href="#">Compliant By Exemption</a>                                                 |
| REACH Regulation                       | <a href="#">Reference contains Substances of Very High Concern above the threshold</a> |



### Energy efficiency

|                             |                            |
|-----------------------------|----------------------------|
| Optimized Energy Efficiency | Energy efficient product   |
| ENERGY STAR®                | ENERGY STAR UPS V2.0 (USA) |

## Use Longer



### Lifetime extension

|        |    |
|--------|----|
| Repair | No |
|--------|----|

## Use Again



### Repack and remanufacture

|                               |                                         |
|-------------------------------|-----------------------------------------|
| Recyclability potential, in % | 61                                      |
| Circularity Profile           | <a href="#">End of Life Information</a> |
| Removable battery             | User replaceable                        |
| Take-back                     | Yes                                     |

Image of product / Alternate images

Alternative

---

