

HP OfficeJet Pro 9125e All-in-One Printer (403X0A)



Print for your business like a Pro.

Say hello to the professional color inkjet printer for your growing business from the World's #1 Printer Company, paired with the easiest-to-use print app. From budgets to reports, enjoy easy cloud sharing and printing across multiple devices.[1,2]



Empower your team with a productivity powerhouse

Always ready for high volumes, get an HP OfficeJet Pro printer equipped with a 250-page input tray.

Our best technology to stay connected and secure[3]

Stay connected with our most reliable Wi-Fi® - dual-band, self-healing - that automatically reconnects.[3]

Always be ready to print. Never run out of ink.[8]

With an Instant Ink subscription, you can get ink delivered directly to your door before you run out.[8]

Specifications

Print Resolution Technologies	HP Thermal Inkjet
Print quality black (best)	1200 x 1200 rendered dpi
Print quality color (best)	Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
Print speed black (ISO, A4)	Up to 22 ppm
Print speed black (ISO, letter)	Up to 22 ppm
Print Speed Color (ISO)	Up to 18 ppm
Print speed color (ISO)	Up to 18 ppm
Print speed	Print speed up to 22 ppm (black) and 18 ppm (color)
Functions	Print, copy, scan, fax
Duplex printing	Automatic
Duty cycle (monthly, A4)	Up to 25,000 pages
Duty cycle (monthly, letter)	Up to 25,000 pages ^[7]
Printer smart software features	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On;
Copier smart software features	Two-Sided; Lighter/Darker; ID Copy; Resize; Quality; Paper Size; Paper Type; Collate; Margin Shift; Crop; Copy Preview; Enhancements
Scanner advanced features	OCR (Optical Character Recognition); Smart Tasks shortcuts: 1-click customizable scan to cloud destinations, email, and print, create editable, searchable documents by scanning from phone or printer; Smart Tasks destinations: Dropbox, Google Drive, One drive, email recipients
Fax smart software features	Digital Fax - Fax to PC is available with Windows (Please use: Visit http://www.hp.com/support to download the latest software.
Energy savings feature technology	Schedule On and Schedule Off
Replacement cartridges	HP 936 Black Original Ink Cartridge (~1,250 pages) 4S6V2LN; HP 936 Cyan Original Ink Cartridge (~800 pages) 4S6U9LN; HP 936 Magenta Original Ink Cartridge (~800 pages) 4S6V0LN; HP 936 Yellow Original Ink Cartridge (~800 pages) 4S6V1LN. HP EvoMore planned to be available April 2024: HP 936e EvoMore Black Original Ink Cartridge (~2,500 pages) 4S6V6LN; HP 936e EvoMore Cyan Original Ink Cartridge (~1,650 pages) 4S6V3LN; HP 936e EvoMore Magenta Original Ink Cartridge (~1,650 pages) 4S6V4LN; HP 936e EvoMore Yellow Original Ink Cartridge (~1,650 pages) 4S6V5LN. Actual yield varies considerably based on content of printed pages and other factors. For details, see https://www.hp.com/go/learnaboutsupplies
Supplies feature	HP Instant Ink eligible
Connectivity, standard	1 Ethernet; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11 a/b/g/n/ac (dual band); 2 RJ-11 Fax/Modem port/phone line
Modem	Synaptics Troy modem; data rate up to 33.6 kbps
Network capabilities	Yes, via built-in Ethernet; Wireless 802.11 a/b/g/n/ac
Wireless capability	Yes, with built-in dual-band Wi-Fi 802.11 a/b/g/n/ac and a self-heal solution
Mobile printing capability	Chrome OS; HP Smart app; Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified
Network protocols, supported	Supported Network Protocols configurations (IPv4, IPv6); DHCPv4, DHCPv6; DHCP options: 81/RFC4702/RFC4704, 12-Hostname; 44; SMTP client; LLMNR; Bonjour/mDNS; LP/ APIPA (Auto IP); NetBIOS/WINS; LPR/LPD; Port9100; DNS Resolver; SNMPv1/v2; Web Services Discovery; Web Services Print; Syslog; Firewall; SSL/TLS (HTTPS); Password-protected network Embedded Web server; Enable/disable network ports & device features, 802.1x wireless authentication (EAP-TLS, LEAP, and PEAP) & 802.1 Wired
Software included	HP Printer Software
Compatible Operating Systems	Windows 11; Windows 10; Windows Server; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; Linux; Chrome OS (Value is confirmed Windows Server 2016 64-bit, Windows Server 2019 64-bit, Windows Server 2022 64-bit, linux (for more information see http://developers.hp.com/hp-linux-imaging-and-printing))
Technical features	Borderless Printing; ADF; Touchscreen; AirPrint; Wireless Direct; Wireless; Automatic two-sided printing; HP Printables; Self-healing WiFi
Sustainable impact specifications	Forest First product with HP+; Recyclable through HP Planet Partners
Energy star certified	Yes

Ecolabels	IT ECO Declaration; EPEAT® registered
Copy speed black (best, A4)	Up to 5 cpm
Copy speed black (best, letter)	Up to 5 cpm
Copy speed color (best, A4)	Up to 4 cpm
Copy speed color (best, letter)	Up to 4 cpm
Digital sending standard features	Scan-to E-mail; Scan to network folder; scan to SharePoint; Scan to thumb drive
Fax Resolution Black (best)	300 x 300 dpi
Faxing	Yes, color
Scan speed (normal, A4)	Up to 8 ipm (200 ppi, b&w); Up to 8 ipm (200 ppi, color)
Scan speed (normal, letter)	Up to 8 ipm (200 ppi, b&w); Up to 8 ipm (200 ppi, color)
Scan file format	JPG, BMP, TIFF, PDF, RTF, TXT, PNG
Scan input modes	Front-panel scan, copy, HP Software, EWS, Mobile apps
Scan technology	Contact Image Sensor (CIS)
Scanner type	Easy slide-off glass, dual pass 2-sided ADF
Display	2.7" (6.86 cm) Capacitive Touchscreen CGD
Minimum dimensions (W x D x H)	439.3 x 342.5 x 278 mm (Minimum Storage Mode) (Dimensions vary as per configuration)
Minimum dimensions (W x D x H)	17.3 x 13.48 x 10.94 in (Minimum Storage Mode)
Weight	~ 9.29 kg (Weight varies as per configuration)
Weight	~ 20.48 lb (Weight varies as per configuration)
Power consumption	5.06 watts (ready), 1.22 watts (sleep), 0.14 watts (manual-off) ^[3] (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.)
Power supply type	Internal (Built-in) Universal Power Supply
What's in the box	NA: HP OfficeJet Pro 9120 AiO Printer; HP 936 Setup Black Ink Cartridge; HP 936 Setup Cyan Ink Cartridge; HP 936 Setup Magenta Ink Cartridge; HP 936 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see http://www.hp.com/go/learnaboutsupplies] EMEA/APJ DM: HP OfficeJet Pro 9120 AiO Printer; HP 937 Setup Black Ink Cartridge; HP 937 Setup Cyan Ink Cartridge; HP 937 Setup Magenta Ink Cartridge; HP 937 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see http://www.hp.com/go/learnaboutsupplies] LAR/ APJ EM: HP OfficeJet Pro 9120 AiO Printer; HP 938 Setup Black Ink Cartridge; HP 938 Setup Cyan Ink Cartridge; HP 938 Setup Magenta Ink Cartridge; HP 938 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see http://www.hp.com/go/learnaboutsupplies]
Manufacturer Warranty	One-Year limited hardware warranty with option to extend to two-years with acceptance of HP+ Offer. For more information, please visit us at http://support.hp.com [8]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Based on 2022 Q4 shipments in the IDC Worldwide Quarterly Hardcopy Peripherals Tracker®, 2022 Q4 Release. Includes shipments of all printing devices (inkjet printers, laser printers, copiers and multifunction devices, including production units).

[2] Compared to OEM printing apps for the majority of top-selling, network-capable inkjet/laser printers and all-in-ones for the home and office, priced ≤\$450 USD. Printers selected by market share as reported by IDC Quarterly Hardcopy Peripherals Tracker – Final Historical CYQ1 2023. Claim based on research of printer manufacturer's print apps and Keypoint Intelligence hands-on testing and study commissioned by HP, July 2023. For details, please see: keypointintelligence.com/HPSmartapp. Requires HP app download available at www.hp.com/go/mobileprinting. Certain features are available in English language only, and may vary by printer model/country, and between desktop/mobile applications. HP reserves the right to introduce charges for use of functionality facilitated by the HP app. Internet access required and may not be available in all countries. HP account required for full functionality. Fax capabilities are for sending a fax only. List of supported operating systems available in app stores. See details at www.hpsmart.com.

[3] HP OfficeJet Pro 9100 printer series has self-healing Wi-Fi and HP Wolf Pro Security, HP's best and most reliable technologies to stay connected and secure. Internet access required and must be purchased separately. Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at www.hp.com/go/mobileprinting. HP Security is now HP Wolf Security. Security features vary by platform, please see product data sheet for details.

[8] Based on plan usage, Internet connection to eligible HP printer, valid payment method, email address, and delivery service in your geographic area.

Technical Specifications Footnotes

[3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.

[7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

