

AMULET HOTKEY



DX1600™ Next Generation Thin Client

The DX1600™ Thin Client is a secure solution for connecting users to a remote workstation or centralized host server.

The DX1600 provides a best-in-industry user experience, with:

- up to four UHD resolution displays;
- high-definition audio;
- USB-A/USB-C compatible;
- dual network ports, and;
- Stratodesk Linux-based NoTouch OS.

Sales

EMEA Sales

+44 (0)20 7960 2400
emeasales@amulethotkey.com

N America Sales

+1 (212) 269 9300
ussales@amulethotkey.com

APJ Sales

+61 409 930 884
apsales@amulethotkey.com

Support

www.amulethotkey.com/support

Specifications

Physical

Dimensions	230mm x 130mm x 42mm
Thermal Cooling Solution	Passive heat sink
Weight	1.41 kg
Mounting	VESA
Orientation	Flat or upright, suitable for confined spaces with limited airflow

Processor

Model	AMD Ryzen V1605B
Max Frequency	3.6GHz
Cores / Threads	4 Cores / 8 Threads

Memory

Specification	2x 4GB DDR4 (2400MTS)
Installation	Soldered down SODIMMS

Storage

Specification	32GB eMMC
Installation	Soldered down SSD

I/O Ports

Video	4x Display Port	Network	1x RJ45 and 1x SFP. Separate connections to the MB (no internal switch)
USB	2x USB 3.1 Type-A 2x USB 3.1 Type-C	Audio	1x Line In (microphone) 1x Line Out (Headphone) 1x Headset

Security

TPM	TPM 2.0
-----	---------

Power

Adaptor	12V DC inlet, proprietary locking connector.
---------	--

Environmental

Operating Temperature	0°C to +40°C (humidity 90%)
Storage Temperature	-20°C to +60°C (humidity 90%)

Operating System

	Stratodesk NTOS, IGEL OS, Win 10 IoT
--	--------------------------------------

Protocol

	PCoIP, Citrix, VMware Horizon, RDP
--	------------------------------------

Compliance Certificates and Agencies

Safety / EMC/ Other	UL, CE, RoHS, REACH, CCC, EAC, FSS, RCM, KCC, BIS, TUV, PSE, CoC V5 (Tier2), DOE VI
---------------------	---