

ProductSheet

HP OfficeJet Pro 9730e Wide Format All-in-One Printer (537P6B)



Print and scan in wide format like a Pro.

Say hello to the wide format professional color inkjet printer for your growing business from the World's #1 Printer Company, paired with the easiest-to-use print app. Print and scan up to A3 with extra performance features.[1,2]



Easily achieve vibrant, screen-accurate prints

Print true-to-screen with the world's first and only wide format printer with P3 for wider gamut vs. sRGB.[3]

Our best technology to stay connected and secure[4]

Stay connected with our most reliable Wi-Fi® - dual-band, self-healing - that automatically reconnects.[4]

Always be ready to print. Never run out of ink.[7]

With an Instant Ink subscription, you can get ink delivered directly to your door before you run out.[7]

Specifications

Print Resolution Technologies	HP Thermal Inkjet
Print Resolution Black (best)	Up to 1200 x 1200 rendered dpi
Print Resolution Color (best)	Up to 4800 by 1200 optimized dpi on HP Advance Photo Paper 1200 by 1200 dpi input
Print Speed Black (normal, A4)	Up to 22 ppm
Print Speed Black (normal, letter)	Up to 22 ppm
Print Speed Color (normal, A4)	Up to 18 ppm
Print Speed Color (normal, letter)	Up to 18 ppm
Print Speed	Print speed up to 22 ppm (black) and 18 ppm (color)
AIO Functions	Print, copy, scan
Duplex Print Options	Automatic
Duty Cycle (monthly, A4)	Up to 30,000 pages
Duty Cycle (monthly, letter)	Up to 30,000 pages
Printer Smart Software Features	Color mode: Color/Grayscale using black only/Grayscale using CMYK black, Two-sided Printing: none/Flip on long edge/Flip on short edge, Pages per sheet: 1,2,4,6,9,16, Pages per sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left, Page Borders: On/Off, Print Quality: Normal/Draft/Best/Maximum dpi, Copy count, Collate, Orientation: Portrait/Landscape, Paper Size, Paper Source, Media Type, Booklet printing: Off/Left Binding/Right Binding, Watermarks, Page order: Front to Back/Back to Front, HP EasyColor: Off/Conservative/Automatic, Borderless printing: Off/On, Presets
Scanner Advanced Features	Smart Task Shortcuts; Scan to Cloud destinations: Dropbox, Google Drive, OneDrive; OCR (Optical Character Recognition); Auto Correct; Smart File Naming; Save as Text File
Energy Savings Feature Technology	Schedule On and Schedule Off
Replacement Cartridges	HP 937 Black Original Ink Cartridge (~1,250 pages) 4S6W5N; HP 937 Cyan Original Ink Cartridge (~800 pages) 4S6W2N; HP 937 Magenta Original Ink Cartridge (~800 pages) 4S6W3N; HP 937 Yellow Original Ink Cartridge (~800 pages) 4S6W4N. HP EvoMore planned to be available April 2024: HP 937e EvoMore Black Original Ink Cartridge (~2,500 pages) 4S6W9N; HP 937e EvoMore Cyan Original Ink Cartridge (~1,650 pages) 4S6W6N; HP 937e EvoMore Magenta Original Ink Cartridge (~1,650 pages) 4S6W7N; HP 937e EvoMore Yellow Original Ink Cartridge (~1,650 pages) 4S6W8N. Actual yield varies considerably based on content of printed pages and other factors. For details, see https://www.hp.com/go/learnaboutsupplies
Supplies Feature	HP Instant Ink eligible
Connectivity, Std	1 Ethernet; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11 a/b/g/n/ac (dual band)
Modem	Not supported
Network Capabilities	Yes, via built-in Ethernet; Wireless 802.11 a/b/g/n/ac
Wireless Capability	Yes, with built-in dual-band Wi-Fi 802.11 a/b/g/n/ac and a self-heal solution
Mobile Printing Capability	Chrome OS; Apple AirPrint™; Mobile Apps; Wi-Fi® Direct Printing; Mopria™ certified; HP app
Supported Network Protocols	TCP/IP
Software Included	HP Printer Software
Compatible Operating Systems	Windows 11; Windows 10; Android; iOS; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; macOS 15 Sequoia; Linux; Chrome OS ^[4] (<i>Windows Server 2016 64-bit, Windows Server 2019 64-bit, Windows Server 2022 64-bit; Linux (For more information see http://developers.hp.com/hp-linux-imaging-and-printing)</i>)
Technical Features	Borderless Printing; Wireless; Wireless Direct; AirPrint; Touchscreen; ADF; HP Printables; Automatic two-sided printing
Sustainable Impact Specifications	Contains ocean-bound recycled plastic; Recyclable through HP Planet Partners; FSC Certified Packaging
Energy Star Certified	No
Ecolabels (fixed)	EPEAT® registered
Blue Angel Compliance	No, please refer to the ECI (Ecolabel Comparison Information) document
Copy Speed Black (best A4)	Up to 4 cpm
Copy Speed Black (best, letter)	Up to 4 cpm
Copy Speed Color (best A4)	Up to 4 cpm
Copy Speed Color (best, letter)	Up to 4 cpm
Digital Sending Standard Features	Scan to PC; Scan to Memory Device; Scan to email
Scan Speed (normal, A4)	Up to 8/6 ipm (B&W/Color 200 ppi)

Scan File Format	Scan File Type supported by Software: Bitmap (.bmp), JPEG (.jpg), PDF (.pdf), PNG (.png), Rich Text (.rtf), Searchable PDF (.pdf), Text (.txt), TIFF (.tif)
Scan Input Modes	Front-panel scan, copy or from software
Scan Technology	Contact Image Sensor (CIS)
Scan Type	Flatbed, ADF
Display Description	4.3" Capacitive Touchscreen CGD
Product Dimensions (metric)	581 x 467 x 386 mm (Output Tray + Cleanout Door not extended)
Product Dimensions (imperial)	22.9 x 18.4 x 15.20 in (Output Tray + Cleanout Door not extended)
Weight (metric)	19.5 kg
Weight (imperial)	42.9 lb
Power Consumption Description	0.11 watts (Manual-Off), 5.40 watts (Standby), 1.39 watts (Sleep) ^{None}
Power Supply Type	Internal (Built-in) Universal Power Supply
What Is In The Box	NA: HP OfficeJet Pro 9730e WF AiO Printer; HP 936 Setup Black Ink Cartridge; HP 936 Setup Cyan Ink Cartridge; HP 936 Setup Magenta Ink Cartridge; HP 936 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide; [For more information about fill and yield, see http://www.hp.com/go/learnaboutsupplies] EU / AP Developed Market: HP OfficeJet Pro 9730e WF AiO Printer; HP 937 Setup Black Ink Cartridge; HP 937 Setup Cyan Ink Cartridge; HP 937 Setup Magenta Ink Cartridge; HP 937 Setup Yellow Ink Cartridge; Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide; [For more information about fill and yield, see http://www.hp.com/go/learnaboutsupplies]
Manufacturer Warranty	One-year limited hardware warranty with option to extend to 2 years with HP+ Offer. For more info please visit us at http://support.hp.com . [9]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Based on 2022 Q4 shipments in the IDC Worldwide Quarterly Hardcopy Peripherals Tracker®, 2022 Q4 Release. Includes shipments of all printing devices (inkjet printers, laser printers, copiers and multifunction devices, including production units).

[2] Compared to OEM printing apps for the majority of top-selling, network-capable inkjet/laser printers and all-in-ones for the home and office, priced ≤\$450 USD. Printers selected by market share as reported by IDC Quarterly Hardcopy Peripherals Tracker – Final Historical CYQ1 2023. Claim based on research of printer manufacturer's print apps and Keypoint Intelligence hands-on testing and study commissioned by HP, July 2023. For details, please see: keypointintelligence.com/HPSmartapp. Requires HP app download available at www.hp.com/go/mobileprinting. Certain features are available in English language only, and may vary by printer model/country, and between desktop/mobile applications. HP reserves the right to introduce charges for use of functionality facilitated by the HP app. Internet access required and may not be available in all countries. HP account required for full functionality. Fax capabilities are for sending a fax only. List of supported operating systems available in app stores. See details at www.hpsmart.com.

[3] HP OfficeJet 9700 printers are the world's first and only Display P3 color gamut capable wide format printers delivering a wider color range than sRGB. Based on June 2023 internal research of Expanded Color Gamut technology's comparison against comparable, top-selling competitive printers.

[4] HP OfficeJet Pro 9700 printer series has self-healing Wi-Fi and HP Wolf Pro Security, HP's best and most reliable technologies to stay connected and secure. Internet access required and must be purchased separately. Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at www.hp.com/go/mobileprinting. HP Security is now HP Wolf Security. Security features vary by platform, please see product data sheet for details.

[7] Based on plan usage, Internet connection to eligible HP printer, valid payment method, email address, and delivery service in your geographic area.

Technical Specifications Footnotes

[4] Not supporting Windows® XP (64-bit) and Windows Vista® (64-bit)

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

