



Visually impactful

Capture your vision better than you ever imagined with the HP Series 7 Pro 24" WUXGA Monitor. Do more with the 16:10 aspect ratio and WUXGA resolution that displays more of your work at once.[2] And, trust what you see on screen with superb color accuracy right out of the box, a smooth refresh rate, and enhanced color contrast.[1] Do it all with the ultra-thin 4-sided micro-edge frame and built-in ergonomics.



Discover what you can do with more.

See your work take on a whole new dimension on a large, smooth screen with vibrant, accurate colors right out of the box. See every detail pop thanks to the deeper shadows and brighter highlights of 1500:1 contrast ratio.[1] Enjoy 99% sRGB and 85% Display P3 color gamuts with factory color calibration for remarkable, real-life color accuracy that stays consistent from screen to screen. This 16:10 screen with WUXGA resolution gives you 11% more display space[2] so you can see—and do—more.

Minimalist design, maximalist function

This beautifully crafted, premium design heightens your work life and highlights your desk space thanks to its razor-thin profile and streamlined connectivity. Enjoy the sleek, 4-sided micro-edge frame and an elegant, ultra-thin design that looks great on any desk. Plus, maximize your productivity by doubling your screens with seamless daisy-chaining.

Comfort at every turn. Swivel. And tilt.

Stay fresh and comfortable with the monitor that helps you get more done throughout your day. Make screentime comfortable with 100 Hz refresh rates[1] for responsive, seamless scrolling and smooth video playback, while you enhance your focus with built-in HP Eye Ease that reduces blue light output while keeping color accuracy true-to-life. Customize your comfort with four-way ergonomic adjustability—complete with a 150 mm height-adjust stand with tilt, swivel and pivot.

Featuring

16:10 WUXGA Resolution

Get 11% more screen with WUXGA (1920x1200) resolution and 16:10 aspect ratio. [2]

100 Hz Refresh Rate

Experience smooth, life-like videos and clear details. [1]

More Contrast

See more detail in color, shadow, and highlights thanks to the enhanced 1500:1 contrast ratio. [1]

99% sRGB & 85% Display P3 Color Gamuts

Trust the colors you see on screen with all the shades and hues of 99% sRGB and 85% Display P3 color gamuts. [1]

Accurate color out of the box

Every HP Series 7 Pro Monitor undergoes strict factory color calibration to ensure that over 400

Specifications

Display size (diagonal)	24"
Panel technology	IPS
Display size (diagonal)	61 cm (24")
Aspect ratio	16:10 ^[1]
Native resolution	WUXGA (1920 x 1200) ^[1,2]
Resolutions supported	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 1920 x 1200
Pixel pitch	0.27 x 0.27 mm
Brightness	350 nits ^[1]
Contrast ratio	1500:1 ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Minimum dimensions (W x D x H)	53.17 x 3.85 x 34.29 cm (without stand)
Minimum dimensions (W x D x H)	20.93 x 1.52 x 13.5 in (without stand)
Dimensions With Stand (W x D x H)	53.17 x 19.5 x 52.14 cm
Weight	4.8 kg (with stand)
Weight	10.6 lb (with stand)
Display features	Anti-glare; Height Adjust/Tilt/Swivel/Pivot; HP Eye Ease
Onscreen controls	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit
Display colors	Up to 16.7 million colors supported ^[3]
Display scan frequency (horizontal)	30-146 kHz ^[1]
Display scan frequency (vertical)	50-100 Hz ^[1]
Camera	No integrated camera
Power	100 - 240 VAC 50/60 Hz
Power consumption	69 W (maximum), 36 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH (non-condensing)
Sustainable impact specifications	Low halogen; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 85% ITE-derived closed loop plastic; Designed with recycled metals; 5% ocean-bound plastic
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; FCC; GS Mark; ISO 9241-307; KC; KCC; NOM; PSB; SEPA; TUV-S; VCCI; Vietnam MEPS; WEEE; ISC; Low blue light; WW application; UAE; Ukraine EE; Ukraine CoC; Ukraine DOC; Microsoft WHQL Certification (Windows 11)
Physical security	Security lock-ready ^[11]
Management Software	HP Display Center; HP Display Manager
UPC number	(A2K) 197498445694; (A2N) 197498445700; (AB0) 197498445717; (AB1) 197498445724; (AB2) 197498445731; (AB4) 197498445748; (ABA) 197498445779; (ABB) 197498445786; (ABG) 197498445793; (ABJ) 4582712372058; (ABT) 197498445809; (ABU) 197498445816; (ABV) 197498445823; (ABY) 197498445830; (ACJ) 197498445847; (ACQ) 197498445854; (AH3) 197498445861; (AKL) 197498445878; (AR6) 197498445885; (UUF) 197498445892; (UUZ) 197498445908
Manufacturer Warranty	HP three-year limited warranty
What's in the box	Monitor; DisplayPort™ cable; HDMI cable; VESA Mount adapter; Warranty card; USB Type-A to B cable; Quick Setup Poster; Color calibration report ^[10]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Based on comparison against a 23.8-inch FHD (1920 x 1080) resolution monitor.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[2] DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1200 at 60 Hz and include 1 HDMI or 1 DisplayPort™ outputs to drive the monitor at the Preferred Mode.

[3] Number of colors through A-FRC technology.

[10] Included cables may vary by country.

[11] Lock sold separately.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR® is a registered mark owned by the U.S. government. EPEAT® is a registered trademark of Green Electronics Council.

