ProductSheet

Poly Savi 7420 Office Stereo Microsoft Teams Certified DECT 1920-1930 MHz Headset TAA (8L588AA)

Built for the modern office

Designed for the modern office with enhanced density performance, multi-device connectivity and advanced security features. You can deploy this headset across the company so everyone will benefit from increased productivity and wireless freedom.



Keep conversations private
Your conversations are private with DECT™ Security Step C, FIPS 140-2 military-grade features, and 256-bit AES encryption. You can be sure your conversations are clear thanks to a noise-canceling microphone boom with acoustic fence technology.

Wireless freedom
With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. And with a roaming range of up to 590 ft/180 m everyone can benefit from increased productivity.

Increased productivity
With 3-way connectivity, a universal base, and easy set-up and pairing, the Savi 7400 office series is the perfect solution for the modern office. You can even conference four headsets together with the base for increased productivity.

Featuring

3-way connectivity
Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Crystal-clear calls
Keep your conversations clear with a noise-canceling boom with Acoustic Fence technology to reduce background noise.

Privacy is ensured
Designed to meet the highest-level DECT™ Security Step C enhanced with military-grade FIPS 140-2 listed features, such as 256-bit AES encryption. [1]

Remote management
Stay in control with remote device management for settings, firmware, and security updates.

Training made easy
Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Specifications

Audio	Noise cancellation with Acoustic Fence technology; Microsoft Teams Open Office certified; Up to 2x more density than other DECT™ headsets; Adaptive power control to maximize user density
Weight	160 g
Weight	0.35 lb
Package weight	300 g
Battery life	Up to 13 hours (talk time); Up to 52 hours (standby time)
Special features	Color display on office base for audio settings management
Minimum System Requirements	USB Type-A port (PC); USB Type-C® port (PC); Bluetooth® (mobile phone); EHS interface (desk phone)
UPC number	197497838237
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Telephone interface cable (TIC)

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] DECT security standards can be found on https://etsi.org

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.