



## Your Everyday Monitor

Expand your view and boost productivity with an additional 21.45 inches of workspace from this FHD monitor. Work in comfort with a crisp, smooth screen and simple design, so you can get more done everyday.



### Elevate the Everyday

Make your everyday experience more productive and enjoyable with an expanded workspace for projects and assignments. This sleek 21.45" FHD monitor boasts an enhanced 3000:1 contrast ratio and up to 100Hz refresh rate<sup>[1]</sup> for sharp images and fluid motion.

### Increased Comfort. Improved Focus.

Keep your eyes comfortable with a flicker-free screen so you can get more done in your day. Plus, avoid the yellow color shift and keep the comfort with HP Eye Ease, an always-on hardware low-blue light filter that doesn't impact color accuracy.

### Clean Design. Clear Mind.

Streamline your desk with a monitor that helps you stay focused on what matters. Cut out clutter with a narrow bezel, neat cable management, and slim, tilt-adjustable stand. Easily customize your settings with the intuitive joypad OSD button.

## Featuring

### Enhanced Contrast

See even more of the nuanced differences of color, shadow, and highlights thanks to an enhanced 3000:1 contrast ratio.<sup>[1]</sup>

### Always-on, True Color, Low-Blue Light Filter

HP Eye Ease, an always-on, hardware low-blue light filter, helps keep your eyes comfortable throughout the day by reducing blue light without the yellow color shift.

### 100 Hz Refresh Rate

Experience smooth scrolling, life-like video and clear detail with a 100 Hz refresh rate that provides fluid movement from frame to frame.<sup>[1]</sup>

### Adjustable Tilt

The tilt-adjustable slim stand helps you find the right angle so you can maximize productivity and work comfortably.

### Plenty of Ports

This monitor is ready to connect for sharp FHD visuals with 1 x VGA and 1 x HDMI 1.4 port.<sup>[4,5]</sup>

## Specifications

<b>Display size (diagonal)</b>	21.45"
<b>Panel technology</b>	VA; LCD
<b>Display size (diagonal)</b>	54.5 cm (21.45")
<b>Aspect ratio</b>	16:9 <sup>[1]</sup>
<b>Native resolution</b>	FHD (1920 x 1080) <sup>[1,2]</sup>
<b>Resolutions supported</b>	640 x 480 @ 60 Hz; 720 x 400 @ 70 Hz; 800 x 600 @ 60 Hz; 800 x 600 @ 75 Hz; 1024 x 768 @ 60 Hz; 1280 x 720 @ 60 Hz; 1280 x 1024 @ 60 Hz; 1440 x 900 @ 60 Hz; 1600 x 900 @ 60 Hz; 1680 x 1050 @ 60 Hz; 1920 x 1080 @ 50 Hz; 640 x 480 @ 75Hz (HDMI only); 800 x 600 @ 75 Hz (HDMI only); 1024 x 768 @ 75 Hz (HDMI only); 1280 x 1024 @ 75 Hz (HDMI only); 1920 x 1080 @ 50 Hz (HDMI only); 1920 x 1080 @ 75 Hz (HDMI only); 1920 x 1080 @ 100 Hz (HDMI only)
<b>Pixel pitch</b>	0.25 x 0.24 mm <sup>[1]</sup>
<b>Brightness</b>	250 nits <sup>[1]</sup>
<b>Contrast ratio</b>	3000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	5ms GtG (with scalar overdrive) <sup>[1]</sup>
<b>Dimensions (W x D x H)</b>	50.42 x 5.08 x 30.3 cm (without stand)
<b>Dimensions (W x D x H)</b>	19.85 x 2 x 11.93 in (without stand)
<b>Dimensions With Stand (W x D x H)</b>	50.42 x 18.05 x 38.69 cm
<b>Weight</b>	2.8 kg (with stand)
<b>Weight</b>	6.2 lb (with stand)
<b>Display features</b>	Anti-glare; HP Eye Ease; Tilt
<b>Onscreen controls</b>	Brightness+; Color; Image; Input; Power; Menu; Management; Information; Exit
<b>Display colors</b>	Up to 16.7 million colors supported <sup>[1,3]</sup>
<b>Display scan frequency (horizontal)</b>	30-80 kHz (VGA); 30-115 kHz (HDMI) <sup>[1]</sup>
<b>Display scan frequency (vertical)</b>	50-60 Hz (VGA); 50-100 Hz (HDMI) <sup>[1]</sup>
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	22 W (maximum), 11 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% RH (non-condensing)
<b>Sustainable impact specifications</b>	Low halogen; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; 85% ITE-derived closed loop plastic; 10% recycled metal
<b>Certifications and compliances</b>	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; CSA; EAC; FCC; ISO 9241-307; KC/KCC; NOM; PSB; SEPA; TÜV Bauart; TÜV LBL; VCCI; Vietnam MEPS; WEEE; ISC; California Energy Commission (CEC); WW application; ICE; TÜV Flicker free certified; UAE safety; UAE RoHS; Works with Chromebook certified; South Africa safety; Ukraine safety
<b>Physical security</b>	Security lock-ready <sup>[5]</sup>
<b>Management Software</b>	HP Display Center; HP Client Management Script Library
<b>UPC number</b>	(A2K) 198122208647; (A2N) 198122208654; (AB0) 198122208661; (AB1) 198122208678; (AB2) 198122208685; (AB4) 198122208692; (ABA) 198122208708; (ABB) 198122208715; (ABG) 198122208722; (ABJ) 4582712437085; (ABT) 198122208739; (ABU) 198122208746; (ABV) 198122208753; (ABY) 198122208760; (AC8) 198122208777; (ACJ) 198122208784; (ACQ) 198122208791; (AH3) 198122208807; (AKH) 198122208814; (AKL) 198122208821; (AR6) 198122208838; (UUF) 198122208845; (UUZ) 198122208852
<b>Manufacturer Warranty</b>	HP three-year limited warranty
<b>What's in the box</b>	Monitor; HDMI cable; Warranty card; Quick Setup Poster; AC power cord <sup>[4]</sup>

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. 100 Hz refresh rate can be supported via HDMI only. 60 Hz refresh rate with VGA.

[4] FHD content is required to view FHD images.

[5] HDMI 1.4 and AC power cable included. All other cables sold separately.

## Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers, actual performance may vary either higher or lower.

[2] HDMI 1.4 or VGA required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 100 Hz with 8-bit color using one HDMI; 1920 x 1080 at 60 Hz with 8-bit color using one VGA.

[3] Number of colors through A-FRC technology.

[4] Included cables may vary by country.

[5] Lock sold separately.

---

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

EPEAT® is a registered trademark of Green Electronics Council. ENERGY STAR® is a registered mark owned by the U.S. government. © 2024 Google LLC All rights reserved. Chrome is a trademarks of Google LLC.

