

HP Color LaserJet Pro 3201dw Printer (499Q9FR)



Designed for business work teams that need professional performance with fast, high-quality two-sided color printing, laser productivity, and award-winning reliability in a space-saving design.[11]

Professional color and speed

Experience high-speed, automatic, two-sided color printing up to 26 pages per minute (Letter) / 25 pages per minute (A4).[1]

Peace-of-mind with award-winning reliability[11]

Performance you can count on page after page with award-winning reliability.[11]

Pro level security to help protect your business

Safeguard your business with proactive, embedded security ready out of the box and tamper-resistant toner.[12]

Featuring

Business team solution

Fast two-sided color printing [1]

True-to-life colors [8]

Compact Design

Advanced productivity features[18] [18]

HP Web Jetadmin[5] [5]



Specifications

Print quality black (best)	Up to 600 x 600 dpi
Print quality color (best)	Up to 600 x 600 dpi
Print speed black (ISO, A4)	Up to 25 ppm
Print speed black (ISO, letter)	Up to 26 ppm
Print Speed Color (ISO)	Up to 25 ppm
Print speed color (ISO)	Up to 26 ppm
Print speed	Print speed up to 25 ppm (black) and 25 ppm (color)
Functions	Print
Duplex printing	Automatic
Duty cycle (monthly, A4)	Up to 40,000 pages
Duty cycle (monthly, letter)	Up to 40,000 pages
Energy savings feature technology	HP Auto-On/Auto-Off Technology
Supplies feature	HP TerraJet Cartridge
Connectivity, standard	1 Hi-Speed USB 2.0 (device); 1 Wi-Fi 802.11 ac (dual band); Auto-crossover Ethernet; 1 Gigabit Ethernet 10/100TX network
Network capabilities	Built-in 10/100 Base-TX Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1X
Wireless capability	Built-in dual-band Wi-Fi; Authentication via WEP, WPA/WPA2, WPA Enterprise; Encryption via AES or TKIP; WPS; Wi-Fi Direct
Network protocols, supported	TCP/IPv4, TCP/IPv6, DHCP, DNS.
Software included	HP Printer Software downloadable from https://www.hpsmart.com/download
Compatible Operating Systems	Windows 11; Windows 10; Android; iOS; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; macOS 15 Sequoia; Linux ^[11] <i>([11] Windows Server 2016, Windows Server 2019, Windows Server 2022, Linux (For more information see https://www.developers.hp.com/hp-linux-imaging-and-printing))</i>
Display area (imperial)	1.80 x 1.03 in
Display area (metric)	4.6 x 2.6 cm
Display	2" diagonal DFSTN-backlit (200 x 114)
Dimensions (W x D x H)	390 x 419.12 x 254.19 mm <i>([4] End to End Dimensions when printer is set up and on standby)</i>
Dimensions (W x D x H)	15.35 x 16.5 x 10.01 in <i>([4] End to End Dimensions when printer is set up and on standby)</i>
Weight	13.8 kg ^[13] <i>([13] Product Weight Inclusive of Starter Supplies)</i>
Weight	30.42 lb <i>([13] Product Weight Inclusive of Starter Supplies)</i>
Power consumption	415 watts (Printing), 6.1 watts (Ready), 0.63 watts (Sleep), 0.05 watts (Auto-Off), 0.05 watts (Manual-Off) ^[1] <i>([1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device.)</i>
Power supply type	Internal (Built-in) power supply
What's in the box	Power cord; Toner cartridge; User Guide; Flyers; CD (#BBU and #AAC only) ^[2]
Manufacturer Warranty	One-year limited warranty. For more info please visit us at https://www.support.hp.com [12]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Measured using ISO/IEC 24734 and excludes first set of test documents. For more information, see <https://www.hp.com/go/printerclaims> . Exact speed varies depending on the system configuration, software application, driver, and document complexity.

[5] HP Web Jetadmin is available for download at no additional charge at <https://www.hp.com/go/webjetadmin>

[8] Standard print mode for HP Color LaserJet Pro series with HP TerraJet Toner Cartridges compared to predecessors. See <https://www.hp.com/TerraJet/colors>

[11] Buyers Lab (BLI) 2022-2024 Most Reliable A4 Brand Award based on devices tested by Keypoint Intelligence from 2017 to 2021. See <https://www.keypointintelligence.com/view-award?region=&id=135871174680>

[12] HP office-class printing systems are select Managed and Enterprise devices with FutureSmart firmware 4.5 and up, Pro devices, LaserJet models 200 and up, with respective Original HP Toner, PageWide and Ink Cartridges. Does not include HP integrated printhead cartridges. Digital supply-chain tracking, hardware, chips and packaging security features vary locally by SKU. See <https://www.hp.com/cartridgesecurity>

[18] HP account required for full functionality.

Technical Specifications Footnotes

[1] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115 V device.

[2] For yield information on the cartridge(s) included with your printer, see <https://www.hp.com/go/toneryield> . Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[11] Windows Server 2016, Windows Server 2019, Windows Server 2022, Linux (For more information see <https://www.developers.hp.com/hp-linux-imaging-and-printing>)

[13] Product Weight Inclusive of Starter Supplies

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

