

ThinkPad T14s Gen 6 (Snapdragon)

Introducing the ultimate ThinkPad, crafted to unleash productivity on the go. The impressive Snapdragon™ X Elite Processor brings a considerable leap forward with improved performance, efficiency and dedicated NPU abilities. With the new improvements from Windows 11 Copilot, the on-device AI enables you to tap into LLM and work faster, even when you're offline. Weighing in at a mere 1.24kg, this portable powerhouse defies expectations. And with the remarkable 58Wh battery, coupled with Rapid Charge support, it lets you work uninterrupted for extended periods.



Redefining possibilities with powerful performance and groundbreaking on-device AI

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.


Designed with versatility in mind, it features multiple USB-A ports and dual Thunderbolt 4 ports for effortless connectivity with a wide range of peripherals and accessories. Stay connected with lightning-fast Qualcomm Wi-Fi 7, ensuring consistent internet speeds whether you're working remotely, streaming content or collaborating with colleagues.

Immerse yourself in a world of stunning visuals with the 2.8K OLED display, boasting an anti-glare surface and a breathtaking 16:10 aspect ratio. Elevate your audio experience with dual Dolby Audio stereo speakers and 360° far-field mics for delivering rich, immersive sound.

Designed with sleek, modern aesthetics, this 1.24 kg marvel reduces the physical burden on mobile users, making it convenient to carry whether in a backpack, briefcase or even a handbag.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo USB-C to VGA Adapter

- Turns a USB-C port into a VGA port for connecting to a wide variety of displays, projectors or TVs with VGA input
- Mirror your primary display or extend your display to double your workspace
- Plug and play with no external power or extra drivers required



PN: GX90M44578

ThinkPad T14s Gen 6 (Snapdragon)

Performance

Processor

Snapdragon X Elite or Snapdragon X Plus

Operating System

Windows 11 Pro (on ARM)
Windows 11 Home (on ARM)

NPU

Integrated Qualcomm Hexagon NPU, up to 45 TOPS

Graphics

Qualcomm Adreno GPU (integrated)

Memory

16GB LPDDR5x-8448, soldered
32GB LPDDR5x-8448, soldered
64GB LPDDR5x-8448, soldered

Storage ¹

Up to 1x 1TB M.2 2242 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, 360° far-field

Camera *

FHD 1080p + IR discrete, MIPI, with privacy shutter & Always On Computer Vision, temporal noise reduction

Battery ^{2 3}

58Wh battery (video playback up to 34.9 hr), Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

³Rapid charge is only guaranteed when the computer is turned off or in standby mode or in hibernation mode.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display ⁴

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, touch, Eyesafe, 3M DBEF5
- 400nits, 100% sRGB, low power, Eyesafe

14" 2.8K (2880x1800) OLED AGARAS 16:10
- 400nits, 100% DCI-P3, 120Hz, DisplayHDR True Black 500, Dolby Vision, Eyesafe

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, Copilot key, backlight

Touchpad

TrackPoint and glass-like Mylar surface touchpad
61 x 115 mm (2.4 x 4.53 inches)

Dimensions ⁵

313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

⁵The system dimensions may vary depending on configurations.

Weight ⁶

Starting at 1.24 kg (2.72 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Black

Case material

CFRP (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*

Qualcomm Wi-Fi 7 NCM825A, 802.11be, Bluetooth 5.3

WWAN*

5G Sub-6 GHz with embedded eSIM*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 1.4a
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Touch style MOC fingerprint reader
Camera privacy shutter
IR camera for Windows Hello (facial recognition)
Computer Vision-based User Presence Sensing including lock on leave

Certifications

Green Certifications ^{7 8 9}

ENERGY STAR 8.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 9.0
RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

⁹EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Eyesafe Certified 2.0
MIL-STD-810H