




FEATURES

- Google TV™**
 Google TV brings together your movies, shows, and more from across your subscriptions, so they're in one place.
- Google Assistant**
 Ask Google Assistant to find movies, stream apps, play music, and control the monitor — all with your voice.
- Speakers powered by Dolby Audio™**
 With built-in speakers and Dolby Audio technologies to play movies and TV shows in surround sound.
- Wireless Display**
 Cast the entertainment you love from your phone or laptop to the monitor.
- Multi Control**
 lets you manage two devices from a single screen with one set of peripherals, enhancing multitasking efficiency.
- Type C 65W Power Delivery**
 Built-in an USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices
- IPS Panel with Wide Viewing Angle**
 Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.
- Adjustable Stand**
 Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.

SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	3840 x 2160 (UHD)
REFRESH RATE	60Hz
RESPONSE TIME	4ms (GtG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	SDR: 300 cd/m2
VIEWING ANGLE	178° (H) / 178° (V)
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
ADOBE RGB / DCI-P3 / SRGB	94% / 98% / 127% (CIE1976 Standard)
ACTIVE DISPLAY AREA (MM)	596.736 (H) x 335.664 (V)
PIXEL PITCH (H X V)	0.1554 (H) x 0.1554 (V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	1.07B
COLOR BIT	10 bits (8 bits + FRC)
HDR SUPPORT	HDR Ready
USB Ports	2x USB 2.0 Type-A
AUDIO PORTS	1x Headphone-out
Ethernet Interface	1x LAN Port
Wi-Fi	Wi-Fi 5 (IEEE 802.11 a/b/g/n/ac)
Bluetooth	5.0
KENSINGTON LOCK	Yes
SPEAKER	3W x2, powered by Dolby Audio
VESA MOUNTING	75 x 75 mm
POWER TYPE	Internal Power Board
POWER INPUT	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	-30° ~ 30°
ADJUSTMENT (PIVOT)	-90° ~ 90°
ADJUSTMENT (HEIGHT)	0 ~ 110 mm
DIMENSION (W X H X D)	613.5 x 201.8 x 413.4 mm (24.15 x 7.94 x 16.28 inch)
CARTON DIMENSION (W X H X D)	702 x 195 x 464 mm (27.64 x 7.68 x 18.27 inch)
WEIGHT (NW / GW)	6.30 kg (13.89 lbs) / 9.10 kg (20.06 lbs)



SMART MONITORS

Modern MD272UPSW

LIVE SMARTER NOT HARDER

CERTIFICATES	Energy Star
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook *All trademarks and the registered trademarks are the property of their respective owners.
ACCESSORIES	1x HDMI™ Cable (2.0b), 1x USB Type-C Cable, 1x Power Cord (C13), 1x Quick Guide, 4x VESA Wall Mount Screw, 1x Remote Control, 2x Battery (AAA)
Note	HDMI™: 3840 x 2160 (Up to 60Hz) DisplayPort: 3840 x 2160 (Up to 60Hz) Type-C: 3840 x 2160 (Up to 60Hz) Support: HDMI™ CEC, KVM; Non Support: PIP/PBP