

ThinkPad X9 14 Gen 1 Aura Edition

Introducing the ThinkPad X9 14 Gen 1 Aura Edition, a modern premium device that blends intentional elegance and an extraordinary UX. Powered by the Intel® Core™ Ultra 7 processor, with a combined NPU, CPU and GPU power of 100+ TOPS, this device delivers exceptional multitasking capabilities and optimized workflow management. With Copilot+ PC features and Lenovo AI Now assistance, it brings on-device AI-driven efficiency to life. The ultrathin lightweight design, extended battery life and legendary ThinkPad reliability make this device the optimal solution for on-the-move ninjas.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad X Series ultraportables combine enterprise security, manageability, docking and productivity features into a thin and lightweight design.

Experience unmatched visual clarity- thanks to the stunning 2.8K OLED display that comes with 500 nits brightness and 100% DCI-P3 color gamut. The EyeSafe technology helps reduce harmful bluelight emissions without compromising on color fidelity, during prolonged hours of use.

Whether you're watching movies, playing games or on video calls, The Dolby Atmos audio delivers a multidimensional, unparalleled listening experience. Rely on the Elevoc noise suppression for minimizing background noise during calls and making communication seamless.

With ENERGY STAR 8.0 certification and EPEAT Gold registration, this device is designed for energy efficiency, offering lower power consumption, a reduced environmental impact, and cost-effective performance for users.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 15.6-inch Laptop Casual Backpack B210 Grey

- Extra cushioning and padding for maximum comfort
- Waterproof fabric to keep your gadgets dry and safe
- Conveniently placed compartments and pockets for easy access.



PN: GX40Q17225

Lenovo Go USB-C Wireless Mouse

- Ergonomically designed ambidextrous mouse with Villi painted grip and wireless connection via USB-C dongle
- Silent buttons with 2-way scroll wheel (up/down), programmable Utility Button on the side
- Default functions optimized for Teams calls, can be configured through Lenovo Go Central Software



PN: 4Y51C21216

ThinkPad X9 14 Gen 1 Aura Edition

Performance

Processor

Intel V Series Core Ultra 5/7 Processor (Series 2)

Operating System

Windows 11 Pro
Windows 11 Home
Ubuntu Linux
Linux

NPU

Integrated Intel AI Boost, up to 48 TOPS

Graphics

Intel Arc Graphics 130V (integrated)
Intel Arc Graphics 140V (integrated)

Memory

16GB LPDDR5x-8533 MoP memory, soldered
32GB LPDDR5x-8533 MoP memory, soldered

Storage ¹

Up to 1x 2TB M.2 2242 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array

Camera *

FHD 1080p + IR discrete, with E-shutter, temporal noise reduction
UHD 8.0MP with large sensor + IR discrete, with E-shutter, ToF sensor, MIPI, temporal noise reduction

Battery ²

55Wh (up to 15.63hr) battery, Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C nano GaN adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display

14" WUXGA (1920x1200) OLED Anti-glare 16:10
- 400nits, 100% DCI-P3, DisplayHDR True Black 500, Dolby Vision, Eyesafe

14" 2.8K (2880x1800) OLED ARAS 16:10
- 500nits, 100% DCI-P3, touch, 30-120Hz VRR, DisplayHDR True Black 600, Dolby Vision, Eyesafe

Pen*

Pen sold separately*

Keyboard

6-row, spill-resistant, Copilot key, backlight

Touchpad

Buttonless glass surface multi-touch Haptic Touchpad
80 x 130 mm (3.15 x 5.12 inches)

Dimensions ³

311.8 x 212.3 x 6.7 - 17.18 mm
(12.28 x 8.36 x 0.26 - 0.68 inches)

³The system dimensions may vary depending on configurations.

Weight ⁴

Multi-touch models: starting at 1.27 kg (2.80 lbs)
Non-touch models: starting at 1.21 kg (2.66 lbs)

⁴The system weight is approximate and may vary depending on configurations

Color

Grey

Case material

Aluminium (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*

Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

Ports

2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0
Touch style MOC fingerprint reader
IR camera for Windows Hello (facial recognition)
E-shutter
Ultrasonic Human Presence Detection (WUXGA models)
ToF Human Presence Detection (2.8K models)

Manageability

System Management* ⁵

Intel vPro Enterprise*

⁵Intel vPro offers a superset of DASH's defined capabilities.

Certifications

Green Certifications ^{6 7 8}

ENERGY STAR 8.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 10.0
RoHS compliant

⁶The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁷EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

⁸EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Intel Evo Platform*
Eyesafe Certified 2.0
MIL-STD-810H