

ThinkPad T16 Gen 4 (AMD)

Powered by up to AMD Ryzen™ AI 7 300 Series Processor and up to AMD Radeon™ 860M graphics, this laptop delivers seamless multitasking and sharp visuals for on-the-go professionals. Whether analyzing engineering simulations, editing marketing videos, or compiling financial reports, its raw power adapts to diverse workflows. With up to 64GB DDR5 memory, architects can render models faster, creatives can edit 4K footage without lag, and data scientists can juggle datasets effortlessly. This level of responsiveness transforms travel downtime into peak productivity across industries, wherever work leads.



**Redefining possibilities with
powerful performance and
groundbreaking on-device AI**

A vibrant 16" WUXGA display brings crisp clarity to presentations and detailed work. Coupled with dual USB-C® (Thunderbolt™ 4 / USB4®) and HDMI® ports, connecting to peripherals or secondary screens is instant and efficient. Meanwhile, Wi-Fi® 7 ensures ultra-fast connectivity in crowded environments.

With up to 2TB SSD storage, large project files, media assets, or analytical archives are always within reach. Enhanced security comes through Discrete TPM 2.0 and an optional touch style fingerprint reader.

For mobile users, performance is crucial as it directly impacts productivity. With an Intel® N-series processor, up to 16GB memory, and Rapid Charge support, this device ensures seamless multitasking, fast charging, and efficient work on the go.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

- On-site support if needed
- Normally next business day service
- Agreed appointment times

Accessories

Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

ThinkBook Bluetooth Silent Mouse

- Bluetooth mouse with silent buttons for noise-free operation
- Low-profile design suitable for both right-handed and left-handed users
- 4 buttons, 2-way scrolling with easy DPI adjustment: 2400, 1600, 800



PN: 4Y50X88824

ThinkPad T16 Gen 4 (AMD)

Performance

Processor

AMD Ryzen AI 5/7 300 Series Processor

AI PC Category

Copilot+ PC

AI Performance

Up to 66 overall TOPS

Operating System*

Windows 11 Pro
Windows 11 Home
Fedora Linux
Ubuntu Linux
Linux

NPU

Integrated AMD Ryzen AI, up to 50 TOPS

Graphics

AMD Radeon 840M (integrated)
AMD Radeon 860M (integrated)

Memory¹

Up to 64GB DDR5-5600, 2x SO-DIMM

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage²

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, 360° far-field, Dolby Voice*

Camera*

5.0MP, with privacy shutter, temporal noise reduction
5.0MP + IR discrete, with privacy shutter, temporal noise reduction

Battery³

52.5Wh or 86Wh battery, up to 22 hr, Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C nano GaN adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0
100W USB-C slim adapter, PD 3.0

Design

Display⁴

16" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC
- 400nits, 45% NTSC, touch, Eyesafe
- 500nits, 100% sRGB, low power, Eyesafe

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, numeric keypad, Copilot key, optional backlight

Touchpad

TrackPoint and glass-like Mylar surface 3-button
Trackpad
67.7 x 115 mm (2.67 x 4.53 inches)

Dimensions⁵

Starting at
359.7 x 250.8 x 11.8/18.14 (front/rear), 23.5 (maximum) mm;
14.16 x 9.87 x 0.46/0.71 (front/rear), 0.93 (maximum) inches

⁵The system dimensions may vary depending on configurations.

Weight⁶

Models with 52.5Wh battery: starting at 1.76 kg (3.89 lbs)
Models with 86Wh battery: starting at 1.98 kg (4.37 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Black

Case material

PC + 20% CF (top), PC + 20% CF (bottom)

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth*⁷

MediaTek Wi-Fi 7 MT7925, 802.11be, Bluetooth 5.4

⁷Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

WWAN*

4G LTE CAT6 with embedded eSIM
5G Sub-6 GHz with embedded eSIM

NFC

Near Field Communication*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Ethernet (RJ-45)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter*
IR camera for Windows Hello (facial recognition)*
Ultrasonic Human Presence Detection*

Manageability

System Management*

DASH

Certifications

Green Certifications^{8 9 10}

ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 10.0
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

¹⁰EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Eyesafe Certified 2.0*
MIL-STD-810H