

Specifications



Eaton

EMAGKEC4C4C4C4L

3-Phase Managed HDX Rack PDU G4, 208V,
24 C39 Outlets, 100A, 36kW, Hardwired
Input, 0U Vertical, TAA

General specifications

PRODUCT NAME	Eaton managed PDU
CATALOG NUMBER	EMAGKEC4C4C4C4L
UPC	037332296191
PRODUCT LENGTH/DEPTH	2.48 in
PRODUCT HEIGHT	69.45 in
PRODUCT WIDTH	4.09 in
PRODUCT WEIGHT	28.02 lb
COMPLIANCES	CE Marked FCC Class A TAA Compliant
CERTIFICATIONS	UL Listed cUL Listed

Product specifications

FORM FACTOR	0U (Vertical)
PHASE	3-Phase
INPUT CONNECTION	Hardwire
OUTLETS	24
CORD LENGTH	0
FREQUENCY RATING	50/60 Hz
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Resources

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

