



SPECIFICATIONS

Panel Size	27"
Active Display Area (mm)	597.888 (H) x 336.312 (V)
Curvature	Curve 1500R
Panel Type	Rapid VA
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.3114 (H) x 0.3114 (V)
Aspect Ratio	16:9
Brightness (nits)	SDR: 250 cd/m ²
Contrast Ratio	3000:1
DCR	100000000:1
Signal Frequency	53~221 KHz(H) / 48~200 Hz(V)
ACTIVATED RANGE	48~200Hz
Refresh Rate	200Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	2x HDMI™ 2.0b (FHD@200Hz) 1x DisplayPort 1.2a
USB ports	N/A
Audio ports	1x Headphone-out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	81% / 76% / 98% (CIE1976 Standard)
Surface Treatment	Anti-glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
SPEAKER	N/A
Power Type	Internal Power Board
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5°~20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Dimension with Stand (W x D x H)	610.5 x 249.8 x 451.6 mm (24 x 9.83 x 17.78 inch)
Dimension without Stand (W x D x H)	610.5 x 90.4 x 362.5 mm (24 x 3.56 x 14.27 inch)

FEATURES



1500R Curved Gaming

Immerse in a captivating experience with a 1500R curvature rate.



Rapid VA

Provide ultra-fast 1ms GTG response time, make sure the intensity and purity of colors when gaming.



200Hz High Refresh Rate

200Hz High Refresh Rate Experience smooth gaming with a blazing fast 200Hz refresh rate, that gives you the upperhand in fast moving games.



0.5ms (GtG, Min.) Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.



HDR Ready

Enhance eye-catching details through adjustments in contrast and shadows.

Weight (NW / GW)	3.95 kg (8.7 lbs) / 6.5 kg (14.33 lbs)
Carton Dimension (W X D X H)	684 x 158 x 475 mm (26.9 x 6.22 x 18.7 inch)
Accessories	1x HDMI™ Cable (2.0), 1x Power Cord (C13), 1x Quick Guide
Note	HDMI™: 1920 x 1080 (Up to 200Hz) DisplayPort: 1920 x 1080 (Up to 200Hz) Support: HDMI™ CEC; Non Support: KVM, PIP/PBP

CONNECTIONS



- 1. OSD Button / 5-Way Navigator
- 2. AC-in
- 3. HDMI™ 2.0b (FHD@180Hz)
- 4. DisplayPort 1.2a
- 5. HDMI™ 2.0b (FHD@180Hz)
- 6. Headphone-out
- 7. Kensington Lock