




SEAMLESS CONNECT

Universal dvLED Floor-to-Ceiling Mount

The SEAMLESS Connect Universal Series by Peerless-AV® offers a versatile lineup of substructures for environments where wall mounting is not an option. Purpose-built for dvLED video walls and all-in-one displays, the SEAMLESS Connect Universal Floor-to-Ceiling Mount supports full system weight with strength and stability. Its slim, space-saving design simplifies setup and speeds up installation. The quad post leveling base and ceiling-attach bracket ensure a plumb structure and a perfectly flat mounting surface for dvLED installation - Ideal for corporate lobbies, retail, hospitality, showrooms, events, and entertainment spaces.

- Adaptable solution for installations where mounting direct to a wall is not an option
- Slim, space saving design fits neatly in any installation environment
- Lightweight aluminum frame makes shipping, handling and installation easier
- Anodized aluminum finish for a durable, decorative appearance
- Modular design provides scalability in installation configuration and size
- Integrated cable management protects, contains and conceals cables for a clean, professional installation
- Compatible with all SEAMLESS Connect Universal mounts, offering peace of mind when designing solutions or if project specs change
- Optional trim kit accessory (LEDTK) offers compatibility with most displays



*Universal spacer (LEDUNVSPACER3) is sold separately.


Contact a Peerless-AV® Sales Representative for the current list of compatible latching dvLED display models.




Cart/Trolley
LEDMTS-6X6 shown



Floor Stand
LEDFFS-6X6 shown



Bolt-Down Pedestal
LEDBDS-6X6 shown



Floor-to-Wall Mount
LEDfWS-6X6 shown

Please visit peerless-av.com/en-us/patents for patent information.

Model Numbers

WARRANTY: 5 Years

LEDFC Models	SEAMLESS Connect Universal dvLED Floor-to-Ceiling Mount
--------------	---

LEDFCS – for dvLED displays up to 610mm wide

LEDFCM – for dvLED displays up to 960mm wide

LEDFCL – for dvLED displays up to 1220mm wide

Product Specifications

UNIVERSAL SPACER*	DIMENSIONS (W x H x D)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS
LEDUNVSPACER3	55.55" x 3.94" x 2.50" (1411 x 100 x 64mm)	4lb (1.8kg)	NA	Powder Coat	Black
PRECONFIGURED MODELS					
LEDFCS-4x4 LEDFCS-5x5 LEDFCS-6x6 LEDFCS-8x8	96.06" x 95.47"-96.45" x 8.19" (2440 x 2425-2450 x 208mm) 120.08" x 95.47"-96.45" x 8.19" (3050 x 22425-2450 x 208mm) 144.02" x 95.47"-96.45" x 8.19" (3660 x 2425-2450 x 208mm) 192.13" x 119.09"-120.07" x 8.19" (4880 x 3025-3050 x 208mm)	108lb (49.1kg) 133lb (60.5kg) 175lb (79.5kg) 299lb (135.9kg)	400lb (181.8kg) 625lb (284.1kg) 900lb (409.1kg) 1600lb (727.3kg)	Anodized, Powder Coat	Black
LEDFCM-3x3 LEDFCM-4x4 LEDFCM-5x5	113.38" x 95.47"-96.45" x 8.19" (2880 x 2425-2450 x 208mm) 151.18" x 95.47"-96.45" x 8.19" (3840 x 2425-2450 x 208mm) 188.97" x 119.09"-120.07" x 8.19" (4800 x 3025-3050 x 208mm)	112lb (50.9kg) 209lb (95.0kg) 228lb (103.6kg)	315lb (143.2kg) 560lb (254.5kg) 875lb (397.7kg)		
LEDFCL-2x2 LEDFCL-3x3 LEDFCL-4x4	96.06" x 95.47"-96.45" x 8.19" (2440 x 2425-2450 x 208mm) 144.09" x 95.47"-96.45" x 8.19" (3660 x 2425-2450 x 208mm) 192.13" x 119.09"-120.07" x 8.19" (4880 x 3025-3050 x 208mm)	104lb (47.3kg) 168lb (76.4kg) 287lb (130.5kg)	400lb (181.8kg) 900lb (409.1kg) 1600lb (727.3kg)		


Package Specifications

UNIVERSAL SPACER*	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
LEDUNVSPACER3	5.00" x 4.375" x 38.00" (127 x 111 x 965mm)	9.5lb (4.3kg)	735029359333	Universal Spacer Kit	1
PRECONFIGURED MODELS					
*Universal spacer (LEDUNVSPACER3) is sold separately.					
LEDFCS-4x4 LEDFCS-5x5 LEDFCS-6x6 LEDFCS-8x8	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	138lb (62.7kg) 163lb (74.1kg) 205lb (93.2kg) 329lb (149.5kg)	735029358237 735029358244 735029358251 735029358268	dvLED Display Mount, Subframe, Floor Anchors and Ceiling Attach Bracket	1
LEDFCM-3x3 LEDFCM-4x4 LEDFCM-5x5	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	142lb (64.5kg) 239lb (108.6kg) 258lb (117.3kg)	735029358275 735029358282 735029358299		
LEDFCL-2x2 LEDFCL-3x3 LEDFCL-4x4	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	134lb (60.9kg) 198lb (90.0kg) 317lb (144.1kg)	735029358305 735029358312 735029358329		

Accessories

LEDTK Models: SEAMLESS Connect Universal dvLED Trim Kit

All dimensions = inch (mm)



MODEL NO.	DIMENSION "A"	DIMENSION "B"	DIMENSION "C"	DIMENSION "D"
LEDFCS-4x4	8.19" (208mm)	96.06" (2440mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCS-5x5		120.08" (3050mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCS-6x6		144.09" (3660mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCS-8x8		192.13" (4880mm)	119.09" (3025mm) - 120.07" (3050mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCM-3x3		113.38" (2880mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCM-4x4		151.18" (3840mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCM-5x5		188.97" (4800mm)	119.09" (3025mm) - 120.07" (3050mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCL-2x2		96.06" (2440mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCL-3x3		144.09" (3660mm)	95.47" (2425mm) - 96.45" (2450mm)	0.11" (3mm) - 19.68" (500mm)
LEDFCL-4x4		192.13" (4880mm)	119.09" (3025mm) - 120.07" (3050mm)	0.11" (3mm) - 19.68" (500mm)

FRONT VIEW

SIDE VIEW

LEDFCS-6x6 Shown Dimension B as fully expanded. Horizontal Extrusions can be cut to length as needed.

Architect Specifications

The SEAMLESS Connect Universal dvLED Floor-to-Ceiling Mount shall be a Peerless-AV LEDFC models and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor displays, kiosks, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV
2300 White Oak Circle
Aurora, IL 60502
USA

(800) 865-2112
(630) 375-5100

Peerless-AV EMEA
Unit 2 Curo Park
Frogmore, St. Albans
Hertfordshire, AL2 2DD
United Kingdom

+44 (0) 1923 200 100

Peerless-AV B.V.
Papendorpseweg 75
3528 BJ Utrecht
The Netherlands

+31 (0) 70 770 8037

Peerless-AV Latin America
Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo, N.L.,
México, 66062

+52 (81) 8384-8300

