

## LEDMT Models




# SEAMLESS CONNECT

## Universal dvLED Cart/Trolley

The SEAMLESS Connect Universal Series by Peerless-AV® offers a versatile lineup of substructures for environments where wall mounting is not an option. Purpose-built for dvLED video walls and all-in-one displays, the SEAMLESS Connect Universal Cart/Trolley supports full system weight with strength and stability. Its slim, space-saving design simplifies setup and speeds up installation. Smooth-rolling castors provide effortless mobility, making it easy to reposition the display as needed - Ideal for corporate lobbies, retail, hospitality, showrooms, events, and entertainment spaces.


- Adaptable solution for installations where mounting direct to a wall is not an option
- Slim, space saving design fits neatly in any installation environment
- Lightweight aluminum frame makes shipping, handling and installation easier
- Anodized aluminum finish for a durable, decorative appearance
- Modular design provides scalability in installation configuration and size
- Integrated cable management protects, contains and conceals cables for a clean, professional installation
- Compatible with all SEAMLESS Connect Universal mounts, offering peace of mind when designing solutions or if project specs change
- Optional trim kit accessory (LEDTK) offers compatibility with most displays




Contact a Peerless-AV® Sales Representative for the current list of compatible latching dvLED display models.




Floor Stand  
LEDFSS-6X6 shown



Bolt-Down Pedestal  
LEDBDS-6X6 shown



Floor-to-Wall Mount  
LEDFWS-6x6 shown



Floor-to-Ceiling Mount  
LEDFCS-6X6 shown

Please visit [peerless-av.com/en-us/patents](http://peerless-av.com/en-us/patents) for patent information.

Model Numbers

WARRANTY: 5 Years

LEDMT Models	SEAMLESS Connect Universal dvLED Cart/Trolley
--------------	---

LEDMTS – for dvLED displays up to 610mm wide	LEDMTM – for dvLED displays up to 960mm wide	LEDMTL – for dvLED displays up to 1220mm wide
--	--	---

Product Specifications

UNIVERSAL SPACER*	DIMENSIONS (W x H x D)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS
LEDUNVSPACER3	55.55" x 3.94" x 2.50" (1411 x 100 x 64mm)	4lb (1.8kg)	NA	Powder Coat	Black
PRECONFIGURED MODELS					
LEDMTS-4x4 LEDMTS-5x5 LEDMTS-6x6 LEDMTS-8x8	96.06" x 102.10" x 39.41" (2440 x 2593 x 1000mm) 120.08" x 102.10" x 39.41" (3050 x 2593 x 1000mm) 144.08" x 102.10" x 39.41" (3660 x 2593 x 1000mm) 192.12" x 125.71" x 39.41" (4880 x 3193 x 1000mm)	144lb (65.5kg) 168lb (76.4kg) 231lb (105.0kg) 348lb (158.2kg)	400lb (181.8kg) 625lb (284.1kg) 900lb (409.1kg) 1600lb (727.3kg)	Anodized, Powder Coat	Black
LEDMTM-3x3 LEDMTM-4x4 LEDMTM-5x5	113.38" x 102.10" x 39.41" (2880 x 2593 x 1000mm) 151.08" x 102.10" x 39.41" (3840 x 2593 x 1000mm) 188.97" x 125.71" x 39.41" (4800 x 3193 x 1000mm)	146lb (66.4kg) 212lb (96.4kg) 263lb (119.5kg)	315lb (143.2kg) 560lb (254.5kg) 875lb (397.7kg)		
LEDMTL-2x2 LEDMTL-3x3 LEDMTL-4x4	96.06" x 102.10" x 39.41" (2440 x 2593 x 1000mm) 144.08" x 102.10" x 39.41" (3660 x 2593 x 1000mm) 192.12" x 125.71" x 39.41" (4880 x 3193 x 1000mm)	139lb (63.2kg) 221lb (100.5kg) 336lb (152.7kg)	400lb (181.8kg) 900lb (409.1kg) 1600lb (727.3kg)		


Package Specifications

UNIVERSAL SPACER*	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
LEDUNVSPACER3	5.00" x 4.375" x 38.00" (127 x 111 x 965mm)	9.5lb (4.3kg)	735029359333	Universal Spacer Kit	1
PRECONFIGURED MODELS *Universal spacer (LEDUNVSPACER3) is sold separately.					
LEDMTS-4x4 LEDMTS-5x5 LEDMTS-6x6 LEDMTS-8x8	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	174lb (79.1kg) 198lb (90.0kg) 261lb (118.6kg) 378lb (171.8kg)	735029357933 735029357940 735029357957 735029357964	dvLED Display Mount, Subframe and Casters	1
LEDMTM-3x3 LEDMTM-4x4 LEDMTM-5x5	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	176lb (80.0kg) 242lb (110.0kg) 293lb (133.2kg)	735029357971 735029357988 735029357995		
LEDMTL-2x2 LEDMTL-3x3 LEDMTL-4x4	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm) VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	169lb (76.8kg) 251lb (114.1kg) 366lb (166.4kg)	735029358008 735029358015 735029358022		

Accessories

LEDTK Models: SEAMLESS Connect Universal dvLED Trim Kit

All dimensions = inch (mm)



MODEL NO.	DIMENSION "A"	DIMENSION "B"	DIMENSION "C"	DIMENSION "D"
LEDMTS-4x4	39.41" (1000mm)	96.06" (2440mm)	102.10" (2593mm)	7.60" (193mm)
LEDMTS-5x5		120.08" (3050mm)	102.10" (2593mm)	
LEDMTS-6x6		144.08" (3660mm)	102.10" (2593mm)	
LEDMTS-8x8		192.12" (4880mm)	125.71" (3193mm)	
LEDMTM-3x3		113.38" (2880mm)	102.10" (2593mm)	
LEDMTM-4x4		151.08" (3840mm)	102.10" (2593mm)	
LEDMTM-5x5		188.97" (4800mm)	125.71" (3193mm)	
LEDMTL-2x2		96.06" (2440mm)	102.10" (2593mm)	
LEDMTL-3x3		144.08" (3660mm)	102.10" (2593mm)	
LEDMTL-4x4		192.12" (4880mm)	125.71" (3193mm)	

LEDMTS-6x6 Shown      Dimension B as fully expanded.      Horizontal Extrusions can be cut to length as needed.

Architect Specifications

The SEAMLESS Connect Universal dvLED Cart/Trolley shall be a Peerless-AV LEDMT models and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit [peerless-av.com](http://peerless-av.com) to see the complete line of AV solutions from Peerless-AV, including outdoor displays, kiosks, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

**Peerless-AV**  
2300 White Oak Circle  
Aurora, IL 60502  
USA  
**(800) 865-2112**  
**(630) 375-5100**

**Peerless-AV EMEA**  
Unit 2 Curo Park  
Frogmore, St. Albans  
Hertfordshire, AL2 2DD  
United Kingdom  
**+44 (0) 1923 200 100**

**Peerless-AV B.V.**  
Papendorpseweg 75  
3528 BJ Utrecht  
The Netherlands  
**+31 (0) 70 770 8037**

**Peerless-AV Latin America**  
Av. de las Industrias 413  
Parque Industrial Escobedo  
General Escobedo, N.L.,  
México, 66062  
**+52 (81) 8384-8300**

**peerless-AV®**  
Driving Technology Through Innovation