




SEAMLESS CONNECT


Universal dvLED Floor-to-Wall Mount

The SEAMLESS Connect Universal Series by Peerless-AV® offers a versatile lineup of substructures for environments where wall mounting is not an option. Purpose-built for dvLED video walls and all-in-one displays, the SEAMLESS Connect Universal Floor-to-Wall Mount supports full system weight with strength and stability. Its slim, space-saving design simplifies setup and speeds up installation. The quad post leveling base and wall tie-back brackets ensure a plumb structure and a perfectly flat mounting surface for dvLED installation - Ideal for corporate lobbies, retail, hospitality, showrooms, events, and entertainment spaces.

- Adaptable solution for installations where mounting direct to a wall is not an option
- Slim, space saving design fits neatly in any installation environment
- Lightweight aluminum frame makes shipping, handling and installation easier
- Anodized aluminum finish for a durable, decorative appearance
- Modular design provides scalability in installation configuration and size
- Integrated cable management protects, contains and conceals cables for a clean, professional installation
- Compatible with all SEAMLESS Connect Universal mounts, offering peace of mind when designing solutions or if project specs change
- Optional trim kit accessory (LEDTK) offers compatibility with most displays




Contact a Peerless-AV® Sales Representative for the current list of compatible latching dvLED display models.




Cart/Trolley
LEDMTS-6X6 shown



Floor Stand
LEDFSS-6X6 shown



Bolt-Down Pedestal
LEDBDS-6X6 shown



Floor-to-Ceiling Mount
LEDFCS-6X6 shown

Please visit peerless-av.com/en-us/patents for patent information.

Model Numbers

WARRANTY: 5 Years

LED FW Models SEAMLESS Connect Universal dvLED Floor-to-Wall Mount

LED FWS – for dvLED displays up to 610mm wide

LED FWM – for dvLED displays up to 960mm wide

LED FWL – for dvLED displays up to 1220mm wide

Product Specifications

UNIVERSAL SPACER*	DIMENSIONS (W x H x D)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS
LEDUNVSPACER3	55.55" x 3.94" x 2.50" (1411 x 100 x 64mm)	4lb (1.8kg)	NA	Powder Coat	Black
PRECONFIGURED MODELS <i>Product height is dependent on the display height.</i>					
LED FWS-4x4	96.06" x 95.47"-96.45" x 8.21"-13.21" (2440 x 2425-2450 x 208-333mm)	109lb (49.5kg)	400lb (181.8kg)	Anodized, Powder Coat	Black
LED FWS-5x5	120.08" x 95.47"-96.45" x 8.21"-13.21" (3050 x 2425-2450 x 208-333mm)	133lb (60.5kg)	625lb (284.1kg)		
LED FWS-6x6	144.09" x 95.47"-96.45" x 8.21"-13.21" (3660 x 2425-2450 x 208-333mm)	177lb (80.5kg)	900lb (409.1kg)		
LED FWS-8x8	192.13" x 119.09"-120.07" x 8.21"-13.21" (4880 x 3025-3050 x 208-333mm)	402lb (182.7kg)	1600lb (727.3kg)		
LED FWM-3x3	113.38" x 95.47"-96.45" x 8.21"-13.21" (2880 x 2425-2450 x 208-333mm)	112lb (50.9kg)	315lb (143.2kg)		
LED FWM-4x4	151.18" x 95.47"-96.45" x 8.21"-13.21" (3840 x 2425-2450 x 208-333mm)	160lb (72.7kg)	560lb (254.5kg)		
LED FWM-5x5	188.97" x 119.09"-120.07" x 8.21"-13.21" (4800 x 3025-3050 x 208-333mm)	305lb (138.6kg)	875lb (397.7kg)		
LED FWL-2x2	96.06" x 95.47"-96.45" x 8.21"-13.21" (2440 x 2425-2450 x 208-333mm)	105lb (47.7kg)	400lb (181.8kg)		
LED FWL-3x3	144.09" x 95.47"-96.45" x 8.21"-13.21" (3660 x 2425-2450 x 208-333mm)	170lb (77.3kg)	900lb (409.1kg)		
LED FWL-4x4	192.13" x 119.09"-120.07" x 8.21"-13.21" (4880 x 3025-3050 x 208-333mm)	391lb (177.7kg)	1600lb (727.3kg)		


Package Specifications

UNIVERSAL SPACER*	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
LEDUNVSPACER3	5.00" x 4.375" x 38.00" (127 x 111 x 965mm)	9.5lb (4.3kg)	735029359333	Universal Spacer Kit	1
PRECONFIGURED MODELS <i>*Universal spacer (LEDUNVSPACER3) is sold separately.</i>					
LED FWS-4x4	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	139lb (63.2kg)	735029358336	dvLED Display Mount, Subframe, Floor Anchors and Wall Attach Bracket	1
LED FWS-5x5	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	163lb (74.1kg)	735029358343		
LED FWS-6x6	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	207lb (94.1kg)	735029358350		
LED FWS-8x8	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	432lb (196.4kg)	735029358367		
LED FWM-3x3	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	142lb (64.5kg)	735029358374		
LED FWM-4x4	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	190lb (86.4kg)	735029358381		
LED FWM-5x5	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	335lb (152.3kg)	735029358398		
LED FWL-2x2	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	135lb (61.4kg)	735029358404		
LED FWL-3x3	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	200lb (90.9kg)	735029358411		
LED FWL-4x4	VARIABLES x VARIABLES x 72.375" (VARIABLES x VARIABLES x 1838mm)	421lb (191.4kg)	735029358428		

Accessories

LEDTK Models: SEAMLESS Connect Universal dvLED Trim Kit

All dimensions = inch (mm)



LED FWS-6x6 Shown

Dimension B as fully expanded.

Horizontal Extrusions can be cut to length as needed.

MODEL NO.	DIMENSION "A"	DIMENSION "B"	DIMENSION "C"
LED FWS-4x4	8.21" - 13.21" (208-333mm)	96.06" (2440mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWS-5x5		120.08" (3050mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWS-6x6		144.09" (3660mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWS-8x8		192.13" (4880mm)	119.09" (3025mm) - 120.07" (3050mm)
LED FWM-3x3		113.38" (2880mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWM-4x4		151.18" (3840mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWM-5x5		188.97" (4800mm)	119.09" (3025mm) - 120.07" (3050mm)
LED FWL-2x2		96.06" (2440mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWL-3x3		144.09" (3660mm)	95.47" (2425mm) - 96.45" (2450mm)
LED FWL-4x4		192.13" (4880mm)	119.09" (3025mm) - 120.07" (3050mm)

Architect Specifications

The SEAMLESS Connect Universal dvLED Floor-to-Wall Mount shall be a Peerless-AV LEDFW models and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor displays, kiosks, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV
2300 White Oak Circle
Aurora, IL 60502
USA
(800) 865-2112
(630) 375-5100

Peerless-AV EMEA
Unit 2 Curo Park
Frogmore, St. Albans
Hertfordshire, AL2 2DD
United Kingdom
+44 (0) 1923 200 100

Peerless-AV B.V.
Papendorpseweg 75
3528 BJ Utrecht
The Netherlands
+31 (0) 70 770 8037

Peerless-AV Latin America
Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo, N.L.,
México, 66062
+52 (81) 8384-8300

