



Key Features

- AMD FreeSync™ premium and NVIDIA G-sync Compatible for smooth gameplay
- 240Hz refresh rate for smooth gameplay
- FHD resolution for incredible detail
- Rapid 1ms MPRT for crisp image
- Flexible connectivity with dual HDMI and DisplayPort input



Product Description

The ViewSonic VX2429 is a 24" FHD monitor featuring HDMI and DisplayPort. It is also equipped with SuperClear® IPS technology, delivering stunning image quality with brilliant visual performance. While the VX2429's high 240Hz refresh rate supports smooth visuals and minimal input lag. You may think it doesn't get better than this, but it does. Not only will you get the job done — be it grueling gaming sessions, video and photo editing, or office assignments — you'll be working on a sleek, beautifully designed monitor.



1. DC
2. HDMI 2.1 x 2
3. DP 1.4
4. Audio Out(Earphone)
5. VESA Wall Mount Compatible (100x100mm)

Visit Us

www.viewsonic.com

DISPLAY

Display Size (in.):	24
Viewable Area (in.):	23.8
Panel Type:	IPS Technology
Resolution:	1920 x 1080
Resolution Type:	FHD (Full HD)
Static Contrast Ratio:	1,000:1 (typ)
Dynamic Contrast Ratio:	80M:1
High Dynamic Range:	HDR10
Light Source:	LED
Brightness:	250 cd/m² (typ)
Colors:	16.7M
Color Space Support:	8 bit (6 bit + FRC)
Aspect Ratio:	16:9
Response Time (MPRT):	1ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	200
Variable Refresh Rate Technology:	FreeSync Premium
Low Blue Light:	Software solution
Flicker-Free:	Yes
Color Gamut:	NTSC: 72% size (Typ) sRGB: 102% size (Typ)
Pixel Size:	0.275 mm (H) x 0.275 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080
PC Operating System:	Windows 11 certified; macOS tested
Mac® Resolution (min):	1920x1080

CONNECTOR

3.5mm Audio Out:	1
HDMI 2.0 (with HDCP 2.2):	2
DisplayPort:	1
Power in:	3-pin Socket (IEC C14 / CEE22)

AUDIO

Internal Speakers:	2Watts x2
--------------------	-----------

POWER

Eco Mode (Conserve):	16W
Eco Mode (optimized):	18W
Consumption (typical):	20W
Consumption (max):	22W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	Internal Power Supply

ADDITIONAL HARDWARE

Kensington Lock Slot:	1
-----------------------	---

CONTROLS

Physical Controls:	Joystick key: Up, Right, Down, Left, Center; Shortcut, Power
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	100 x 100 mm
------------------	--------------

INPUT SIGNAL

Frequency Horizontal:	30 ~ 230KHz
Frequency Vertical:	48 ~ 200Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v2.0), PCI-E - DisplayPort (v1.4)
---------------	--

ERGONOMICS

Tilt (Forward/Back):	-3° / 21°
----------------------	-----------

WEIGHT (IMPERIAL)

Net (lbs):	6.9
Net Without Stand (lbs):	6.3
Gross (lbs):	10.5

WEIGHT (METRIC)

Net (kg):	3.1
Net Without Stand (kg):	2.8
Gross (kg):	4.8

DIMENSIONS (IMPERIAL) (WXHxD)

Packaging (in.):	23.6 x 16.1 x 5.5
Physical (in.):	21.26 x 15.96 x 8.39
Physical Without Stand (in.):	21.26 x 12.46 x 1.89

DIMENSIONS (METRIC) (WXHxD)

Packaging (mm):	600 x 410 x 140
Physical (mm):	540.13 x 405.26 x 213.19
Physical Without Stand (mm):	540.13 x 316.37 x 48.1

GENERAL

Regulations:	cSGSUS, FCC-B, ICES003, CEC, TUV S-Mark, NOM, Mexico Energy
PACKAGE CONTENTS:	VX2429 x1, 3-pin Plug (IEC C13 / CEE22) x1, HDMI Cable (v1.4; Male-Male) x1, Quick Start Guide x1
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market