


BU113G2

CamStream 4K

Pro Camera, Pro Creation



Camera and Camcorder Video Capture

Ultra-Low Latency Audio & Video in Sync

Tripod-Mountable Design

Plug and Play

4K60

Record 4K60 Video

Compact and On-the-Go

Multiple Video Format Record

RGB24

True Color Images

Your Camera Is More Than Just A Photo Tool

- **Transform Your Camera into a Pro Streaming Device:** Elevates your DSLR, mirrorless, action cam, or camcorder for high-performance streaming and recording.
- **Ultra-Smooth 4K60 Streaming:** Supports up to 4K at 60fps and 1080p at 240fps, ensuring stunning clarity and smooth motion.
- **Real-Time, Low-Latency Performance:** Near-zero latency for an instant, professional production experience.
- **Vibrant and True-to-Life Colors:** Preserves full color space and image quality, ensuring rich and accurate visuals.
- **Universal Compatibility:** Works seamlessly with popular streaming, recording, and video conferencing software.




©2025 by AVerMedia Technologies, Inc. All right reserved. AVerMedia is a registered trademark of AVerMedia Technologies, Inc. All other trademarks belong to their respective companies.

AVerMedia

CamStream 4K

BU113G2



Specifications:

- **Interface:** USB 3.2 (Gen 1) Type-C (plug and play, UVC)
- **Input:** HDMI 2.0
- **Output:** USB 3.2 (Gen 1) Type-C
- **Max Supported Resolutions (Video Input):** 3840x2160p60 HDR/2560x1440p144 HDR/ 1920x1080p240 HDR
- **Max Recording Resolution:**

  MJPEG: 3840x2160p60, 3440x1440p60, 2560x1440p144, 2560x1080p144, 1920x1080p144

  NV12: 3840x2160p30, 2560x1440p60, 2560x1080p60, 1920x1080p120, 1280x1024P60

  YUY2: 2560x1080p60, 1920x1200p60, 1920x1080p60, 1280x1024p60

  P010(HDR10) (Windows only): 1920x1080p60, 1280x1024p60

  RGB24 (Windows only): 1920x1080p60, 1280x1024p60
- **Dimension (W x D x H):** 80.8 x 40.8x 14.5 mm (3.18 x 1.61 x 0.57 in.)
- **Weight:** 26 g (0.92 oz.)

System Requirements:

Windows® 10 x64 or later

- Desktop: Intel® Core™ i5-6XXX/ AMD Ryzen™ 3 XXX or above + NVIDIA® GTX 1060 / AMD RX 5700 or above
- Laptop: Intel® Core™ i7-7700HQ + NVIDIA® GTX 1050Ti or above
- 8 GB RAM recommended (Dual-channel)

macOS 14/ 15 or later

- Apple M1 or 3.6 GHz quad-core Intel Core i7
- Apple M1 or Radeon Pro 555 with 2 GB of VRAM
- 16 GB of 2400 MHz DDR4 memory
- For 4K60 MJPEG capture, requires M1 Ultra / M2 Ultra or above
- HDR capture and RGB24 format are not available for macOS

iPadOS 17 or later

Type	Color	EAN	UPC
WW	Black	4711289505563	850070892179
WW	White	4711289505440	850070892186
AMZ	Black	4711289505433	850070892131
AMZ	White	4711289505518	850070892148
JP	Black	4711289505396	--
JP	White	4711289505570	--

What's in the box:

- CamStream 4K (BU113G2)
- USB Type-C to Type-A Cable (1 m/3.28 ft.)
- 1/4” Cold/Hot Shoe Mount (Adapter)
- Quick Start Guide

Package Dimensions:

- Single Box (L x W x D): 173 x 116.5 x 48 mm (6.81 x 4.59 x 1.89 in.)
- Carton (L x W x H): 36.5 x 24.9 x 38.2 cm (14.37 x 9.80 x 15.04 in.)

Shipping Weights:

- Single Box: 215 g (0.47 lbs.)
- Carton: 6.68 Kg (14.73 lbs.)
- 28pcs per carton

- **Specifications are subject to change without prior notice.**
- **Please visit the AVerMedia official website at www.avermedia.com for the latest information.**

©2025 by AVerMedia Technologies, Inc. All right reserved. AVerMedia is a registered trademark of AVerMedia Technologies, Inc. All other trademarks belong to their respective companies.