

  
Copilot+PC

## SPECIFICATIONS

|                            |                                                                                                                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Operating System</b>    | Windows 11 Home<br>Windows 11 Pro - MSI recommends Windows 11 Pro for business                                                                                                                                                    |
| <b>CPU</b>                 | Intel® Core™ Ultra 9 Processor 288V<br>Intel® Core™ Ultra 7 Processor 258V<br>Intel® Core™ Ultra 5 Processor 226V                                                                                                                 |
| <b>Chipset</b>             | Intel® SoC                                                                                                                                                                                                                        |
| <b>Graphics</b>            | Intel® Arc™ Graphics 140V (integrated, Ultra 7 above)<br>Intel® Arc™ Graphics 130V (integrated, Ultra 5)                                                                                                                          |
| <b>Storage</b>             | 1x M.2 2280 SSD                                                                                                                                                                                                                   |
| <b>I/O (Front)</b>         | 2x USB 10Gbps Type A<br>1x Mic-in / Headphone-out combo<br>1x Micro-SD Card Reader<br>1x Power Button with Fingerprint Security Design<br>1x Copilot Button                                                                       |
| <b>I/O (Rear)</b>          | 2x Thunderbolt 4 (DP 2.1 alt-mode up to 4K@60Hz / PD-out 15W / One of TBT supports PD-in up to 100W)<br>2x USB 2.0 Type A<br>2x RJ45 (2.5G)<br>1x HDMI out (supports 4K @60Hz as specified in HDMI 2.1 & supports MSI Power Link) |
| <b>I/O (SIDE)</b>          | 1x Kensington Lock<br>1x External Power Switch Pin Header                                                                                                                                                                         |
| <b>Bluetooth</b>           | 5.3 (for AX211) / 5.4 (for BE201)                                                                                                                                                                                                 |
| <b>LAN</b>                 | 2x Intel® I226V (2.5G)                                                                                                                                                                                                            |
| <b>Wireless LAN</b>        | Intel® Wi-Fi 6E AX211 / Intel® Wi-Fi 7 BE201 Support                                                                                                                                                                              |
| <b>KEYBOARD / MOUSE</b>    | Optional                                                                                                                                                                                                                          |
| <b>AC Adapter / PSU</b>    | 120W                                                                                                                                                                                                                              |
| <b>Dimension (WxDxH)</b>   | 135.60 x 132.50 x 50.10 mm (5.34 x 5.22 x 1.97 inch)                                                                                                                                                                              |
| <b>WEIGHT (N.W./ G.W.)</b> | 0.667 Kg (1.47 lbs) / 1.682 Kg (3.71 lbs)                                                                                                                                                                                         |
| <b>Certificates</b>        | FCC, CB/CE, UL & CUL, VCCI, RCM                                                                                                                                                                                                   |

## FEATURES

-  **Copilot+ PC**  
Deliver unique Copilot+ PC experiences to enhance productivity and computational power for AI applications.
-  **Thunderbolt™ 4**  
Up to 40Gb transmission speed and 2X PCI-e bandwidth than previous generation, brings fast speed and versatility, offering a fast and simple level of connection for work.
-  **Matrix Display**  
Supports the Multi-display mode and the surround view mode
-  **Fingerprint Security Design**  
Unlock the device quickly and securely with a one-touch fingerprint button for easy access.
-  **Dual 2.5G LAN**  
Dual 2.5G network solution for Intranet and Internet offers a smooth experience for effective network connection.
-  **Built-in Mic and Speaker**  
Using the built-in Mic and speaker for voice control in AI applications.
-  **Power Meter**  
Power Meter enables one-click power saving, carbon emission calculation & electricity cost estimation.
-  **dTPM 2.0 Support**  
dTPM 2.0 design secures your confidential data with encryption keys.
-  **VESA Mountable**  
To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

## CONNECTIONS



- 1x Mic-in / Headphone-out combo
- 2x USB 10Gbps Type A
- 1x Micro-SD Card Reader
- 1x External Power Switch Slot
- 2x USB 2.0 Type A
- 1x Thunderbolt 4 (DP 2.1 alt-mode up to 4K@60Hz / PD-out 15W)
- 2x RJ45 LAN (2.5G)
- 1x HDMI out (supports 4K @60Hz as specified in HDMI 2.1 & supports MSI Power Link)
- 1x DC Jack
- 1x Thunderbolt 4 (DP 2.1 alt-mode up to 4K@60Hz / PD-out 15W / supports PD-in up to 100W)
- 1x Kensington Lock Slot