

# ThinkPad T14s Gen 6 (AMD)

Powered by next-generation AMD Ryzen AI 7 PRO 360 processors, the ThinkPad T14s Gen 6 is optimized to elevate productivity and unleash creative expression. It is the first ever x86 next-gen AI PC that offers 50 TOPS and puts you in command of AI processing power. Encased in a sleek and stylish in Eclipse Black chassis, with a refined interior and 16:10 display, this intelligent device offers both brains and beauty. Plus, the redesigned exhaust, new 3M optical solutions and industry-first accessibility features, sets a new standard for the modern workforce.



**Redefining possibilities with powerful performance and groundbreaking on-device AI**

The impressive 14" WUXGA panel with 88% screen-to-body ratio is made even more extraordinary by 3M's optical solution that amplifies screen brightness to 400nit while lowering power consumption. With the 5MP camera, you'll also be seen by others with crisp, unyielding clarity—elevating every collaboration.

Connectivity will never be an obstruction. With Qualcomm Wi-Fi 7, this device enhances wireless performance and helps professionals stay productive with stable network connectivity, low latency and great bandwidth.

Stacked with up to 12 high-performance "Zen 5" cores, the next-generation AMD Ryzen 7 AI PRO processor offers unparalleled responsiveness and multitasking prowess.

## Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Co2 Offset Service

- Hardware transaction facilitates easy Co2 offset integration.
- Co2 compensation covers production to lifecycle.
- Co2 Offset contributions can be easily tracked and confirmed.

## Accessories

### ThinkPad Professional 14-inch Topload Gen 2

- Sleek and Sophisticated Design
- Weather-Proof Security with Waterproof Zippers
- Easily Locate Essentials



PN: 4X41M69796

### Thinkpad Universal USB-C Smart Dock

- Access to multiple 4K monitors, and blazing-fast data transfers with USB-C and USB-A
- Supports both Thunderbolt™ 3 and 4, USB 4™ and USB-C, and extended compatibility with a wide range of brands and Multi-OS notebooks
- 11+ expansion possibilities in a single quick-release cable for maximum efficiency



PN: 40B20135XX

# ThinkPad T14s Gen 6 (AMD)

## Performance

### Processor

AMD Ryzen AI 7 300 Series Processor

### AI PC Category

Copilot+ PC

### AI Performance

Up to 72 overall TOPS

### Operating System\*

Windows 11 Pro  
Windows 11 Home  
Fedora Linux  
Ubuntu Linux  
Linux

### NPU

Integrated AMD Ryzen AI, up to 50 TOPS

### Graphics

AMD Radeon 880M (integrated)

### Memory

32GB LPDDR5x-7500, soldered  
64GB LPDDR5x-7500, soldered

### Storage<sup>1 2</sup>

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

<sup>1</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings.

<sup>2</sup>The max storage capacity is only technical readiness and may be different from current Lenovo storage offerings.

### Audio\*

High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Atmos  
Dual-microphone array, 360° far-field, Dolby Voice

### Camera\*

5.0MP + IR discrete, with privacy shutter, temporal noise reduction

### Battery<sup>3</sup>

58Wh (up to 17.1 hr) battery, Rapid Charge

<sup>3</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

### Power Adapter\*

65W USB-C adapter, PD 3.0  
65W USB-C slim adapter, PD 3.0  
65W USB-C slim GaN adapter, PD 3.0

## Design

### Display<sup>4</sup>

14" WUXGA (1920x1200) IPS Anti-glare 16:10  
- 400nits, 100% sRGB, low power  
- 400nits, 45% NTSC, touch, Eyesafe, 3M DBEF5

<sup>4</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

### Keyboard

6-row, spill-resistant, Copilot key, backlight

### Touchpad

TrackPoint and glass-like Mylar surface 3-button  
Trackpad  
61 x 115 mm (2.40 x 4.53 inches)

### Dimensions<sup>5</sup>

313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

<sup>5</sup>The system dimensions may vary depending on configurations.

### Weight<sup>6</sup>

Starting at 1.30 kg (2.86 lbs)

<sup>6</sup>The system weight is approximate and may vary depending on configurations

### Color

Black

### Case material

Carbon fiber hybrid (top), aluminium (bottom)

## Connectivity

### WLAN + Bluetooth\*<sup>7</sup>

Qualcomm Wi-Fi 7 NCM825, 802.11be, Bluetooth 5.3

<sup>7</sup>Bluetooth 5.3 operation requires Windows 11.

### WWAN\*

5G Sub-6 GHz with embedded eSIM

### Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)  
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On  
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1  
1x HDMI 2.1, up to 4K/60Hz  
1x Headphone / microphone combo jack (3.5mm)  
1x Smart card reader\*  
1x Nano-SIM card slot (WWAN support models)\*

### Docking

Docking support via Thunderbolt or USB-C

## Security & Privacy

### Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0  
Kensington Nano Security Slot  
Smart card reader, supports ISO 7816 and EMV\*  
Touch style MOC fingerprint reader\*  
Camera privacy shutter  
IR camera for Windows Hello (facial recognition)  
Ultrasonic Human Presence Detection

## Certifications

### Green Certifications<sup>8 9 10</sup>

ENERGY STAR 8.0  
EPEAT Gold Registered  
ErP Lot 6/26  
TCO Certified 10.0  
RoHS compliant

<sup>8</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>9</sup>EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

<sup>10</sup>EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

### Other Certifications

Eyesafe Certified 2.0\*  
MIL-STD-810H