

ThinkPad L13 2-in-1 Gen 6 (Intel)

Introducing the new-gen ThinkPad engineered for modern business professionals who demand performance, portability, and reliability. Whether you're multitasking across demanding applications or collaborating in real-time, the Intel® U Series Core™ Ultra 5 / 7 Processors ensure seamless responsiveness and intelligent workload distribution. Complementing the robust CPU is integrated Intel® Graphics, offering crisp visuals and smooth performance for everyday computing tasks, virtual meetings, presentations, and creative workloads without lag. With support for up to 1TB M.2 2242 SSD storage, the laptop ensures lightning-fast boot times, rapid file access, and ample space for datasets and critical software.



**Redefining possibilities with
powerful performance and
groundbreaking on-device AI**


The 2W dual Dolby Atmos® stereo speakers deliver high-fidelity audio that enhances everything from video conferencing to multimedia presentations. Complementing the audio experience is a dual-microphone array with Elevoc Voice technology, designed to intelligently filter out background noise while capturing crystal-clear voice, making remote meetings and collaborative work effortless.

On the security front, discrete TPM 2.0 securely encrypts sensitive data and authenticates hardware integrity. For physical security, the 2.5 x 6 mm Kensington® Nano Security Slot™ provides a robust, compact anchor point for locking down your device in shared workspaces.

Experience unparalleled productivity with the high-capacity 54.7Wh rechargeable Li-ion battery that delivers long-lasting performance, enabling you to power through extended work sessions and intensive meetings without constantly searching for a power outlet.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Wired VoIP Headset

- Optimized audio comfort
- Lightweight design
- Seamless management



PN: Teams : 4XD1M45626, UC : 4XD1M39028

Lenovo Go USB-C Wireless Mouse

- Ergonomically designed ambidextrous mouse with Villi painted grip and wireless connection via USB-C dongle
- Silent buttons with 2-way scroll wheel (up/down), programmable Utility Button on the side
- Default functions optimized for Teams calls, can be configured through Lenovo Go Central Software



PN: 4Y51C21216

ThinkPad L13 2-in-1 Gen 6 (Intel)

Performance

Processor

Intel U Series Core Ultra 5/7 Processor (Series 2)

AI PC Category

AI PC

Operating System*

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Ubuntu Linux

NPU

Integrated Intel AI Boost, up to 12 TOPS

Graphics

Intel Graphics (integrated)

Memory¹

16GB LPDDR5x-7467, soldered
32GB LPDDR5x-7467, soldered

¹Installed memory is actually LPDDR5x-8533 but run as LPDDR5x-7467 due to platform limitation.

Storage²

One drive, up to 1TB M.2 2242 SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, Elevoc Voice

Camera*

Front HD 720p, with privacy shutter
Front HD 720p, with privacy shutter; rear 5.0MP
Front 5.0MP + IR discrete, with privacy shutter,
Front 5.0MP + IR discrete, with privacy shutter; rear 5.0MP

Battery³

41Wh or 54.7Wh battery, up to 11.7 hr, Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display⁴

13.3" WUXGA (1920x1200) IPS ARAS 16:10
- 400nits, 100% sRGB, 60Hz, Eyesafe, touch

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Multimode

Laptop, tent, stand and tablet modes supported by 360° hinge

Pen*

Lenovo Integrated Pen*

Keyboard

6-row, spill-resistant, Copilot key, optional backlight

Touchpad

TrackPoint, Mylar or glass-like Mylar surface TrackPad
60 x 115 mm (2.36 x 4.53 inches)

Dimensions⁵

299.0 x 215.0 x 12.0/15.7 (front/rear), 18.35 (maximum) mm;
11.77 x 8.46 x 0.47/0.62 (front/rear), 0.72 (maximum) inches

⁵The system dimensions may vary depending on configurations.

Weight⁶

Starting at 1.30 kg (2.87 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Grey

Case material

Aluminium (top), PC + 40% GF (bottom)

Connectivity

WLAN + Bluetooth*

Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3
Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

WWAN*

4G LTE CAT6 with embedded eSIM*

NFC

Near Field Communication*

Ports

2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 and DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Manageability

System Management*

Intel vPro Enterprise*

Certifications

Green Certifications^{7 8 9}

EPEAT Gold Registered
ENERGY STAR 9.0
ErP Lot 6/26
TCO Certified 10.0
RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

⁹EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

Other Certifications

Eyesafe Certified 2.0*