

ThinkPad X13 Gen 6 AMD

Powered by up to Intel® Core Ultra 7 processors, this laptop delivers lightning-fast responsiveness ideal for professionals juggling demanding workloads while on the move. Whether editing presentations, rendering visuals with the optional Intel® Arc™ 140T GPU, or managing real-time data models, it ensures seamless execution. Its integrated Intel® AI Boost accelerates smart applications, perfect for predictive analytics, language processing, and adaptive workflows, while up to 32GB of DDR5x memory allows for smooth multitasking, whether in a café or between meetings.



**Redefining possibilities with
powerful performance and
groundbreaking on-device AI**

The 13.3" WUXGA display with 100% sRGB brings visuals to life, ideal for creatives and consultants working on visuals or reports. With optional multi-touch support and a suite of ports including USB-A, USB-C®, DisplayPort™, and HDMI, plus optional Wi-Fi® 7, staying connected is effortless.

Secure and reliable, it offers up to 2TB of SSD storage for large project files and instant access. Discrete TPM 2.0 and an optional touch-style fingerprint reader keep sensitive data protected.

Engineered for crystal-clear virtual meetings, this laptop features Dolby Voice audio and a dual-microphone array to capture every nuance. The discrete 5.0MP + IR fixed-focus camera offers sharp, secure visuals with a convenient privacy shutter.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

Lenovo Go Wired Speakerphone

- Microsoft Teams certified, omni-directional far-field 2x microphones array
- Portable plug-and-play capabilities and effortless PC UC support
- Comes with intuitive control with volume wheel, tactile keys, and readable LEDs



PN: 4XD1C82055, GXD1C82051

ThinkPad X13 Gen 6 AMD

Performance

Processor

AMD Ryzen AI 5/7 300 Series Processor

AI PC Category

Copilot+ PC

AI Performance

Up to 66 overall TOPS

Operating System*

Windows 11 Pro
Windows 11 Home
Fedora Linux
Ubuntu Linux
Linux

NPU

Integrated AMD Ryzen AI, up to 50 TOPS

Graphics

AMD Radeon 840M (integrated)
AMD Radeon 860M (integrated)

Memory

16GB LPDDR5x-8000, soldered
32GB LPDDR5x-8000, soldered

Storage^{1 2}

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

²The max storage capacity is only technical readiness and may be different from current Lenovo storage offerings.

Audio*

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, Dolby Voice

Camera*

5.0MP, with privacy shutter, temporal noise reduction
5.0MP + IR discrete, with privacy shutter, Computer Vision on ISP, temporal noise reduction

Battery³

41Wh or 54.7Wh battery, up to 14.88 hr, Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C nano GaN adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display⁴

13.3" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 100% sRGB, Eyesafe
- 400nits, 100% sRGB, touch, Eyesafe

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant, Copilot key, optional backlight

Touchpad

TrackPoint and glass-like Mylar surface 3-button
Trackpad
74.3 x 115 mm (2.93 x 4.53 inches)

Dimensions⁵

Starting at 299.3 x 207 x 9.85/12.95 (front/rear), 17.75 (maximum) mm;
11.78 x 8.15 x 0.39/0.51 (front/rear), 0.70 (maximum) inches

⁵The system dimensions may vary depending on configurations.

Weight⁶

Models with 41Wh battery: starting at 953 g (2.10 lbs)
Models with 54.7Wh battery: starting at 988 g (2.18 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Black

Case material

CFRP (top), aluminium (bottom)
CFRP (top), magnesium (bottom)
Carbon fiber hybrid (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*⁷

MediaTek Wi-Fi 7 MT7925, 802.11be, Bluetooth 5.4

⁷Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

WWAN*

4G LTE CAT6 with embedded eSIM
5G Sub-6 GHz with embedded eSIM

NFC

Near Field Communication*

Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*
Computer Vision-based User Presence Sensing on ISP*

Manageability

System Management*

DASH*

Certifications

Green Certifications^{8 9 10}

ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 10.0
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

¹⁰EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

Eyesafe Certified 2.0
MIL-STD-810H