

# ThinkPad L13 Gen 6 (Intel)

Built for mobility and designed with versatility in mind, this laptop leverages up to Intel® U Series Core Ultra 7 Processor to streamline heavy workloads while keeping energy use in check. With integrated Intel® AI Boost delivering up to 12 TOPS, it powers intelligent applications that support content creation, data analysis, and real-time collaboration with remarkable efficiency. Intel® graphics ensure fluid visuals for everything from video editing to presentations, while up to 32GB DDR5x memory enables seamless multitasking across design software, spreadsheets, and research tools without performance dips.



**Redefining possibilities with  
powerful performance and  
groundbreaking on-device AI**

Its vibrant 13.3" WUXGA display with 100% sRGB color accuracy offers crisp, true-to-life visuals ideal for creatives and presenters alike. The optional multi-touch screen enhances interactivity, while a range of modern ports and up to Wi-Fi® 7 ensure uninterrupted connectivity everywhere.

With up to 1TB SSD storage, professionals can carry large files and boot applications quickly. Discrete TPM 2.0 and a touch style fingerprint reader safeguard sensitive data, securing remote work for consultants, executives, and field-based teams.

Optimized for seamless web conferencing, it features a dual-microphone array that captures clear voice input and an HD 720p camera with fixed focus. A built-in privacy shutter ensures visual security between meetings and video calls.

## Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

### Lenovo Essential Wireless Combo Keyboard & Mouse Gen 2

- Embrace the freedom of a clutter-free and cable-free work setup.
- Ergonomically sculpted cups and low-profile island keys for maximum comfort.
- A 2.4 MHz receiver for a seamless keyboard and mouse connection.



PN: 4X31N50708 – 4X31N50757

# ThinkPad L13 Gen 6 (Intel)

## Performance

**Processor**  
Intel U Series Core Ultra 5/7 Processor (Series 2)

**AI PC Category**  
AI PC

**Operating System\***  
Windows 11 Pro  
Windows 11 Home  
Windows 11 Home Single Language  
Ubuntu Linux

**NPU**  
Integrated Intel AI Boost, up to 12 TOPS

**Graphics**  
Intel Graphics (integrated)

**Memory<sup>1</sup>**  
16GB LPDDR5x-7467, soldered  
32GB LPDDR5x-7467, soldered

<sup>1</sup>Installed memory is actually LPDDR5x-8533 but run as LPDDR5x-7467 due to platform limitation.

**Storage<sup>2</sup>**  
One drive, up to 1TB M.2 2242 SSD

<sup>2</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings.

**Audio\***  
High Definition (HD) Audio  
Stereo speakers, 2W x2, Dolby Atmos  
Dual-microphone array, Elevoc Voice

**Camera\***  
HD 720p, with privacy shutter  
5.0MP + IR discrete, with privacy shutter, temporal noise reduction

**Battery<sup>3</sup>**  
41Wh or 54.7Wh battery, up to 12.8 hr, Rapid Charge

<sup>3</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

**Power Adapter\***  
65W USB-C adapter, PD 3.0  
65W USB-C slim GaN adapter, PD 3.0

## Design

**Display<sup>4</sup>**  
13.3" WUXGA (1920x1200) IPS Anti-glare 16:10  
- 400nits, 45% NTSC 3M DBEF5  
- 400nits, 100% sRGB, Eyesafe  
- 400nits, 100% sRGB, Eyesafe, touch

<sup>4</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

**Keyboard**  
6-row, spill-resistant, Copilot key, optional backlight

**Touchpad**  
TrackPoint, Mylar or glass-like Mylar surface TrackPad  
60 x 115 mm (2.36 x 4.53 inches)

**Dimensions<sup>5</sup>**  
299.0 x 215.0 x 12.0/15.7 (front/rear), 18.95 (maximum) mm;  
11.77 x 8.46 x 0.47/0.62 (front/rear), 0.75 (maximum) inches

<sup>5</sup>The system dimensions may vary depending on configurations.

**Weight<sup>6</sup>**  
Starting at 1.21 kg (2.67 lbs)

<sup>6</sup>The system weight is approximate and may vary depending on configurations

**Color**  
Black

**Case material**  
Aluminium (top), PC + 40% GF (bottom)

## Connectivity

**WLAN + Bluetooth\***  
Intel Wi-Fi 6E AX211, 802.11ax, Bluetooth 5.3  
Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

**WWAN\***  
4G LTE CAT6 with embedded eSIM\*

**NFC**  
Near Field Communication\*

**Ports**  
2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On  
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 and DP 2.1  
1x HDMI 2.1, up to 4K/60Hz  
1x Headphone / microphone combo jack (3.5mm)  
1x Smart card reader\*  
1x Nano-SIM card slot (WWAN support models)\*

**Docking**  
Docking support via Thunderbolt

## Security & Privacy

**Security**  
Discrete TPM 2.0  
Kensington Nano Security Slot  
Smart card reader\*  
Touch style MOC fingerprint reader\*  
Camera privacy shutter  
IR camera for Windows Hello (facial recognition)\*

## Manageability

**System Management\*<sup>7</sup>**  
Intel vPro Enterprise\*

<sup>7</sup>Intel vPro offers a superset of DASH's defined capabilities.

## Certifications

**Green Certifications<sup>8 9 10</sup>**  
EPEAT Gold Registered  
ENERGY STAR 9.0  
ErP Lot 6/26  
TCO Certified 10.0  
RoHS compliant

<sup>8</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>9</sup>EPEAT registration and ENERGY STAR certification are optional and only available on the models with preload OS.

<sup>10</sup>EPEAT is registered where applicable, please see [epeat.net](https://epeat.net) for registration status by country.

**Other Certifications**  
Eyesafe Certified 2.0\*  
MIL-STD-810H