

PERFORMANCE

Display Size	23.8"
View Area	527x296.5 mm
Panel	In-Plane Switching
Backlight	WLED
Aspect Ratio	16:9
Resolution	1920x1080
Pixel Pitch	0.2745x0.2745 mm
Dot / Pixel Per Inch	92 dpi
View Angle (H / V)	178° / 178°
Response Time	4ms (Extreme mode) / 6ms (Normal mode)
Color Support	16.7 Million
Refresh Rate	100Hz
Brightness	250 cd/m ²
Contrast Ratio	1300:1
Color Gamut	99% sRGB
Screen Surface Treatment	Anti-glare
Curvature	Flat Panel
Camera	None
Microphone	None
Speakers	2Wx2
Power Consumption (Typical / Maximum)	13W / 24W
Power Adapter	Integrated
Touchscreen	None

Smart System	None
DESIGN	
Stand	Tilt, Swivel, Pivot, Height Adjust Stand
Case Color	Raven Black
Side Bezel Width	2.0 mm
Mounting	Supports VESA mount 100 x 100 mm
ThinkCentre® M Series Support	Tiny Support

Pen	None
Dimensions (WxDxH)^[1]	- Lowest Position 539.8 x 178.6 x 343.4 mm (21.25 x 7.03 x 13.52 inches) - Highest Position 539.8 x 178.6 x 498.4 mm (21.25 x 7.03 x 19.62 inches) - Head Only 539.8 x 44.0 x 325.7 mm (21.25 x 1.73 x 12.82 inches)
Packaging Dimensions (WxDxH)	710.0 x 111.0 x 421.0 mm (27.95 x 4.37 x 16.57 inches)
Weight^[2]	- Monitor With Stand 4.5 kg (9.9 lbs) - Monitor Head Only 2.9 kg (6.4 lbs)

Packaging Weight	6.4 kg (14.1 lbs)
-------------------------	-------------------

CONNECTIVITY

USB Port	None
Video Connector	1x HDMI® 1.4, 1x DP 1.2, 1x VGA
Network Connectivity	None

SERVICE

Base Warranty	3-year
----------------------	--------

CERTIFICATIONS

Environmental Certification	ENERGY STAR® Certified, TCO 10.0, TCO Edge 2.1, EPEAT™ Gold, RoHS, EU Energy Efficiency Level (Level-C)
------------------------------------	---

Ergonomic Certification	TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free
Sync Technology	None
Special Features	Natural Low Blue Light

SOFTWARE

Operating System	Support Windows® 10, Windows® 11
-------------------------	----------------------------------

ACCESSORIES

Video Cables	HDMI® cable
---------------------	-------------

MODEL

Announce Date	: 2025-06-09	Region	: NA
EAN / UPC / JAN	: 0198156755797 / 198156755797 / None		



Product image is a sample, it may not match the real color of this model

Note:

[1] The system dimensions may vary depending on configurations.
 [2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.
 · California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Technician Installed Customer
- Onsite Support
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference