



GHSP8824

8K 4-Port HDMI Splitter

Coming Soon!

The GHSP8824 8K 4-Port HDMI Splitter is the perfect solution for connecting a single HDMI source to four displays, delivering stunning 8K resolution at 60Hz. With support for HDR and RGB4:4:4 color sampling, you'll enjoy lifelike images with exceptional clarity and detail.



Features

- One HDMI Input, splits signal to four HDMI outputs up to 8K@60Hz resolution
- HDMI 2.1 Compliant and backwards compatible
- HDCP 2.3, 2.1 and 1.4 compliant
- Supports HDR
- Supports RGB4:4:4 Color Sampling
- Data rate up to 48Gbps
- Small, compact design in metal housing.

Requirements

Display:

- Up to four 8K Displays with HDMI Input

Media Source:

- 1 HDMI Output

Package Contents

- 1x GHSP8824
- 1x HDMI Cable (6ft)
- 1x Power Adapter



Specifications

MODEL	GHSP8824
Video connections	
Input	1 x Female HDMI Type A 19-Pin
Output	4 x Female HDMI Type A 19-Pin
LEDs	
Input	1
Output	4
Power On	1
Housing	
Case	Metal
Warranty	1-Year
Video Resolution	Up to 8K@60Hz
Environment	
Humidity	10-80%
Operation Temperature	32~122°F
Storage Temperature	-4~140°F
Power	
Voltage	5 V
Amps	1A
Connectors	
Video Input	Female HDMI Type A 19 Pin
Video Output	Female HDMI Type A 19 Pin
DIMENSIONS	GHSP8824
Unit Dimensions	
Height	0.74 in (1.9 cm)
Length	2 in (5.1 cm)
Width	4.8 in (12.2 cm)
Unit Package Dimensions	
Height	6.2 in (16 cm)
Length	4.3 in (11cm)
Width	2.6 in (6.6 cm)
Master Carton	
Height	16.1 in (41 cm)
Length	9.2 in (23.5 cm)
Width	7 in (18 cm)
Master Carton Qty.	12
Weight	



DIMENSIONS	GHSP8824
Master Carton Wt.	12.1 lbs (5.5 kgs)
Unit Pack Wt.	0.9 lbs (0.4 kgs)
Unit Wt.	0.35 lbs (0.16 kgs)