


InFlex 215

Touchscreen

InFlex Touchscreen Monitors are designed with modern compact and elegant styling with support for a variety of accessory modules such as camera, bar code scanner and card readers etc. Flex monitors support single USB-C computer installation for a slim all-in-one application with the Lenovo Chromebox micro and a single power supply. Flex screens and UNITY modules are well-suited for point-of-sale, self-service, signage and hospitality applications.

Features

- Hardened glass for easy cleaning, optically bonded
- VESA 100 by 100 using M4 x 10 mm
- Lightweight plastic chassis construction
- 10 Point PCAP touch
- PTD USB-C "Power to Device" feature
- Slot for Lenovo Chromebox Micro & Flexbox
- 4 x Unity micro-USB slots for accessories



InFlex 215

Touchscreen

Monitor Specifications

Display Size	21.5 Inches	Resolution	1920 x 1080 pixels
Brightness	400 cd/m2	Viewing Area	594 x 336.3 mm
Aspect Ratio	16:9	Contrast Ratio	3000:1
Viewing Angle	89/89/89/89 degrees	Pixel Pitch	0.248 x 0.248 mm
Refresh Rate	60 Hz	Response Time	12 ms
Color Support	16.7 million	Touch Technology	10 Point PCAP 10 ms response
Protective Glass	Hardened optically bonded	Led Backlight	30 000 h
Mtbf	50 000 h		

Unit Specifications

Power Consumption	25W	Power Input	Barrel 5.5 x 2.5 mm 19V 4.74A
Mounting Options	VESA 100 by 100	Touch Interface	USB
Video Ports	USB-C 3.1 Gen 2, DP, HDMI 1.4	Data Ports	USB-C and USB-A
OSD Settings	OSD Touch and Buttons	Unit Color	Black
Unit Dimensions	501 x 306 x 41 mm	Unit Weight	3.65 kg
Operating Temperature	0°C to 50°C / 32°F to 122°F	Operating Humidity	20% to 90%, relative
Shipping Dimensions	616 x 414 x 140 mm	Shipping Weight	5.5 kg
Storage Temperature	-20°C to 60°C / -4°F to 140°F	Storage Humidity	5% to 90%, relative

In The Box

Unit	inFLEX215	Video Cables	HDMI, 1.5 m
Touch Cables	USB-A to USB-A 1.5 m	Power Supply	AC 110 - 240V to DC 19V
Power Cable	US C5 power cable 1.5 m		

Certifications

Certification Unit	CE, FCC, ROHS	Certification Power Supply	CE, FCC, ROHS, UL
--------------------	---------------	----------------------------	-------------------

Warranty

Warranty Standard	3-year return to depot	Warranty Extended	Optional
-------------------	------------------------	-------------------	----------