

ThinkPad E14 Gen 7 (Intel)

Powered by up to Intel® U or H Series Core Ultra 7 Processor, this laptop is engineered for high-efficiency performance on the move. Whether it's an architect modeling render-heavy visuals or a financial analyst multitasking across large datasets, up to 64GB DDR5 memory ensures fluid responsiveness. Creative professionals can rely on optional Intel® Arc™ 140T graphics to finesse visual compositions, while integrated Intel® AI Boost, delivering up to 13 TOPS, accelerates real-time translation, transcription, and predictive workflows—all without compromising battery life or mobility.



Redefining possibilities with powerful performance and groundbreaking on-device AI

The entry-level ThinkPad, E Series features the famous keyboard and trackpoint, and is MIL-SPEC tested ensuring the build quality for which ThinkPad is renowned.

Its vibrant 14" display with up to 2.8K resolution captures even the subtlest color gradients, ideal for content reviews and visual design tasks. The optional touch film enhances interactive use in tight spaces. Meanwhile, Wi-Fi® 6E keeps remote collaboration seamless, and versatile connectivity.

To protect sensitive project files and communications, the device offers hardware-level security via discrete TPM 2.0, an optional touch-style fingerprint reader built into the power button, and an optional IR camera for facial authentication.

Performance remains a top priority for mobile users, and with up to an Intel® Core Ultra 7 Processor, integrated AI Boost, and up to 64GB DDR5 memory, this device delivers power to handle demanding tasks on the go.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Expedited Depot Repair Warranty

- Speeds up standard 7-10 business-day depot service
- Get the repaired system back in 3 to 4 business days
- Avoid unplanned expenses when you need a faster repair

Accessories

Lenovo Wireless Stereo Headset

- 60-hour music playback with quick-charge convenience
- Intuitive on-ear buttons and flip microphone
- Dual-device pairing with Bluetooth® 5.3 reliability



PN: Part Numbers (PN) Headset: 4XD1Q30302 Earcups: 4XD1M80021

ThinkPad Bluetooth Silent Mouse

- Left/Right hand, easy-to-carry low profile mouse
- Switch between 2 devices with dual-host Bluetooth 5.0 connectivity
- 2-way scrolling with on-the-fly DPI adjustment (2400, 1600, 800)



PN: With Battery : 4Y50X88822 Without Battery : 4Y50X88823



ThinkPad E14 Gen 7 (Intel)

Performance

Processor

Intel U Series Core 3 Processor (Series 1) - Raptor Lake (RPL)
Intel U or H Series Core 5/7 Processor (Series 2) - Raptor Lake (RPL)
Intel U or H Series Core Ultra 5/7 Processor (Series 2) - Arrow Lake (ARL)
Intel V Series Core Ultra 5/7 Processor (Series 2) - Lunar Lake (LNL)

AI PC Category*

AI PC (Arrow Lake)
Copilot+ PC (Lunar Lake)

Operating System*

Windows 11 Pro or Home
Ubuntu Linux

NPU

Integrated Intel AI Boost, up to 47 TOPS

Graphics^{1 1}

Intel Graphics (integrated)
Intel Arc 130T GPU (integrated)
Intel Arc 140T GPU (integrated)
Intel Arc Graphics 130V (integrated)
Intel Arc Graphics 140V (integrated)

¹Intel Arc graphics only available on select H-series Intel Core Ultra processor powered systems with at least 16GB of system memory in a dual-channel configurations, otherwise it will function as Intel Graphics.

¹Intel Arc graphics only available on select H-series Intel Core Ultra processor powered systems with at least 16GB of system memory in a dual-channel configurations, otherwise it will function as Intel Graphics.

Memory^{2 2}

Raptor Lake and Arrow Lake:
Up to 64GB DDR5-5200 or DDR5-5600, 2x SO-DIMM
Lunar Lake:
16GB LPDDR5x-8533 MoP memory, soldered
32GB LPDDR5x-8533 MoP memory, soldered

²The max memory is based on the test results with current Lenovo memory offerings.

²The max memory is based on the test results with current Lenovo memory offerings.

Storage^{3 4 3}

Raptor Lake and Arrow Lake:
Up to two drives, 2x M.2 SSD
M.2 2242 SSD up to 1TB
M.2 2280 SSD up to 1TB
Lunar Lake:
One drive, up to 1TB M.2 2280 SSD

³The storage capacity supported is based on the test results with current Lenovo storage offerings.

⁴The system supports dual SSD via two M.2 slots, but Lenovo only offers one M.2 2242 SSD configuration and M.2 2280 slot for user self-extension.

³The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*

High Definition (HD) Audio
audio by HARMAN stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, smart noise-cancelling

Camera*

HD 720p, with privacy shutter
FHD 1080p + IR hybrid, with privacy shutter, temporal noise reduction
5.0MP, with privacy shutter, temporal noise reduction

Battery^{5 4}

48Wh or 64Wh battery, up to 14.75 hr
48Wh battery supports Rapid Charge Pro

⁵Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

⁴Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display^{6 5}

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 300nits, 45% NTSC, 60Hz
- 300nits, 45% NTSC, 60Hz, touch
- 300nits, 100% sRGB, 60Hz, Eyesafe
14" 2.8K (2880x1800) IPS Anti-glare 16:10
- 400nits, 100% sRGB, 120Hz, Eyesafe

⁶IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

⁵IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Screen-to-Body Ratio

90%

Keyboard

6-row, spill-resistant, Copilot key, optional backlight

Touchpad

TrackPoint and Mylar surface TrackPad
60 x 115 mm (2.36 x 4.53 inches)

Dimensions^{7 6}

Models with aluminium (top) and aluminium (bottom)
313 x 220.3 x 10.1/15.25 (front/rear), 19.7 (maximum) mm
12.32 x 8.67 x 0.40/0.60 (front/rear), 0.78 (maximum) inches

Models with aluminium (top) and PC-ABS (bottom)
313 x 220.3 x 10.1/15.25 (front/rear), 20.5 (maximum) mm
12.32 x 8.67 x 0.40/0.60 (front/rear), 0.81 (maximum) inches

⁷The system dimensions may vary depending on configurations.

⁶The system dimensions may vary depending on configurations.

Weight^{8 7}

Raptor Lake and Arrow Lake: starting at 1.34 kg (2.95 lbs)
Lunar Lake: starting at 1.32 kg (2.91 lbs)

⁸The system weight is approximate and may vary depending on configurations

⁷The system weight is approximate and may vary depending on configurations

Color

Black

Case material

Aluminium (top), aluminium (bottom)
Aluminium (top), PC-ABS (bottom)

Connectivity

Ethernet*

Gigabit onboard Ethernet

WLAN + Bluetooth*

802.11ax (Wi-Fi 6 or Wi-Fi 6E), Bluetooth 5.2 or 5.3
802.11be (Wi-Fi 7), Bluetooth 5.4
Up to MediaTek Wi-Fi 7 MT7925, 802.11be, Bluetooth 5

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2025 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.