


Lenovo ThinkVision S27-4e Monitor

Discover new peaks of productivity.



Vibrant and color-rich visuals

Get more work done with sharp and clear images on the 27-inch FHD monitor. Enjoy a smooth working experience with the 100Hz high refresh rate, which can be manually adjusted to 48Hz to further match your workflow.



Seamless and intuitive connectivity

Connect to any peripheral with ease. Enjoy connectivity and compatibility with all your devices using the VGA and HDMI ports, unlocking greater productivity for your workflows.



Environmentally friendly design

Make an environment-friendly choice with this monitor that limits environmental impact by coming packaged with recyclable cushion, and meets major international standards for energy efficiency with its ENERGY STAR 8.0 and EPEAT® Gold certifications.

Lenovo ThinkVision S27-4e Monitor

Display

Panel Size
27-inch

Screen Dimensions
607.1 mm x 354.1 mm

Panel Type
3-sided NearEdgeless,
In-Plane Switching

Active Area
597.9 mm x 336.3 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.3114 mm x 0.3114 mm

**Dot/Pixel Per Inch
(DPI/PPI)**
82

**Viewing Angle
(H x V @ CR 10:1)**
178° / 178°

Response Time (G to G)
4ms (Extreme Mode),
6ms (Normal Mode)

Refresh Rate
100Hz

Brightness
300 cd/m²

Contrast Ratio (Typical)
1500:1

**Dynamic Contrast Ratio
(Typical)**
3M:1

**Color Gamut
(Coverage Ratio)**
99% sRGB (CIE 1931)

Color Support (Typical)
16.7 Million

Color Depth
8-bit (6+FRC)

Anti-glare
Yes

Connectivity

Video Signal
1 x HDMI 1.4¹
1 x VGA

Power

**Power Consumption
(Typ. / Max.)**
17.3W / 19.8W

**Power Consumption
Sleep/Off Mode**
< 0.5W

**Power Consumption
Switch-Off Mode**
< 0.3W

**ENERGY STAR Power
Consumption (Pon/E_{TEC})**
15.0W / 52.1kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back)
-5° / 22°

VESA Mount Capability
Yes (100 x 100 mm)

**ThinkCentre M Series
Tiny Support**
Yes, by ThinkCentre Tiny
Mounting Kit²
(PN: 4XF0N03161)

Kensington Nano Security Slot
Yes (2.5 mm x 6 mm)

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top)
2.0 mm

Bezel Width (Bottom)
21.7 mm

Dimension & Weight

**Size Packed
(W x D x H, mm/inch)**
690.0 x 111.0 x 525.0 mm
27.17 x 4.37 x 20.67 inches

**Size Unpacked w/ Stand
(W x D x H, mm/inch)**
611.9 x 210.0 x 443.5 mm
24.09 x 8.27 x 17.46 inches

**Size Unpacked w/o Stand
(Head Only)
(W x D x H, mm/inch)**
611.9 x 44.4 x 366.5 mm
24.09 x 1.75 x 14.43 inches

Weight Packed (kg / lbs.)
EPS : 5.8 kg / 12.8 lbs.
Pulp : 6.4 kg / 14.1 lbs.

Weight Unpacked (kg / lbs.)
4.1 kg / 9.0 lbs.

Weight (Head Only) (kg / lbs.)
3.7 kg / 8.2 lbs.

What's in the Box

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (1.8 m)

HDMI Cable (Cable Length)
1 x HDMI 1.4 Cable (1.8 m)

Quick Setup Guide
Yes

Certification

ENERGY STAR Certification
Yes

EPEAT
Gold

Windows Certification
Windows 10, Windows 11

EU Energy Level Certification
Yes (Level-D)

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Flicker Free
Yes

**TÜV Rheinland Low Blue Light
(Hardware Solution)**
Yes



Windows



¹ Supports 1920 x 1080 @ 100Hz as specified in HDMI 1.4. | ² Sold separately. Need to assemble ThinkCentre Tiny Mounting Kit (PN: 4XF0N03161) to support Tiny PC installation.

© 2025 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A. Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others. Specifications may vary depending upon region.