



Lenovo ThinkVision E27-40 Monitor

# Made for the contemporary work environment!



**Smooth and sharp images from any angle**

Experience smooth, clear, and distortion-free visuals. The 27-inch ThinkVision 100Hz refresh rate In-Plane Switching monitor delivers better image quality and highly accurate colors from any viewing angle while reducing flicker for an extra-comfortable viewing experience.



**Excellent audio quality and connectivity**

Connect to your devices with ease using the VGA, HDMI, and DP ports. Featuring built-in 2 x 2W speakers, this monitor offers a convenient, all-in-one setup that simplifies your audio needs.



**Efficient cable management and ergonomics**

The versatile stands offer a full range of adjustments—lift, tilt, pivot, and swivel—allowing you to create the perfect screen position for every task. Keep your desk organized with the stand's improved cable management.

## Lenovo ThinkVision E27-40 Monitor

### Display

**Panel Size**  
27-inch

**Screen Dimensions**  
606.9 mm x 347.3 mm

**Panel Type**  
3-sided NearEdgeless  
In-Plane Switching

**Active Area**  
597.9 mm x 336.3 mm

**Backlight**  
WLED

**Aspect Ratio**  
16:9

**Resolution**  
1920 x 1080

**Pixel Pitch**  
0.3114 mm x 0.3114 mm

**Dot/Pixel Per Inch  
(DPI/PPI)**  
82

**Viewing Angle  
(H x V @ CR 10:1)**  
178° / 178°

**Response Time (G to G)**  
4ms (Extreme Mode),  
6ms (Normal Mode)

**Refresh Rate**  
100Hz

**Brightness**  
300 cd/m<sup>2</sup>

**Contrast Ratio (Typical)**  
1500:1

**Dynamic Contrast Ratio  
(Typical)**  
3M:1

**Color Gamut  
(Coverage Ratio)**  
99% sRGB (CIE 1931)

**Color Support (Typical)**  
16.7 Million

**Color Depth**  
8-bit (6+FRC)

**Anti-glare**  
Yes

### Connectivity

**Video Signal**  
1 x HDMI 1.4<sup>1</sup>  
1 x DP 1.2  
1 x VGA

### Multimedia

**Integrated Speakers**  
Yes (2x2W)

### Special Features

**Natural Low Blue Light**  
Yes

### Power

**Power Consumption (Typ. / Max.)**  
16.3W / 34.0W

**Power Consumption Sleep/Off Mode**  
< 0.5W

**Power Consumption Switch-Off Mode**  
< 0.3W

**ENERGY STAR Power Consumption  
(Pon / ETEC)**  
12.6W / 39.2kWh

**Power Supply**  
Internal

**Voltage Required**  
AC 100 to 240 V (50-60Hz)

### Mechanical

**Tilt Angle (Front / Back)**  
-5° / 22°

**Swivel Angle (Left / Right)**  
-360° / 360°

**Lift (Max. Range)**  
155 mm

**Pivot**  
-90° / 90°

**VESA Mount Capability**  
Yes (100 x 100 mm)

### ThinkCentre M Series Tiny Support

Yes, by Tiny VESA Mount II<sup>2</sup>  
(PN: 4XFON03161)

**Kensington Lock Slot**  
Yes (2.5 mm x 6 mm and 3 mm x 7 mm)

**Cable Management**  
Yes

**Bezel Color**  
Raven Black

**Bezel Width (Side)**  
2.3 mm

**Bezel Width (Top)**  
2.6 mm

**Bezel Width (Bottom)**  
20.5 mm

### Dimension & Weight

**Size Packed  
(W x D x H, mm/inch)**  
695.0 x 155.0 x 447.0 mm  
27.36 x 6.10 x 17.60 inches

**Size Unpacked w/ Stand  
(Highest Position)  
(W x D x H, mm/inch)**  
613.1 x 220.0 x 538.5 mm  
24.14 x 8.66 x 21.20 inches

**Size Unpacked w/ Stand  
(Lowest Position)  
(W x D x H, mm/inch)**  
613.1 x 220.0 x 383.5 mm  
24.14 x 8.66 x 15.10 inches

**Size Unpacked w/o Stand  
(Head Only) (W x D x H, mm/inch)**  
613.1 x 40.4 x 366.4 mm  
24.14 x 1.59 x 14.43 inches

**Weight Packed (kg / lbs.)**  
EPS : 7.9 kg / 17.4 lbs.  
Pulp : 8.5 kg / 18.7 lbs.

**Weight Unpacked (kg / lbs.)**  
6.2 kg / 13.7 lbs.

**Weight (Head Only) (kg / lbs.)**  
4.0 kg / 8.8 lbs.

### What's in the Box

**Monitor with Stand**  
Yes

**Power Cable (Cable Length)**  
1 x Power Cable (1.8 m)

**HDMI Cable (Cable Length)**  
1 x HDMI 1.4 Cable (1.8 m)

**Quick Setup Guide**  
Yes

**Tools**  
4 x Screws

### Certification

**ENERGY STAR Certification**  
Yes

**TCO**  
10

**TCO Edge**  
2.1

**EPEAT**  
Gold

**Windows Certification**  
Windows 10, Windows 11

**EU Energy Level Certification**  
Yes (Level-D)

**China Energy Efficiency Standard**  
Tier 1

**TÜV Rheinland Flicker Free**  
Yes

**TÜV Rheinland Low Blue Light  
(Hardware Solution)**  
Yes



<sup>1</sup> Supports 1920 x 1080 @ 100Hz as specified in HDMI 1.4. | <sup>2</sup> Sold separately. Need to assemble ThinkCentre Tiny VESA Mount II (PN: 4XFON03161) to support Tiny PC installation.