





Lenovo ThinkVision S22-4e Monitor

Powers peak professional productivity!



Good visual fidelity for great productivity

- **Clear content**
Experience clear content with 99% sRGB color space coverage and 1300:1 contrast ratio.
- **Smooth visuals**
Enjoy a smooth working experience with the 100Hz high refresh rate, which can be manually adjusted to 48Hz to further match your workflow.
- **Eye-strain-reducing technology**
Get work done without suffering from any eye fatigue, leveraging the monitor's low blue light hardware and flicker-free technology, which guarantees reduced blue light emissions without color distortion.

Ergonomics and connectivity at its core

- **Accessible connectivity**
Connecting to your work computer is easy using the monitor's HDMI and VGA ports.
- **Designed for ergonomics**
Elevate your working experience with a comfortable posture and clean desk with the monitor's easy-to-assemble tilt stand (-5°/+22°) and Tiny PC-supported VESA mount.

Prioritizes sustainability

- Designed to work for you and the environment, the monitor comes in recyclable cushion packaging and has EPEAT Gold and ENERGY STAR 8.0 certifications, making it environmentally friendly.

Lenovo ThinkVision S22-4e Monitor

Display

Panel Size
21.5-inch

Screen Dimensions
484.5 mm x 284.5 mm

Panel Type
3-sided NearEdgeless,
In-Plane Switching

Active Area
476.1 mm x 267.8 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.2479 mm x 0.2479 mm

**Dot/Pixel Per Inch
(DPI/PPI)**
102

**Viewing Angle
(H x V @ CR 10:1)**
178° / 178°

Response Time
4ms (Extreme Mode),
6ms (Normal Mode)

Refresh Rate
100Hz

Brightness
250 cd/m²

Contrast Ratio (Typical)
1300:1

**Dynamic Contrast Ratio
(Typical)**
3M:1

**Color Gamut
(Coverage Ratio)**
99% sRGB (CIE 1931)

Color Support (Typical)
16.7 Million

Color Depth
8-bit (6+FRC)

Anti-glare
Yes

Connectivity

Video Signal
1 x HDMI 1.4¹
1 x VGA

Special Features

Natural Low Blue Light
Yes

Power

**Power Consumption
(Typ. / Max.)**
10.5W / 20.0W

**Power Consumption
Sleep/Off Mode**
< 0.5W

**Power Consumption
Switch-Off Mode**
< 0.3W

**ENERGY STAR Power
Consumption (Pon/E_{TEC})**
9.9W / 33.2kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60Hz)

Mechanical

Tilt Angle (Front / Back)
-5° / 22°

VESA Mount Capability
Yes (100 x 100 mm)

ThinkCentre M Series Tiny Support
Yes, by ThinkCentre Tiny
VESA Mount II² (PN: 4XFON03161)

Kensington Lock Slot
Yes (3 mm x 7 mm)

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top)
2.0 mm

Bezel Width (Bottom)
21.2 mm

Dimension & Weight

**Size Packed
(W x D x H, mm/inch)**
563.0 x 119.0 x 350.0 mm
22.17 x 4.69 x 13.78 inches

**Size Unpacked w/ Stand
(W x D x H, mm/inch)**
489.3 x 174.0 x 379.4 mm
19.26 x 6.85 x 14.94 inches

**Size Unpacked w/o Stand
(Head Only)
(W x D x H, mm/inch)**
489.3 x 52.7 x 296.8 mm
19.26 x 2.07 x 11.69 inches

Weight Packed (kg / lbs.)
4.1 kg / 9.0 lbs.

Weight Unpacked (kg / lbs.)
2.8 kg / 6.2 lbs.

Weight (Head Only) (kg / lbs.)
2.5 kg / 5.5 lbs.

What's in the Box

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (1.8 m)

HDMI Cable (Cable Length)
1 x HDMI 1.4 Cable (1.8 m)

Quick Setup Guide
Yes

Certification

ENERGY STAR Certification
Yes

EPEAT
Gold

Windows Certification
Windows 10, Windows 11

EU Energy Level Certification
Yes (Level-C)

China Energy Efficiency Standard
Tier 2

TÜV Rheinland Flicker Free
Yes

**TÜV Rheinland Low Blue Light
(Hardware Solution)**
Yes



¹ Supports 1920 x 1080 @ 100Hz as specified in HDMI 1.4. | ² Sold separately. Need to assemble ThinkCentre Tiny VESA Mount II (PN: 4XFON03161) to support Tiny PC installation.