

1.5m (5ft) USB4 Cable, 80Gbps, USB-IF Certified USB-C Cable, 240W PD, 8K 120Hz/4K 240Hz DP2.1 DP80, TPE Jacket, Thunderbolt 4 Compatible - Black USB-C Cord

**Product ID:** CC150CM80GUSB4CABLE



Connect reliably to USB Type-C (USB4), Thunderbolt, and PCIe-enabled devices, delivering up to 80Gbps, 8K/4K video, and 240W of Power Delivery. Each connector is laser-etched with USB4 specifications, an exclusive feature that eliminates guesswork, confirms compatibility, and verifies full USB4 performance.

Safely power high-performance laptops and USB-C devices with up to 240W of Extended Power Range (EPR) Power Delivery 3.1 using a compatible USB-C docking station or wall charger. An integrated E-marker chip ensures accurate power negotiation for stable, consistent charging. Ideal for professional laptops such as Apple M-series Pro/Max MacBooks

Enable full-speed, spec-compliant USB4 performance with a USB-IF Certified cable designed for demanding power, data, and display applications. Rigorously tested to meet electrical and mechanical standards, it ensures reliable interoperability, signal integrity, and consistent operation across a wide range of USB-C devices. The USB4 cable features shielded 30/34AWG coaxial wire for optimal EMI protection.

Drive sharp 8K 120Hz video or dual 4K 120Hz displays via DisplayPort 2.1 Alt Mode with DSC, HBR3, and HDR10+ support. Suitable for professional 3D rendering, high-frame-rate video, and bandwidth-intensive visual workflows. This USB4 cable integrates seamlessly with USB-C or Thunderbolt 4 docks, and maintains backward compatibility with a wide range of resolutions and refresh rates. The 1.5-meter (5-foot) cable length is useful for desk workstations and portable USB-C monitors.

## Certifications, Reports and Compatibility



## Applications

- Designed for seamless operation with USB-C or Thunderbolt 4 docking stations
- Drive sharp 8K 120Hz video or support dual 4K 120Hz UHD displays
- Transfer data at 80 Gbps speeds and 240W of power over a USB4 connection
- Power and charge USB4/USB-C, and Thunderbolt devices

## Features

- **Versatile USB4 Performance**: Enhance productivity with full USB4 capabilities, featuring 8K 120Hz video, 80Gbps, and 240W charging over a single connection; The 1.5-meter (5-foot) cable length is ideal for desk workstations and portable USB-C displays
- **Safe, Certified Compatibility**: Trust this USB-IF Certified Cable to ensure peak USB4 performance in critical workflows, with E-marker chip for safe and consistent Power Delivery to USB-C devices; Certified cables guarantee full USB4 and backward compatibility
- **Identify Specs Instantly**: Swiftly identify this USB4 cable with Quick ID connector markings; The eco-friendly TPE jacket is flexible and durable, designed to withstand tight bends and is fully RoHS-compliant; Shielded 30/34AWG coaxial wire minimizes EMI
- **Ultra-Fast Docking Cable**: Designed to work seamlessly with USB-C or Thunderbolt 4 docks; Drive an 8K 120Hz or dual 4K 120Hz displays via DP2.1 (DP80) w/DSC for professional 3D imaging; Ideal for high-performance laptops such as Apple M-series Pro/Max MacBooks
- **The IT Pro's Choice**: Our USB-C cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

|                           |                                |
|---------------------------|--------------------------------|
| Warranty                  | Lifetime                       |
| Active or Passive Adapter | Passive                        |
| Connector Plating         | Nickel                         |
| Cable Jacket Material     | TPE - Thermoplastic Elastomers |
| Cable Shield Material     | Aluminum-Mylar Foil with Braid |

---

### Performance

|                             |                 |
|-----------------------------|-----------------|
| Video Revision              | DisplayPort 2.1 |
| Maximum Data Transfer Rate  | 80 Gbps         |
| Maximum Digital Resolutions | 8K 120Hz        |

|                                 |                       |                                         |
|---------------------------------|-----------------------|-----------------------------------------|
|                                 | Audio Specifications  | DisplayPort - 32 Channel Audio          |
|                                 | Type and Rate         | USB4 - 80Gbps                           |
| <b>Connector(s)</b>             |                       |                                         |
|                                 | Connector A           | 1 - USB4 - 80Gbps                       |
|                                 | Connector B           | 1 - USB4 - 80Gbps                       |
| <b>Power</b>                    |                       |                                         |
|                                 | Power Delivery        | 240W                                    |
|                                 | Input Current         | 5A                                      |
| <b>Environmental</b>            |                       |                                         |
|                                 | Operating Temperature | 0&degC to 60&degC (32&degF to 140&degF) |
|                                 | Storage Temperature   | -20C to 60C (-4F to 140F)               |
|                                 | Humidity              | 40 - 65% RH                             |
| <b>Physical Characteristics</b> |                       |                                         |
|                                 | Color                 | Black                                   |
|                                 | Connector Style       | Straight                                |
|                                 | Wire Gauge            | 30/34 AWG                               |
|                                 | Material              | Santoprene - Thermoplastic Rubber (TPE) |
|                                 | Cable Length          | 1.7 ft [0.5 m]                          |
|                                 | Cable OD              | 0.2 in [5.0 mm]                         |
|                                 | Product Length        | 1.6 ft [0.5 m]                          |
|                                 | Product Width         | 0.5 in [12.8 mm]                        |
|                                 | Product Height        | 0.3 in [6.9 mm]                         |
|                                 | Weight of Product     | 2.4 oz [69 g]                           |
| <b>Packaging Information</b>    |                       |                                         |
|                                 | Package Length        | 3.1 in [8.0 cm]                         |

|                           |                  |
|---------------------------|------------------|
| Package Width             | 9.1 in [23.0 cm] |
| Package Height            | 1.2 in [3.0 cm]  |
| Shipping (Package) Weight | 3.7 oz [105.0 g] |

---

#### What's in the Box

|                     |                       |
|---------------------|-----------------------|
| Included in Package | 1 - USB4 80Gbps Cable |
|---------------------|-----------------------|

---

#### Warranty Information

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

***\*Product appearance and specifications are subject to change without notice.***