



SPECIFICATIONS

Panel Size	26.5"
Active Display Area (mm)	590.42 (H) x 333.72 (V)
Curvature	Flat
Panel Type	QD-OLED
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2292 (H) x 0.2292 (V)
Aspect Ratio	16:9
Brightness (nits)	SDR: 200 HDR: 400 (Typ.)
Contrast Ratio	1500000:1 (Typ.)
DCR	N/A
Signal Frequency	384~386.9 KHz(H) / 48 ~ 240 Hz(V)
ACTIVATED RANGE	48~240Hz
Refresh Rate	240Hz
Response time	0.03ms (GtG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	HDR Ready
Video ports	2x HDMI™ 2.1 (FRL 10G) (WQHD@240Hz) 1x DisplayPort 1.4a (HBR3)
USB ports	N/A
Audio ports	1x Headphone-out
Viewing Angle	178°(H) / 178°(V)
Adobe RGB / DCI-P3 / sRGB	98% / 99% / 138% (CIE1976 Standard)
Surface Treatment	Anti-Reflection
Display Colors	1.07B, 10 bits
Console Mode	Supported Resolution & Refresh Rate: 1080p: 60Hz and 120Hz 1440p: 60Hz and 120Hz HDMI™ CEC: Supported VRR: PS5 and Xbox Supported
Power Type	Internal Power Board
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 ~ 110 mm

FEATURES



QD-OLED Display

MSI's renowned QD tech, combined with the latest OLED panel technology, these displays exhibit the best picture quality and incredible high contrast when gaming.



240Hz High Refresh Rate

Experience smooth gaming with a blazing-fast refresh rate, providing you with the upper hand in fast-moving games.




Fastest 0.03 Response time

Response time is much faster and smoother than conventional LCD displays. The response time is up to 0.03 ms GtG exceeds the most mainstream refresh rates requirements.



OLED Care 2.0

MSI has developed a more advanced version to provide several care services and significantly reduce the chances of OLED screen aging.




Graphene film with Custom Heatsink

Graphene film and customized heatsink designs, the synergy between these two elements enables monitor to operate without an active cooling fan, achieving a fanless design. This ensures efficient and silent heat dispersion, further extending the panel's lifespan.

Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Dimension with Stand (W x D x H)	609.3 x 241.9 x 427.1 mm (23.9 x 9.5 x 16.8 inch)
Dimension without Stand (W x D x H)	609.3 x 67.1 x 356.2 mm (23.9 x 2.6 x 14.02 inch)
Weight (NW / GW)	6.7 kg (14.7 lbs) / 9.4 kg (20.7 lbs)
Carton Dimension (W X D X H)	820 x 169 x 513 mm (32.2 x 6.6 x 20.1 inch)
Accessories	1x DisplayPort Cable (1.4a), 1x Power Cord (C13), 1x Quick Guide, 4x VESA Wall Mount Screw, 1x Fiber Cloth, 1x Color Report
Note	HDMI™: 2560 x 1440 (Up to 240Hz) DisplayPort: 2560 x 1440 (Up to 240Hz) Support: HDMITM CEC, PIP/PBP; Non Support: KVM
Warranty	3 years (including panel burn-in)

CONNECTIONS



- 1. AC-in
- 2. 5-way Joystick Navigator
- 3. 2 x HDMI™ 2.1 (WQHD@240Hz)
- 4. DisplayPort 1.4a (HBR3)
- 5. Headphone out
- 6. Kensington lock