

TECRA® A65-M (BHL11U-035011)

GIVE YOUR WORKFLOW AN AI BOOST

The Tecra A65-M combines a spacious 16" display with AMD Ryzen™ performance, designed for professionals who need more room to work. With expansive storage, advanced AI video features and enterprise level security, the Tecra A65 delivers an immersive productive experience without compromise.



SUPERIOR PERFORMANCE & EFFICIENCY

Delivering fast, efficient performance and remarkable battery life, the Tecra® A65 is powered by AMD Ryzen™ 200 Series processors and AMD Radeon™ Graphics for modern productivity on the go.



CLEARLY SEE THE BIGGER PICTURE

Experience the vibrant new 16-inch WUXGA display with a 16:10 aspect ratio, (touch optional), providing crisp and clear visuals for a more engaging work and entertainment experience.



ROBUST SECURITY AND DURABILITY

Built to meet Microsoft's Secured-core PC requirements, it offers advanced hardware and software security. The durable MIL-SPEC-rated chassis is engineered for resilience.



MASTERING THE HYBRID WORKPLACE

The Tecra® A65-M's 5MP AI-enhanced webcam, dual microphones, and upgraded audio system with DTS processing make it perfect for clear, productive video conferencing.



CONNECT AT SUPERHERO SPEEDS

Stay connected with MediaTek Wi-Fi 7 802.11BE and a comprehensive selection of ports, including HDMI, Thunderbolt 4, USB Type-A, and a microSD card slot, ensuring you have all the connections you need.



EMPOWERED WITH AN AI WINGMAN


Meet Microsoft Copilot, accessible via a dedicated key, it streamlines tasks, like launching apps and adjusting system settings, through voice or text commands, enhancing efficiency and device navigation.



Laptops That Defend Against Cyber Threats



Dynabook's Windows 11 Secured-core PC laptops offer advanced security by integrating robust hardware and software defenses into their core components. These laptops provide a fortified shield against sophisticated cyber threats, employing specialized hardware protections and firmware safeguards. They ensure unparalleled security from boot-up, defending against malware and firmware attacks to safeguard critical data and uphold the integrity of business operations.



PLATFORM SPECIFICATIONS AND CONFIGURABLE OPTIONS

Operating System*

- Windows 11 Pro

Processor and Graphics*

- AMD Ryzen™ 7 250
 ◦ (24 MB Cache, up to 5.10 GHz)
- AMD Radeon™ 780M Graphics

Memory*

- 16 GB DDR5
- Two DDR5 5400 SODIMM slots
- Configurable up to 64GB
- Dual-channel support

Display*

- 16.0" WUXGA (1920x1200)

Storage*

- 512 GB SSD
- PCIe NVMe SSD up to 2 TB

Communications

- 1 Gbps Ethernet
- MediaTek Wi-Fi 7 802.11BE
- Bluetooth™

Camera w/ Privacy Shutter*

- HD 720p Webcam
- 5MP Webcam
- 5MP Webcam + IR Camera
- IR Camera for Windows Hello® Face Sign-in

Audio

- Stereo Speakers w/ DTS Processing
- Dual-microphone array

Ports

- HDMI®
- Two (2) USB-C ports supporting Thunderbolt 4
- Two (2) USB 3.2 Gen 1 Type-A ports
- One supporting USB Sleep & Charge
- RJ-45 Ethernet LAN port
- Headset jack (Combo port)
- microSD™ card slot

Security*

- Microsoft Secured-core PC
- Trusted Platform Module 2.0
- Fingerprint Reader
- Smart Card Reader
- Security Lock Slot

Input Devices

- Premium Raised-tile
- Spill-resistant
- Backlit Keyboard
- ClickPad Pointing Device

Battery

- 60 Wh Li-Polymer Battery

Physical Description


- Dark Blue Metallic
- Polycarbonate ABS Chassis
- Designed to MIL-STD-810H standards
- 357 x 248.85 x 19.9 mm (14.05 x 9.80 x 0.78 in)
- Starting at 1.69 kilograms (3.73 pounds)

Regulatory / Environmental Specifications

- EPEAT® Rated
- ENERGY STAR® Qualified
- RoHS Compatible

Warranty*

- Includes up to 4 years of standard limited warranty, covering depot or carry-in service.
 +Care Service® Warranty with On-Site is optional.



+Care Service® Warranty with On-Site

Tecra laptops are backed by one of the best standard warranties in the business. For even greater peace of mind, Dynabook's industry-leading +Care Service® Warranty with On-site can be added for worry-free reliability with up to four years of coverage. With comprehensive warranty coverage and access to a vast service and support network, Dynabook helps businesses minimize downtime, reduce IT costs, and ensure uninterrupted productivity.

Optional Accessories

- PS0120UA1PRP – Dynabook Thunderbolt™ 4 Dock
- PA5356U-1PRP – Dynabook USB-C® Dock
- PS0001UA1PRP – USB-C® to HDMI® / VGA / LAN / USB 3.0 Adapter with Power Delivery (PD) Charging
- PS0089UA1PRP – USB-C® to VGA / LAN Adapter with Power Delivery (PD) Charging
- PA5270U-1PRP – USB-C® to VGA Adapter with Power Delivery (PD) Charging
- PA5352U-1ACA – 65W USB-C® AC Adapter (5V / 9V / 15V / 20V)

CONFIGURE THE RIGHT LAPTOP FOR YOUR ORGANIZATION TODAY

US.DYNABOOK.COM

* Based on Configuration

** Visit <http://us.dynabook.com/info> for a complete list of all product legal footnotes

© 2025 Dynabook Americas, Inc. While Dynabook has made every effort at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, prices, system/component/options availability are all subject to change without notice. Dynabook, the Dynabook logo and +Care Service are trademarks or service marks of Dynabook Americas, Inc. and/or Dynabook, Inc. All other products and names are the property of their respective owners. All rights reserved.



Dynabook Recommends
Windows 11 Pro for Business



042925MF