

ThinkPad L14 Gen 6 (AMD)

For fast-paced professionals on the move, this laptop delivers high-endurance performance wherever work takes them. Powered by up to AMD Ryzen™ 7 PRO 200 series processors, it handles complex tasks with ease, while AI capabilities reaching up to 38 TOPS accelerate workloads like intelligent automation and content generation. Creative visuals and responsive interfaces are supported by up to AMD Radeon™ 780M graphics, making it ideal for real-time editing or immersive design. And with up to 64GB DDR5 memory, multitasking across demanding applications remains smooth and uninterrupted throughout the day.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad L series laptops offer reliable performance and durability for modern professionals with powerful processors, robust security features, long battery life, and versatile connectivity options, ensuring productivity on-the-go.

With a 14" WUXGA display and up to 500 nits brightness, visuals stay sharp in any environment, perfect for professionals reviewing contracts outdoors or demoing presentations on the go. Its optional multi-touch screen boosts interactivity, while USB-A, USB-C®, DisplayPort™, HDMI, and optional Wi-Fi® 7 ensure flexible connectivity anywhere.

Up to 2TB SSD storage allows ample room for high-resolution media, business files, or virtual machines. Enhanced protection comes via discrete TPM 2.0, with added biometric convenience from the optional touch fingerprint reader and IR camera.

Ideal for virtual meetings, it features an HD 720p camera with a privacy shutter and fixed focus, along with a dual-microphone array enhanced by Elevoc Voice for clear, professional audio in any environment.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

ThinkPad Bluetooth Silent Mouse

- Left/Right hand, easy-to-carry low profile mouse
- Switch between 2 devices with dual-host Bluetooth 5.0 connectivity
- 2-way scrolling with on-the-fly DPI adjustment (2400, 1600, 800)



PN: With Battery : 4Y50X88822 Without Battery : 4Y50X88823

ThinkPad L14 Gen 6 (AMD)

Performance

Processor

AMD Ryzen 3/5/7 PRO 200 Series Processor - Hawk Point (HWK)
AMD Ryzen AI 5/7 PRO 300 Series Processor - Krackan Point (KRK)

AI PC Category*

AI PC (models with AMD Ryzen 5 PRO 230, Ryzen 7 PRO 250 processors)
Copilot+ PC (Krackan Point)

Operating System*

Windows 11 Pro or Home
Windows 11 IoT Enterprise LTSC 2024
Windows 10 IoT Enterprise LTSC 2021
Ubuntu Linux, Linux

NPU

Integrated AMD Ryzen AI, up to 50 TOPS*

Graphics

AMD Radeon 740M (integrated)
AMD Radeon 760M (integrated)
AMD Radeon 780M (integrated)
AMD Radeon 840M (integrated)
AMD Radeon 860M (integrated)

Memory^{1 11}

Up to 64GB DDR5-5600, 2x SO-DIMM

¹The max memory is based on the test results with current Lenovo memory offerings.

¹¹The max memory is based on the test results with current Lenovo memory offerings.

Storage^{2 2}

Up to 1x 2TB M.2 2280 PCIe NVMe SSD

²The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, 360° far-field, Elevoc Voice

Camera*

HD 720p, with privacy shutter
5.0MP + IR discrete, with privacy shutter, temporal noise reduction

Battery³

46.5Wh or 57Wh battery, up to 14.26 hr
Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim GaN adapter, PD 3.0

Design

Display⁴

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 60Hz, 3M DBEF5
- 400nits, 45% NTSC, 60Hz, 3M DBEF5, on-cell touch, Eyesafe
- 500nits, 100% sRGB, 60Hz, low power, Eyesafe

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Screen-to-Body Ratio

85.5%

Keyboard

6-row, spill-resistant, Copilot key, optional backlight

Touchpad

TrackPoint and Mylar surface TrackPad
60 x 115 mm (2.36 x 4.53 inches)

Dimensions^{3 5}

Models with PC-ABS (top) and PC-ABS (bottom)
313.7 x 226 x 11.39/17.31 (front/rear), 22.9 (maximum) mm
12.35 x 8.90 x 0.45/0.68 (front/rear), 0.90 (maximum) inches

Models with aluminium (top) and PC-ABS (bottom)
313.7 x 226 x 11.32/17.01 (front/rear), 21.7 (maximum) mm
12.35 x 8.90 x 0.45/0.67 (front/rear), 0.85 (maximum) inches

Models with aluminium (top) and PC-CF (bottom)
313.7 x 226 x 11.32/17.01 (front/rear), 21.5 (maximum) mm
12.35 x 8.90 x 0.45/0.67 (front/rear), 0.85 (maximum) inches

³The system dimensions may vary depending on configurations.

⁵The system dimensions may vary depending on configurations.

Weight^{4 6}

Starting at 1.38 kg (3.05 lbs)

⁴The system weight is approximate and may vary depending on configurations

⁶The system weight is approximate and may vary depending on configurations

Color

Black

Case material

Aluminium (top), PC-CF (bottom)
Aluminium (top), PC-ABS (bottom)
PC-ABS (top), PC-ABS (bottom)

Connectivity

Ethernet*

Gigabit onboard Ethernet

WLAN + Bluetooth*⁵

MediaTek Wi-Fi 7 MT7925, 802.11be, Bluetooth 5.4

⁵Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

WWAN*

4G LTE CAT6 with embedded eSIM
4G LTE CAT16 with embedded eSIM

NFC

Near Field Communication*

Ports

1x USB-A (Hi-Speed USB / USB 2.0)
2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.1 & DP 1.4a
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Ethernet (RJ45)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking

Docking support via Thunderbolt or USB-C

Security & Privacy

Security

Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*
Privacy Guard with Privacy Alert (software solution)
ThinkShield

Manageability

System Management*⁶

DASH

⁶Intel vPro offers a superset of DASH's defined capabilities