

ThinkPad X9-15 Gen 1 Aura Edition

Enhance productivity with up to Intel® Core™ Ultra 7 processor on Intel vPro®, Evo™ Edition platform, delivering lightning-fast speeds for seamless multitasking. Paired with Intel® Arc™ Xe 2 graphics, this laptop is a powerhouse for creative professionals handling complex designs and animations. With up to 32GB LPDDR5x memory, mobile consultants can run resource-intensive software effortlessly, while business travelers breeze through simultaneous applications with zero lag. From spreadsheets to CAD designs, every task feels remarkably smooth.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkPad X series laptops offer portability and power for modern professionals. With lightweight designs, robust performance from their processors, long battery life, and security features, they are ideal for on-the-go productivity.

Enhance visual experiences with its 15.3" 2.8k OLED display. With vibrant colors, anti-reflection technology, and TÜV-certified low blue light comfort, it ensures every image is crisp and clear. Whether presenting ideas or editing visuals, the display adapts to one's needs, delivering impeccable clarity.

Stay effortlessly connected with dual Thunderbolt™ 4 ports for high-speed data transfers and docking. Experience the future of connectivity with Intel® Wi-Fi 7, enabling ultra-fast and stable networks, whether working from the office or attending a virtual meeting on the go.

With TÜV Rheinland certifications and Eyesafe® features, the anti-reflection, anti-smudge OLED display ensures reduced eye strain during extended work sessions, making it ideal for professionals juggling demanding schedules.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo Go USB-C Wireless Mouse

- Ergonomically designed ambidextrous mouse with Villi painted grip and wireless connection via USB-C dongle
- Silent buttons with 2-way scroll wheel (up/down), programmable Utility Button on the side
- Default functions optimized for Teams calls, can be configured through Lenovo Go Central Software



PN: 4Y51C21216

Lenovo 16-inch Laptop Casual Topload

- One-size-fits-all compartment for laptops up to 16 inches
- High-quality, water repellent fabric for maximum durability
- Conveniently placed compartments and pockets for quick access



PN: GX41L83769



ThinkPad X9-15 Gen 1 Aura Edition

Performance

Processor
Intel V Series Core Ultra 5 / 7 Processor (Series 2)

AI PC Category*
Copilot+ PC

Operating System*
Windows 11 Pro or Home
Ubuntu Linux, Linux

NPU*
Integrated Intel AI Boost, up to 48 TOPS

Graphics
Intel Arc Graphics 130V (integrated)
Intel Arc Graphics 140V (integrated)

Memory
16GB LPDDR5x-8533 MoP memory, soldered
32GB LPDDR5x-8533 MoP memory, soldered

Storage¹
Up to 1x 2TB M.2 2242 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*
SoundWire
Stereo speakers, 2W x2 woofers and 2W x2 tweeters
Dolby Atmos
Dual-microphone array with smart noise-cancelling

Camera*
UHD 8.0MP with large sensor + IR discrete, with E-shutter, ToF sensor, MIPI

Battery²
80Wh (up to 21.18 hr) battery

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
65W USB-C slim GaN adapter, PD 3.0
65W USB-C nano GaN adapter, PD 3.0

Design

Display
15.3" 2.8K (2880x1800) OLED anti-reflection / anti-fingerprint 16:10 91% STB
- 500nits, 100% DCI-P3, Eye Comfort, Dolby Vision, DisplayHDR True Black 600, 120Hz VRR, X-Rite factory color calibration
- 500nits, 100% DCI-P3, Eye Comfort, Dolby Vision, DisplayHDR True Black 600, 120Hz VRR, X-Rite factory color calibration, touch

Screen-to-Body Ratio
91%

Keyboard
6-row, spill-resistant, Copilot key, backlight

Touchpad
Glass surface Trackpad or Haptic Touchpad
80 x 135 mm (3.15 x 5.31 inches)

Dimensions³
339.55 x 228.5 x 12.9 mm (13.37 x 9.0 x 0.51 inches)

³The system dimensions may vary depending on configurations.

Weight⁴
Starting at 1.4 kg (3.08 lbs)

⁴The system weight is approximate and may vary depending on configurations

Color
Grey
White

Case material
Aluminium (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth*
Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

Ports
1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)

Docking
Docking support via Thunderbolt or USB-C

Security & Privacy

Security
ThinkShield
Discrete TPM 2.0
Touch style MOC fingerprint reader
E-shutter
IR camera for Windows Hello (facial recognition)
ToF Human Presence Detection

Manageability

System Management*⁵
Intel vPro Enterprise*

⁵Intel vPro offers a superset of DASH's defined capabilities.

Environmental

Material
50% recycled aluminium on top cover
50% recycled aluminium on keyboard frame
50% recycled aluminium on bottom cover
90% PCC recycled plastic used in the battery pack enclosure
100% recycled cobalt used in the 80Wh battery
85% PCC recycled plastic used in key caps
90% PCC recycled plastic used in speaker enclosure
30% recycled REE (Rare Earth) in speaker magnet
90% PCC recycled plastic used in standard 65W adapter
FSC certified plastic-free packaging (except for Japan models with white case)
Bamboo+sugarcane fiber standard/retail packaging (except for Japan models with white case)
Paper Based Giftbox (Japan models with white case)

Certifications

Green Certifications^{6 7 8}
ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified, generation 10
RoHS compliant

⁶The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁷EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

⁸EPEAT is registered where applicable, please see PEAT.net for registration status by country.

Other Certifications
Intel Evo Platform*
Eyesafe Certified 2.0
TÜV Rheinland Eye Comfort Certification (5-star)
MIL-STD-810H

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2025 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.