

Lenovo V15 G6 ARP

Engineered for the mobile professional, the laptop combines efficiency, reliability, and sleek performance. Powered by the AMD Ryzen™ 3 / 5 / 7 100 Series Processor and equipped with integrated AMD Radeon™ 660M or 680M Graphics, it effortlessly handles everyday business tasks while keeping visuals sharp and responsive. With up to 32GB DDR5-4800 memory and up to 1TB SSD storage, users get the speed and capacity needed to stay productive on the go, whether managing projects, attending virtual meetings, or multitasking between apps.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Combining security and productivity features with a simple design, powerful technology, and all-day battery life, Lenovo V Series laptops are perfect for small business professionals who demand long-term performance and reliability.

The HD 2W dual Realtek® ALC3287 codec speakers provide a rich, immersive sound experience, enabling professionals to collaborate seamlessly with colleagues and clients, even while on the move. Furthermore, the dual-microphone array guarantees clear voice transmission during video calls and conferences.

Whether working on a project deadline or managing a client presentation, the 47Wh Rechargeable Li-ion Battery with rapid charge support ensures the laptop allows professionals to work confidently, without worrying about constant recharging.

The dimensions of 359.2 x 235.8 x 19.9 mm (14.14 x 9.28 x 0.78 inches) make it easier to carry the laptop around, whether it's for meetings, travel, or working from different locations. This portability enhances flexibility and productivity for professionals who are often on the go.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Thinkpad Essential 16" Backpack (Eco)

- Two internal compartments (one for notebooks up to 16"), two front zipper pockets, and one side mesh water bottle sleeve that ensure you'll never run out of space.
- A padded top handle. And a rear luggage strap. Every feature is crafted for convenience and comfort.
- Elegant black nylon exterior, grey interior lining, and a splash of red accents.



PN: 4X41C12468

Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: G0A6130WUS, G0A6130WEU, G0A6130WUK

Performance

Processor AMD Ryzen 3 / 5 / 7 100 Series Processor
Operating System* Windows 11 Pro or Home
Graphics AMD Radeon 660M (integrated) AMD Radeon 680M (integrated)
Memory¹ Up to 32GB DDR5-4800 offering, 2x SODIMM
<i>¹The max memory is based on the test results with current Lenovo memory offerings.</i>
Storage² One drive, up to 1TB M.2 2242 SSD
<i>²The storage capacity supported is based on the test results with current Lenovo storage offerings.</i>
Audio* High Definition (HD) Audio Stereo speakers, 2W x2 Dual-microphone array
Camera* HD 720p, with privacy shutter
Battery³ 47Wh battery (up to 7.28 hr), Rapid Charge
<i>³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.</i>
Power Adapter* 65W round tip adapter 65W USB-C adapter, PD 3.0 65W USB-C slim adapter, PD 3.0

Design

Display⁴ 15.6" FHD (1920x1080) 16:9 TN Anti-glare 300nits, 45% NTSC 15.6" FHD (1920x1080) 16:9 IPS Anti-glare 300nits, 45% NTSC <i>⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.</i>
Screen-to-Body Ratio 87%
Keyboard 6-row, spill-resistant, numeric keypad, Copilot key
Touchpad Mylar surface touchpad 70 x 105 mm (2.76 x 4.13 inches)
Dimensions⁵ 359.2 x 235.8 x 19.9 mm (14.14 x 9.28 x 0.78 inches) <i>⁵The system dimensions may vary depending on configurations.</i>
Weight⁶ Starting at 1.6 kg (3.53 lbs) <i>⁶The system weight is approximate and may vary depending on configurations</i>
Color Business black Luna grey
Case material PC-ABS (top) PC-ABS (bottom)
Connectivity
Ethernet Gigabit onboard Ethernet

WLAN + Bluetooth* 802.11ax(Wi-Fi 6), Bluetooth 5.2
Ports 2x USB-A (USB 5Gbps) 1x USB-C (USB 10Gbps), with USB PD (20V only) & DP 1.2 1x HDMI 1.4b 1x Ethernet (RJ-45) 1x Headphone / microphone combo jack (3.5mm) 1x Power connector
Docking Docking support via USB-C
Security Discrete TPM 2.0 Kensington Nano Security Slot Touch style MOC fingerprint reader on power button* Camera privacy shutter
Material 25-30% PCC recycled plastic used in the battery pack 90% PCC recycled plastic used in standard 65W USB-C adapter 30% PCC recycled plastic used in standard 65W round tip adapter 100% recycled dry-pressed pulp cushion 90% recycled content in OBP bag FSC certified content in carton and accessory box

Certifications

Green Certifications^{7 8 9} ENERGY STAR 9.0 EPEAT Gold Registered* ErP Lot 6/26 TCO Certified, generation 10* RoHS compliant <i>⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.</i> <i>⁸EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.</i> <i>⁹EPEAT registration and TCO certification are only available for MT 83V4. EPEAT is registered where applicable, please see epeat.net for registration status by country.</i>
Other Certifications TÜV Rheinland Low Blue Light (Software Solution)

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2025 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.