

Aspekt Touch

32" 4K UHD Docking Monitor with Touchscreen and 145W USB Charging



UHD Display



Bright & Colour
Accurate



Laptop
Charging



Fold Down
To Draw



Supports Daisy
Chaining
Windows: Extended Displays.
Mac: Mirrored Displays



Supports Stylus and
Multitouch



145W Charging
for Laptop and
Accessories



80% Recycled
Aluminium



Part no

Colour

32A4KPDMSLV
32A4KPDMSG
32A4KPDMSBLK

• Silver
• Space Grey
• Space Black

Part no

Colour

Stand


A32FSSGR
A32FSBLK
A32FSSLV
A32RSSGR
A32RSSLV
A32OFSSLV

• Space Grey
• Space Black
• Silver
• Space Grey
• Silver
• Silver

Fold Stand
Fold Stand
Fold Stand
Raise Stand
Raise Stand
Omni 2-in-1

Aspekt Does It All

With Omni 2-in-1 Mac Mini Fold Stand



With Aspekt Fold Stand



Aspekt Touch 4K Ultra-High Definition Docking Monitors combine the extraordinary brightness, colour accuracy and advanced touchscreen technology of our Clarity Touch monitors with ALOGIC's industry-leading integrated docking station technology, creating a spectacular centrepiece at the heart of your desktop that provides all the connectivity you need to get things done.

With 145W of USB charging for your laptop and up to four USB accessories, multi-monitor daisy chain connectivity, Gigabit Ethernet for fast and secure networking all delivered over a single USB-C cable, Aspekt's cutting-edge connectivity makes it the monitor of choice for anyone who wants to reduce the cables on their desk.

Connections

Ports	1x HDMI 2.0 Input
	1x DisplayPort 1.4 Input
	1x USB-C Host Input w/ 90W PD (DP Alt Mode)
	1x DisplayPort Output for Daisy Chain (MST)
	1x USB-C Device Input w/ 15W PD (rear)
	1x USB-A Device Input w/ 5W charging (rear)
	1x USB-C Device Input w/ 30W PD (side)
	1x USB-A Device Input w/ 5W charging (side)
	1x 3.5mm Headphone Jack
	1x Gigabit Ethernet RJ45
	1x Security Lock Slot

Touchscreen

10 Point Multitouch
Compatible with MPP 2.0 Styluses
Built-in Magnetic Stylus Holder

Brightness

400 nits (Typical)

Resolution

Up to 3480x2160 (Landscape)

Aspect Ratio

16:9

Physical Characteristics

Product Dimensions	730x570x260mm (LxWxH)
Material	ABS, Glass, Aluminium
Weight	Monitor Only: 9kg
	Raise Stand: 3.3kg
	Fold Stand: 5.6kg
	Omni Stand: 5.4kg
VESA Mount Compatible:	FDMI MIS-D 100mm
Screen Size:	32"

Contrast Ratio

1000:1

Package Includes

Aspekt Touch Monitor
Aspekt Monitor Stand (SKU Dependent)
USB-C Cable
HDMI Cable
DisplayPort Cable
Power Adapter
User Manual

Power Adapter

Adapter Input	AC 100V-240V~ 50/60Hz
Adapter Output	DC 24V $\overline{\text{---}}$ 8A, 192W (Max)
Typical Consumption	30-50W
Max Consumption	192W

Charging

Laptop: Up to 90W over USB-C
55W shared between USB accessories

Colour Accuracy

Colour Coverage (DCI-P3):	100%
Colour Coverage (Adobe RGB):	93%
Colour Coverage (sRGB):	100%
Average ΔE:	>2

Refresh Rate

60Hz

Panel

IPS with Matt Finish

Viewing Angle

178°(H) / 178°(V)

Audio

Speakers: 5Wx2
Audio Out: Yes

Device Compatibility

Apple, Chromebook, Microsoft

Response Time

14ms (Grey to Grey)

Warranty

2 Years